

TIDA-00807 REV E2 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1	1	2200pF	GRM188R71C222KA01D	MuRata	CAP, CERM, 2200 pF, 16 V, +/- 10%, X7R, 0603	0603
C2	1	0.47uF	C0603C474K9RACTU	Kemet	CAP, CERM, 0.47 µF, 6.3 V, +/- 10%, X7R, 0603	0603
C3, C4, C6, C7,	11	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1uF, 25V, +/-5%, X7R, 0603	0603
C11, C13, C15,						
C20, C21, C23,						
C24						
C5	1	4.7uF	GRM188R60J475ME19D	MuRata	CAP, CERM, 4.7 µF, 6.3 V, +/- 20%, X5R, 0603	0603
C8, C9, C14, C18,	5	0.01uF	C1608C0G1E103J	TDK	CAP, CERM, 0.01uF, 25V, +/-5%, C0G/NP0, 0603	0603
C22						
C10	1	0.015uF	GRM188R71E153KA01D	MuRata	CAP, CERM, 0.015 µF, 25 V, +/- 10%, X7R, 0603	0603
C12, C16, C17,	4	100pF	06033C101KAT2A	AVX	CAP, CERM, 100pF, 25V, +/-10%, X7R, 0603	0603
C19		· ·				
C25	1	4.7uF	C2012X5R1H475K125AB	TDK	4.7µF ±10% 50V X5R Ceramic Capacitor	0805
C26, C29	2	33 uF	T491D336M010AT	Kemet	CAP TANT 33UF 10V 20% 2917	7343 (D)
C27	1	10uF	1210YD106KAT2A	AVX	CAP, CERM, 10uF, 16V, +/-10%, X5R, 1210	1210
C28	1	1uF	C0603C105K4PACTU	Kemet	CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603	0603
D1	1	Green	LG L29K-G2J1-24-Z	OSRAM	LED, Green, SMD	1.7x0.65x0.8mm
D2	1	3.3V	PESD3V3L1BA	NXP Semiconductor	DIODE, TVS, BIDIRECTIONAL, 3.3VWM, 26VC, SOD323	SOD323
D3	1	3.6V	MMSZ4685T1G	ON Semiconductor	Diode, Zener, 3.6 V, 500 mW, SOD-123	SOD-123
D4, D5, D6, D7,	6	Green	150060GS75000	Wurth Elektronik	LED, Green, SMD	LED_0603
D8, D9						
FB1, FB2	2	42 OHM	FBMJ2125HS420-T	TAIYO YUDEN	FERRITE BEAD, 42 OHM, 4 A, DCR0.008 OHM, SMT-0805	0805
J1, J2	2		5-146278-4	TE Connectivity	Header, 100mil, 4x1, Tin, TH	Header, 4x1, 100mil,
				j		TH
J3, J5	2		OSTVN02A150	On-Shore Technology	Terminal Block, 2.54mm, 2x1, Brass, TH	Terminal Block,
						2.54mm, 2-pole,
						Brass, TH
J4	1		ED120/2DS	On-Shore Technology	TERMINAL BLOCK 5.08MM VERT 2POS, TH	TERM_BLK, 2pos,
						5.08mm
JP2	1		5-146280-2	TE Connectivity	Header, 100mil, 2x1, Gold, TH	2x1 Header
L1	1	3.3uH	B82422H1332K	EPCOS Inc	Inductor, Chip, 3.3uH 770MA 1210 10%	1210
L2	1	2.2uH	744030002	Wurth Elektronik	Inductor, Shielded Drum Core, Metal Composite, 2.2 µH, 0.74 A, 0.14	3.5x0.95x3.3mm
					ohm, SMD	
R1, R2, R33, R35,	8	47.0k	RC0603FR-0747KL	Yageo America	RES, 47.0 k, 1%, 0.1 W, 0603	0603
R37, R39, R67,						
R68						
R3	1	680	RC0603FR-07680RL	Yageo America	RES, 680, 1%, 0.1 W, 0603	0603
R4, R5, R11, R12	4	4.70k	RC0603FR-074K7L	Yageo America	RES, 4.70 k, 1%, 0.1 W, 0603	0603
R6, R44	2	30.0k	RC0603FR-0730KL	Yageo America	RES, 30.0 k, 1%, 0.1 W, 0603	0603
R7, R9, R15, R17,	7	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100 ohm, 1%, 0.1W, 0603	0603
R20, R27, R38						
R8, R10	2	220	RC0603FR-07220RL	Yageo America	RES, 220, 1%, 0.1 W, 0603	0603
R13, R45, R49,	8	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, 0603	0603
R50, R63, R64,						
R65, R66						

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R14, R16, R18,	7	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
R25, R26, R28,						
R36						
R19	1	470	RC0603FR-07470RL	Yageo America	RES, 470 ohm, 1%, 0.1W, 0603	0603
R21	1	30.0k	RC0603FR-0730KL	Yageo America	RES, 30.0k ohm, 1%, 0.1W, 0603	0603
R22, R23	2	22.0	RC1206FR-0722RL	Yageo America	RES, 22.0 ohm, 1%, 0.25W, 1206	1206
R24	1	27.0k	RC0603FR-0727KL	Yageo America	RES, 27.0k ohm, 1%, 0.1W, 0603	0603
R29, R31, R43,	6	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100k ohm, 1%, 0.1W, 0603	0603
R47, R61, R69						
R30, R32, R34	3	332k	ERJ-8ENF3323V	Panasonic	RES, 332k ohm, 1%, 0.25W, 1206	1206
R40	1	10k	CRCW060310K0FKEA	Stackpole Electronics Inc	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
R41, R42	2	2.80k	CRCW12062K80FKEA	Vishay-Dale	RES, 2.80k ohm, 1%, 0.25W, 1206	1206
R46	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00Meg ohm, 1%, 0.1W, 0603	0603
R48	1	1.02	RC1206FR-071R02L	Yageo America	RES, 1.02 ohm, 1%, 0.25W, 1206	1206
R52	1	0	CRCW08050000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.125W, 0805	0805
R55, R56, R57,	6	220	CRCW0603220RJNEA	Vishay-Dale	RES, 220 ohm, 5%, 0.1W, 0603	0603
R58, R59, R60						
J1	1		MSP430FR5728IPWR	Texas Instruments	MIXED SIGNAL MICROCONTROLLER, PW0028A	PW0028A
J2	1		SN74LVC1G3157DBVR	TEXAS INSTRUMENTS	IC, SWITCH, SPDT, SOT23-6	DBV
U3	1		DAC101C081CIMK	Texas Instruments	10-Bit Micro Power Digital-to-Analog Converter with an I2C-Compatible	MK06A
					Interface, 6-pin Tiny SOT23	
J4	1		LMT87LPM	Texas Instruments	Analog Temperature Sensors with Class-AB Output, LP0003A	LP0003A
J5	1		DRV5032FBDBZR	Texas Instruments	Ultra-Low Power Digital-Switch Hall Effect Sensor, DBZ0003A	DBZ0003A
J6, U8	2		OPA2317IDR	Texas Instruments	Low-Offset, Rail-to-Rail I/O Operational Amplifier Precision Catalog,	D0008A
•					D0008A	
J7	1	LM4041BID	LM4041BIDBZ	TI	IC, Micropower Shunt Voltage Reference 100 ppm/°C, 45µA-12mA,	SOT23
		BZ			Adjustable	
J9	1		LMV331IDBV	Texas Instruments	Single General Purpose Low-Voltage Comparator, DBV0005A	DBV0005A
J10	1		TPS62740DSSR	Texas Instruments	360nA IQ Step Down Converter for Low Power Applications, DSS0012A	DSS0012A
R51, R53, R54,	0	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, 0603	0603
862						

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ('TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

Tl's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter Tl's applicable published warranties or warranty disclaimers for Tl products, and no additional obligations or liabilities arise from Tl providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Tl's standard terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated