

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	PCB	1		TIDA-01367	Any	Printed Circuit Board	
2	3P3V, 5V_EXT, AVR_EN, AVR_RDY, BVR_EN, BVR_RDY, CSNIN, CSPIN, SMB_ALT#, SMB_CLK, SMB_DAT, TSEN, VIN, VOUT_A_P, VOUT_B_P, VRFault#	16	Red	5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
3	C1, C11	2	1uF	C0603C105Z9VACTU	Kemet	CAP, CERM, 1 uF, 6.3 V, +/- 20%, Y5V, 0603	0603
4	C2, C3	2	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
5	C4, C5, C6, C7	4	22pF	GRM1885C1H220JA01D	MuRata	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
6	C10, C31, C48, C65, C75, C92, C109, C161, C185	9	0.1uF	C0603C104J4RACTU	Kemet	CAP, CERM, 0.1 uF, 16 V, +/- 5%, X7R, 0603	0603
7	C13	1	1000pF	C0603C102J5RACTU	Kemet	CAP, CERM, 1000 pF, 50 V, +/- 5%, X7R, 0603	0603
8	C14, C33, C50, C67, C84, C100, C154	7	0.1uF	GCM188R71H104KA57D	MuRata	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
9	C15, C34, C51, C68, C85, C102, C155	7	2.2uF	C0603C225K9PACTU	Kemet	CAP, CERM, 2.2 uF, 6.3 V, +/- 10%, X5R, 0603	0603
10	C16, C35, C52, C69, C86, C103, C156	7	0.01uF	06031C103KAT2A	AVX	CAP, CERM, 0.01 uF, 100 V, +/- 10%, X7R, 0603	0603
11	C17, C18, C20, C21, C36, C37, C38, C39, C53, C54, C55, C56, C70, C71, C72, C73, C87, C88, C89, C90, C104, C105, C106, C107, C157, C158, C159, C182, C183, C187	30	22uF	GRM31CR61C226ME15L	MuRata	CAP, CERM, 22 uF, 16 V, +/- 20%, X5R, 1206	1206
12	C30, C186	2	470uF	EEE-FK1E471P	Panasonic	CAP, AL, 470uF, 25V, +/-20%, 0.08 ohm, SMD	SMT Radial G
13	C44, C45, C46, C59, C60, C64, C93, C99	8	47uF	JMK212BJ476MG-T	Taiyo Yuden	CAP, CERM, 47 uF, 6.3 V, +/- 20%, X5R, 0805	0805
14	C81, C111, C112, C113, C114, C115, C192	7	470uF	EEF-GX0E471R	Panasonic	CAP, Aluminum Polymer, 470 uF, 2.5 V, +/- 20%, 0.003 ohm, SMD_7.3x1.9x4.3mm SMD	SMD_7.3x1.9x4.3mm
15	C123, C124, C125, C126, C127, C128, C129, C130, C131, C132, C133, C141, C142, C143, C144, C145, C146, C147, C148, C149, C150, C151	22	22uF	GRM21BR61E226ME44L	MuRata	CAP, CERM, 22 uF, 25 V, +/- 20%, X5R, 0805	0805
16	C162, C163, C164, C165, C166, C167, C168, C169, C170, C171, C172, C173	12	100uF	GRM21BR60J107M	MuRata	CAP, CERM, 100 uF, 6.3 V, +/- 20%, X5R, 0805	0805
17	C175, C176, C180	3	1uF	EMK107B7105KA-T	Taiyo Yuden	CAP, CERM, 1 uF, 16 V, +/- 10%, X7R, 0603	0603
18	C181, C184	2	1uF	C0603C105K3RACTU	Kemet	CAP, CERM, 1 uF, 25 V, +/- 10%, X7R, 0603	0603
19	C188, C190, C191	3	4.7uF	GRM188R61A475ME15	MuRata	CAP, CERM, 4.7 uF, 10 V, +/- 20%, X5R, 0603	0603
20	C189	1	0.01uF	GRM188R70J103KA01D	MuRata	CAP, CERM, 0.01 uF, 6.3 V, +/- 10%, X7R, 0603	0603
21	D1, D2	2	30V	MBR0530T1G	ON Semiconductor	Diode, Schottky, 30 V, 0.5 A, SOD-123	SOD-123
22	FID4, FID5, FID6	3		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
23	H9, H10, H11, H12	4		SJ-5303 (CLEAR)	3M	Bump-on, Hemisphere, 0.44 X 0.20, Clear	Transparent Bump-on
24	J1	1		5103308-1	TE Connectivity	Header (shrouded), 100mil, 5x2, Gold, TH	5x2 Shrouded header
25	J2, J4, J5, J6	4		TSW-102-07-G-S	Samtec	Header, TH, 100mil, 2x1, Gold plated, 230 mil above insulator	2x1 Header
26	J3	1		1727010	Phoenix Contact	Conn Term Block, 2POS, 3.81mm, TH	2POS Terminal Block
27	L1	1	55nH	HCB65-550X	Delta Electronics Inc.	Inductor, ?, 55 nH, 30 A, 0.0002 ohm, SMD	5.5x5.7mm
28	L2, L3, L4, L5, L6, L7	6	150nH	IHLPS050FDERR15M01	Vishay-Dale	Inductor, Shielded, Powdered Iron, 150 nH, 55 A, 0.0006 ohm, SMD	IHLPS-5050FD
29	L8	1	200nH	MPC0730LR20C	Kemet	Inductor, Ferrite, 200 nH, 17.5 A, 0.00132 ohm, SMD	8x6.7mm
30	LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
31	PGND, PGND2, PGND3, PGND4, VOUT_A_N, VOUT_B_N	6	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
32	Q1, Q2, Q3, Q4	4	30V	CSD17570Q5B	Texas Instruments	MOSFET, N-CH, 30 V, 51 A, DNK0008A (VSON-CLIP-8)	DNK0008A
33	R1, R2, R3, R4, R87	5	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
34	R5, R7, R8, R12, R13, R14, R15, R86	8	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
35	R9, R10, R11	3	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
36	R17, R21, R24, R25, R28, R30, R31, R33, R36, R37, R39, R42, R44, R47, R48, R50, R83	17	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
37	R18, R22, R27, R34, R40, R45	6	110k	CRCW0402110KFKED	Vishay-Dale	RES, 110 k, 1%, 0.063 W, 0402	0402
38	R19, R23, R29, R35, R41, R46, R52	7	2.20	ERJ-3RQF2R2V	Panasonic	RES, 2.20, 1%, 0.1 W, 0603	0603
39	R51	1	150k	CRCW0603150KFKEA	Vishay-Dale	RES, 150 k, 1%, 0.1 W, 0603	0603
40	R59, R60	2	24.9	RC0603FR-0724R9L	Yageo America	RES, 24.9, 1%, 0.1 W, 0603	0603
41	R61, R62, R63, R64, R65, R66, R67, R68, R69, R70, R71, R72, R73, R74, R75, R76, R77, R78, R79, R80, R81, R82, R84, R85	24	0.1	ERJ-8BWF100V	Panasonic	RES, 0.1, 1%, 0.5 W, 1206	1206
42	S1, S2	2		GT11MCBE	C&K Components	Switch, SPDT, On-On, 1 Pos, 0.4VA, 20V, TH	7.01x4.5mm
43	SR 1	1	0.0003	WSL4026L3000FEB	Vishay-Dale	RES, 0.0003, 1%, 3 W, 10.1x2.68x2.6mm	10.1x2.68x2.6mm
44	T2, T3, T5, T6, T7, T8, T9, T10	8	90A	CB70-14-CY	Panduit	Terminal 90A Lug	CB70-14-CY
45	TP1, TP2, TP3, TP4	4		5007	Keystone	Test Point, Compact, White, TH	White Compact Testpoint
46	U1	1		TPS53679RSB	Texas Instruments	Dual-Channel (6+1 or 5+2 Phases) D-CAP+ Step-Down Multiphase Controller with Non-Volatile Memory and PMBus Interface for VR13 Server VCore, RSB0040E (WQFN-40)	RSB0040E
47	U2, U3, U4, U5, U6, U7, U8	7		CSD95490Q5MC	Texas Instruments	Synchronous Buck NexFET Power Stage, DMC0012A (VSON-CLIP-12)	DMC0012A
48	U9	1		TPS73733QDRBRQ1	Texas Instruments	Single Output Automotive LDO, 1 A, Fixed 3.3 V Output, 2.2 to 5.5 V Input, with Reverse Current Protection, 8-pin SON (DRB), -40 to 125 degC, Green (RoHS & no Sb/Br)	DRB0008A
49	U502	1		UCC27524AD	Texas Instruments	Dual, 5A, High-Speed Low-Side Power MOSFET Driver, with Negative Input Voltage Ability, D0008A (SOIC-8)	D0008A
50	C8, C9, C12	0	0.1uF	C0603C104J4RACTU	Kemet	CAP, CERM, 0.1 uF, 16 V, +/- 5%, X7R, 0603	0603
51	C22, C40, C57, C74, C91, C108, C160	0	1000pF	GRM1555C1H102JA01D	MuRata	CAP, CERM, 1000 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
52	C23, C24, C25, C26, C27, C28, C29, C41, C42, C43, C47, C58, C61, C62, C63, C76, C77, C78, C79, C80, C82, C94, C95, C96, C97, C98, C110, C116	0	47uF	JMK212BJ476MG-T	Taiyo Yuden	CAP, CERM, 47 uF, 6.3 V, +/- 20%, X5R, 0805	0805
53	C32, C49, C66, C83, C101, C117, C174	0	0.01uF	C0805C103K5RACTU	Kemet	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, 0805	0805
54	C118, C119, C120, C121, C122, C134, C135, C136, C137, C138, C139, C140, C152, C153	0	22uF	GRM21BR61E226ME44L	MuRata	CAP, CERM, 22 uF, 25 V, +/- 20%, X5R, 0805	0805
55	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
56	R6, R16	0	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
57	R20, R26, R32, R38, R43, R49, R53	0	1.00	ERJ-6RQF1R0V	Panasonic	RES, 1.00, 1%, 0.125 W, 0805	0805
58	R58	0	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
59	T1, T4	0	90A	CB70-14-CY	Panduit	Terminal 90A Lug	CB70-14-CY

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated