

PMP40355 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1	1	47uF	EMVH101ARA470MKE0S	Chemi-Con	CAP, AL, 47 µF, 100 V, +/- 20%, 0.33 ohm, SMD	KE0
C2, C3, C4, C15	4	1uF	GRM32CR72A105KA35L	MuRata	CAP, CERM, 1 µF, 100 V, +/- 10%, X7R, 1210	1210
C5	1	0.01uF	08051C103JAT2A	AVX	CAP, CERM, 0.01 µF, 100 V,+/- 5%, X7R, 0805	0805
C7	1	0.1uF	GRM219R71C104KA01D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0805	0805
C8	1	220uF	EMVA250ADA221MHA0G	Chemi-Con	CAP, AL, 220 µF, 25 V, +/- 20%, SMD	HA0
C9, C10, C16, C17	4	0.01uF	CGA3E2X7R2A103K080AA	TDK	CAP, CERM, 0.01 µF, 100 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C11	1	22uF	CL32A226KAJNNNE	Samsung Electro-Mechanics	CAP, CERM, 22 µF, 25 V, +/- 10%, X5R, 1210	1210
C12	1	22uF	EMK212BBJ226MG-T	Taiyo Yuden	CAP, CERM, 22 µF, 16 V, +/- 20%, X5R, 0805	0805
C13	1	47pF	12061A470JAT2A	AVX	CAP, CERM, 47 pF, 100 V, +/- 5%, C0G/NP0, 1206	1206
C14	1	10uF	GMK316AB7106KL	Taiyo Yuden	CAP, CERM, 10 µF, 35 V,+/- 10%, X7R, 1206	1206
C18	1	1000pF	VJ1210Y102KXGAT5Z	Vishay-Vitramon	CAP, CERM, 1000 pF, 1000 V, +/- 10%, X7R, 1210	1210
C19	1	220pF	08051A221JAT2A	AVX	CAP, CERM, 220 pF, 100 V,+/- 5%, C0G/NP0, 0805	0805
C20	1	0.1uF	C0805C104K1RACTU	Kemet	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	0805
C21	1	22pF	GRM2195C2A220JZ01D	MuRata	CAP, CERM, 22 pF, 100 V,+/- 5%, C0G/NP0, 0805	0805
C22	1	1000pF	08051A102JAT2A	AVX	CAP, CERM, 1000 pF, 100 V, +/- 5%, C0G/NP0, 0805	0805
C23	1	0.1uF	C3216C0G2A104J160AC	TDK	CAP, CERM, 0.1 µF, 100 V, +/- 5%, C0G/NP0, 1206_190	1206_190
C26	1	1uF	08055C105KAT2A	AVX	CAP, CERM, 1 µF, 50 V,+/- 10%, X7R, 0805	0805
C27	1	2200pF	CC0805KRX7R9BB222	Yageo America	CAP, CERM, 2200 pF, 50 V,+/- 10%, X7R, 0805	0805
D1	1	12V	DFLZ12-7	Diodes Inc.	Diode, Zener, 12 V, 1 W, PowerDI123	PowerDI123
D2	1	100V	V12P10-M3/86A	Vishay-Semiconductor	Diode, Schottky, 100 V, 12 A, AEC-Q101, TO-277A	TO-277A
D3	1	Red	LTST-C150CKT	Lite-On	LED, Red, SMD	1206
D4, D5	2	100V	HD01-T	Diodes Inc.	Diode, Switching-Bridge, 100 V, 0.8 A, MiniDIP	MiniDIP
D6	1	58V	SMAJ58A	Diodes Inc.	Diode, TVS, Uni, 58 V, SMA	SMA
D7	1	75V	BAV99-7-F	Diodes Inc.	Diode, Switching, 75 V, 0.3 A, SOT-23	SOT-23
J1, J2	2		SS-7188V-A-NF	Stewart Connector	RJ-45, Vertical, TH	RJ-45 Jack, 8Pos Right Angle
L1	1	10uH	74477710	Würth Elektronik	Inductor, Shielded Drum Core, Metal Composite, 10 µH, 2 A, 0.045 ohm, SMD	SMD
L2	1	68uH	7447709680	Würth Elektronik	Inductor, Shielded Drum Core, Ferrite, 68 µH, 3.2 A, 0.06864 ohm, SMD	SMD
Q1	1	80 V	BCX56-16,115	Nexperia	Transistor, NPN, 80 V, 1 A, AEC-Q101, SOT-89	SOT-89
Q2	1	100V	CSD19537Q3	Texas Instruments	MOSFET, N-CH, 100 V, 50 A, DQG0008A (VSON-CLIP-8)	DQG0008A
Q9, Q10	2	80 V	MMBTA56LT1G	ON Semiconductor	Transistor, PNP, 80 V, 0.5 A, SOT-23	SOT-23
R1	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0805	0603
R2, R18, R31	3	1.00k	CRCW08051K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.125 W, 0805	0805
R3	1	49.9	ERJ-8ENF49R9V	Panasonic	RES, 49.9, 1%, 0.25 W, 1206	1206
R4, R5, R9, R10	4	75	CRCW060375R0JNEA	Vishay-Dale	RES, 75, 5%, 1/16 W, 0603	0603
R6	1	75.0k	CRCW060375K0FKEA	Vishay-Dale	RES, 75.0 k, 1%, 0.1 W, 0603	0603
R7	1	39.2k	CRCW060339K2FKEA	Vishay-Dale	RES, 39.2 k, 1%, 0.1 W, 0603	0603
R8	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R11	1	49.9	CRCW080549R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.125 W, 0805	0805
R12	1	6.2k	CRCW08056K20JNEA	Vishay-Dale	RES, 6.2 k, 5%, 0.125 W, 0805	0805
R13	1	2.0k	CRCW08052K00JNEA	Vishay-Dale	RES, 2.0 k, 5%, 0.125 W, 0805	0805

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R14	1	3.3k	CRCW08053K30JNEA	Vishay-Dale	RES, 3.3 k, 5%, 0.125 W, 0805	0805
R15	1	24.9k	CRCW060324K9FKEA	Vishay-Dale	RES, 24.9 k, 1%, 0.1 W, 0603	0603
R16	1	90.9	CRCW080590R9FKEA	Vishay-Dale	RES, 90.9, 1%, 0.125 W, 0805	0805
R17	1	0	CRCW08050000Z0EA	Vishay-Dale	RES, 0, 5%, 0.125 W, 0805	0805
R19	1	0.25	CSRN2010FKR250	Stackpole Electronics Inc	RES, 0.25, 1%, 1 W, 2010	2010
R20	1	10k	CRCW080510K0JNEA	Vishay-Dale	RES, 10 k, 5%, 0.125 W, 0805	0805
R21	1	30k	CRCW080530K0JNEA	Vishay-Dale	RES, 30 k, 5%, 0.125 W, 0805	0805
R30	1	8.87k	CRCW08058K87FKEA	Vishay-Dale	RES, 8.87 k, 1%, 0.125 W, 0805	0805
R32	1	3.92k	CRCW08053K92FKEA	Vishay-Dale	RES, 3.92 k, 1%, 0.125 W, 0805	0805
R34	1	5.1k	CRCW08055K10JNEA	Vishay-Dale	RES, 5.1 k, 5%, 0.125 W, 0805	0805
T1	1	350uH	H2019FNLT	Pulse Engineering	Transformer, 350uH, SMT	358x236x500mil
U1	1		TPS23753APW	Texas Instruments	IEEE 802.3-2005 PoE Interface and Isolated Converter Controller with Enhanced ESD Ride-Through, -40 to 125 degC, 14-pin SOP (PW14), Green (RoHS & no Sb/Br)	PW0014A
U5	1		TLV431ACDBZR	Texas Instruments	Low Voltage Adjustable Precision Shunt Regulator, 39 ppm / degC, 15 mA, 0 to 70 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated