

Variant: 001
 Generated: 11/06/2018 10:45:21 AM
 TID #: TIDA-010038



TIDA-010038 REV E1 Bill of Materials

Item	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	PCB	1		TIDA-010038	Any	Printed Circuit Board	
2	C2, C3, C11, C12, C59	5	10uF	GRM31CR61H106KA12L	MuRata	CAP, CERM, 10 uF, 50 V, +/- 10%, X5R, 1206	1206
3	C4, C10	2	820uF	UHW1V821MHD	Nichicon	CAP, AL, 820 uF, 35 V, +/- 20%, TH	10x25mm
4	C5, C6	2	150pF	GRM31A5C2J151JW01D	MuRata	CAP, CERM, 150 pF, 630 V, +/- 5%, COG/NP0, 1206	1206
5	C7, C37	2	2.2uF	GRM188Z71C225KE43	MuRata	CAP, CERM, 2.2 uF, 16 V, +/- 10%, X7R, 0603	0603
6	C8, C21	2	1uF	UMK107AB7105KA-T	Taiyo Yuden	CAP, CERM, 1 uF, 50 V, +/- 10%, X7R, 0603	0603
7	C13	1	0.022uF	B32671Z6223J189	TDK	CAP, Film, 0.022 uF, 630 V, +/- 10%, TH	13mmx4mm
8	C14	1	6800pF	GRM1882C1H682JA01	MuRata	CAP, CERM, 6800 pF, 50 V, +/- 5%, COG/NP0, 0603	0603
9	C15	1	120uF	35ZLQ120MEFC6.3X11	Rubycon	CAP, AL, 120 uF, 35 V, +/- 20%, TH	D6.3xL11mm
10	C16	1	1000pF	DE1E3KX102MA4BL01	MuRata	CAP, CERM, 2200 pF, 250 V, +/- 20%, E, Cap, 7x12x9 mm	7x12x9 mm
11	C17, C27, C61	3	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
12	C18, C22, C54, C55	4	1uF	GCM188R71C105MA64D	MuRata	CAP, CERM, 1 uF, 16 V, +/- 20%, X7R, AEC-Q200 Grade 1, 0603	0603
13	C19	1	1uF	12063C105KAT2A	AVX	CAP, CERM, 1 uF, 25 V, +/- 10%, X7R, 1206	1206
14	C23, C24, C57	3	100pF	C1608C0G1H101J080AE	TDK	CAP, CERM, 100 pF, 50 V, +/- 5%, COG/NP0, 0603	0603
15	C25	1	2.2uF	GRM188R6YA225KA12D	MuRata	CAP, CERM, 2.2 uF, 35 V, +/- 10%, X5R, 0603	0603
16	C26	1	330pF	C0603C331J5GACTU	Kemet	CAP, CERM, 330 pF, 50 V, +/- 5%, COG/NP0, 0603	0603
17	C28	1	4.7uF	GCM21BC71E475KE36L	MuRata	CAP, CERM, 4.7 uF, 25 V, +/- 10%, X7S, AEC-Q200 Grade 1, 0805	0805
18	C29	1	220pF	GRM188R71H221KA01D	MuRata	CAP, CERM, 220 pF, 50 V, +/- 10%, X7R, 0603	0603
19	C31, C34	2	0.01uF	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, 0603	0603
20	C32	1	0.047uF	GRM188R71E473KA01D	MuRata	CAP, CERM, 0.047 uF, 25 V, +/- 10%, X7R, 0603	0603
21	C33	1	2.7pF	06035A2R2CAT2A	AVX	CAP, CERM, 2.7 pF, 50 V, +/- 11%, COG/NP0, 0603	0603
22	C36	1	4700pF	06031C472KAT2A	AVX	CAP, CERM, 4700 pF, 100 V, +/- 10%, X7R, 0603	0603
23	C40, C41	2	0.47uF	890324024005	Würth Elektronik	CAP, Film, 0.47 uF, 275 V, +/- 10%, TH	15x10mm
24	C44	1	0.47uF	B32672P4474K000	TDK	CAP, Film, 0.47 uF, 450 V, +/- 10%, TH	5x10.5x18mm
25	C45	1	150uF	450US150MEFCSN25x25	Rubycon	CAP, AL, 150 uF, 450 V, +/- 20%, TH	D25xL25mm
26	C46	1	10pF	VJ0805A100JXGAT5Z	AVX	CAP, CERM, 10 pF, 100 V, +/- 5%, COG/NP0, 0805	0805
27	C47, C48, C49, C50	4	0.1uF	C1210V104KCRCTU	Kemet	CAP, CERM, 0.1 uF, 500 V, +/- 10%, X7R,	1210
28	C51	1	3900pF	GRM188R72A392KA01D	MuRata	CAP, CERM, 3900 pF, 100 V, +/- 10%, X7R, 0603	0603
29	C52	1	100pF	C1608C0G2A101F080AA	TDK	CAP, CERM, 100 pF, 100 V, +/- 1%, COG/NP0, 0603	0603
30	C53	1	0.47uF	GRM188R71E474KA12D	MuRata	CAP, CERM, 0.47 uF, 25 V, +/- 10%, X7R, 0603	0603
31	C56	1	0.033uF	GRM188R71C333KA01D	MuRata	CAP, CERM, 0.033 uF, 16 V, +/- 10%, X7R, 0603	0603
32	C58	1	1000pF	GRM188R61H102KA01D	MuRata	CAP, CERM, 1000 pF, 50 V, +/- 10%, X5R, 0603	0603
33	C60	1	2200pF	GRM188R71E222KA01D	MuRata	CAP, CERM, 2200 pF, 25 V, +/- 10%, X7R, 0603	0603
34	D1, D3, D9, D15	4		1N4148W-7-F	Diodes Inc.	Diode, Schottky, 70 V, 0.015 A, SOD-123	SOD-123
35	D2	1		PMEG10010ELRX	Nexperia	Diode, Schottky, 100 V, 2 A, AEC-Q101, SOD-123W	SOD-123W
36	D4	1		ES1JTR	SMC Diode Solutions	Diode, Superfast Rectifier, 600 V, 1 A, SMA	SMA
37	D5, D20	2		MMSZ5234B-7-F	Diodes Inc.	Diode, Zener, 6.2 V, 500 mW, SOD-123	SOD-123
38	D6	1		BAT43W	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOD-123	SOD-123
39	D7	1		BAW56-V-GS08	Vishay-Semiconductor	Diode, Switching, 70 V, 0.25 A, SOT-23	SOT-23
40	D8	1		MMSZ5251B-7-F	Diodes Inc.	Diode, Zener, 22 V, 500 mW, SOD-123	SOD-123
41	D10	1		S3JB-13-F	Diodes Inc.	Diode, Ultrafast, 600 V, 1 A, SMB	SMB
42	D11	1		GBU6J	Fairchild Semiconductor	Diode, Switching-Bridge, 600 V, 6 A, TH	GBU
43	D12	1		STTH506B-TR	STMicroelectronics	Diode, Ultrafast, 600 V, 5 A, DPAK	DPAK
44	D13, D14, D16, D17	4		MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 1 A, AEC-Q101, SMA	SMA
45	D18	1		MMSZ4690T1G	ON Semiconductor	Diode, Zener, 5.6 V, 500 mW, SOD-123	SOD-123
46	F1	1		39215000000	Littelfuse	Fuse, 5 A, 250VAC/VDC, TH	8x8.5x4mm
47	L1	1	300uH	7447060	Würth Elektronik	WE-FI Leaded Toroidal Line Choke, L = 300uH	
48	L2	1	200uH	750316570	Würth Elektronik	Inductor, 200 uH, 0.235 ohm, TH	
49	L3	1	10mH	744823210	Würth Elektronik	Coupled inductor, 10 mH, 2 A, 0.125 ohm, TH	
50	L4	1	1mH	744821201	Würth Elektronik	Coupled inductor, 1 mH, 2 A, 0.045 ohm, TH	
51	NTC1	1	10k	TSM1B103J4203R	台湾兴勤	NTC, 10k, 0603	0603
52	Q1, Q4	2		CSD19533Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 13 A, DQJ0008A (VSONP-8)	DQJ0008A
53	Q2, Q3	2		TK290P65Y,RQ	Toshiba	MOSFET, N-CH, 650 V, 11.5 A, DPAK	DPAK
54	Q5, Q7	2		BC 846PN H6327	Infineon Technologies	Transistor, NPN/PNP Pair, 65 V, 0.1 A, SOT-363	SOT-363
55	Q6	1		TK16G60W,RVQ	Toshiba	MOSFET, N-CH, 600 V, 15.8 A, DPAK	DDPAK
56	Q8	1	600V	TK290P60Y,RQ	Toshiba	MOSFET, N-CH, 600 V, 11.5 A, DPAK	DPAK
57	Q9	1	60V	2N7002-7-F	Diodes Inc.	MOSFET, N-CH, 60 V, 0.17 A, SOT-23	SOT-23
58	R1, R4, R8	3	5.10Meg	KTR18EZPF5104	Rohm	RES, 5.10 M, 1%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
59	R9, R23, R26	3	2.00	CRCW06032R00FKEA	Vishay-Dale	RES, 2.00, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
60	R3, R15, R49	3	5.60	RC0805FR-075R6L	Yageo America	RES, 5.60, 1%, 0.125 W, 0805	0805
61	R5, R20, R51	3	1.00	RC0805FR-071RL	Yageo America	RES, 1.00, 1%, 0.125 W, 0805	0805
62	R6, R18, R21, R29, R36, R44, R81	7	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
63	R7	1	910	RC0603FR-07910RL	Yageo	RES, 910, 1%, 0.1 W, 0603	0603
64	R10, R11, R35	3	0	RMCF0603ZT0R00	Stackpole Electronics Inc	RES, 0, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
65	R12	1	270k	CRCW0603270KJNEA	Vishay-Dale	RES, 270 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
66	R13	1	300k	CRCW0603300KJNEA	Vishay-Dale	RES, 300 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
67	R17	1	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
68	R19, R22	2	0.008	ERJ-M1WTF8M0U	Panasonic	RES, 0.008, 1%, 1 W, 2512	2512

69	R24	1	510	RC0603FR-07510RL	Yageo	RES, 510, 1%, 0.1 W, 0603	0603
70	R25	1	1.50k	CRCW06031K50FKEA	Vishay-Dale	RES, 1.50 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
71	R27	1	6.2k	CRCW06036K20JNEA	Vishay-Dale	RES, 6.2 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
72	R28	1	2.7k	CRCW06032K70JNEA	Vishay-Dale	RES, 2.7 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
73	R30, R67, R76	3	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
74	R32	1	8.2k	CRCW06038K20JNEA	Vishay-Dale	RES, 8.2 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
75	R33, R34	2	10.2	CRCW060310R2FKEA	Vishay-Dale	RES, 10.2, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
76	R37	1	2.0k	CRCW06032K00JNEA	Vishay-Dale	RES, 2.0 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
77	R38	1	402k	CRCW0603402KFKFA	Vishay-Dale	RES, 402 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
78	R39	1	24.0k	RC0603FR-0724KL	Yageo	RES, 24.0 k, 1%, 0.1 W, 0603	0603
79	R40	1	56.2k	CRCW060356K2FKEA	Vishay-Dale	RES, 56.2 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
80	R41, R78	2	5.11k	CRCW06035K11FKEA	Vishay-Dale	RES, 5.11 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
81	R42	1	5k	PV37W502C01B00	Bourns	Trimmer Potentiometer, Lead Sealed Type Multiturn PV37 Series, TH	6.71x4.5mm
82	R43	1	3.65k	CRCW06033K65FKEA	Vishay-Dale	RES, 3.65 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
83	R45, R46, R47, R48, R50, R53	6	3.3Meg	CRCW12063M30JNEA	Vishay-Dale	RES, 3.3 M, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
84	R52	1	24.3k	RC0603FR-0724K3L	Yageo	RES, 24.3 k, 1%, 0.1 W, 0603	0603
85	R54, R60, R65	3	1.62k	RC1206FR-071K62L	Yageo America	RES, 1.62 k, 1%, 0.25 W, 1206	1206
86	R55	1	2.00k	RC0603FR-072KL	Yageo	RES, 2.00 k, 1%, 0.1 W, 0603	0603
87	R56, R57	2	0.12	CSR1206FTR120	Stackpole Electronics Inc	RES, 0.12, 1%, 0.5 W, 1206	1206
88	R58, R59, R63, R64, R80	5	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
89	R61, R70	2	0	CRCW12060000Z0EA	Vishay-Dale	RES, 0, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
90	R62, R66, R68	3	3.0Meg	CRCW12063M00JNEA	Vishay-Dale	RES, 3.0 M, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
91	R69, R73	2	130k	CRCW0603130KFKEA	Vishay-Dale	RES, 130 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
92		1	2.05	RC1206FR-072R05L	Yageo America	RES, 2.05, 1%, 0.25 W, 1206	1206
93	R71	1	82.0k	ERJ3EKF8202V	Panasonic	RES, 82.0 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
94	R72	1	182k	CRCW0603182KFKEA	Vishay-Dale	RES, 182 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
95	R74	1	120k	CRCW0603120KJNEA	Vishay-Dale	RES, 120 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
96	R75, R77, R79	3	51.1k	CRCW060351K1FKEA	Vishay-Dale	RES, 51.1 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
97	RT1	1	10	B57236S0100M000	TDK	Thermistor NTC, 10 ohm, 20%, Disc_11.5mmx6mm	Disc_11.5mmx6mm
98	RV1	1	275V	S10K275E2	TDK	Varistor 275V RMS 10MM Radial, TH	10mm Radial
99	T1	1	408uH	750344060	Würth Elektronik	WE-LLC Resonant Converter, size ER28, 408uH, 34:4:3, 150W	
100	U1	1		PUCC24624D	Texas Instruments	High frequency Dual Synchronous Rectifier Controller for LLC Converter	D0008A_N
101	U2	1		LM317LCPK	Texas Instruments	3-Terminal Adjustable Regulator, PK0003A (SOT-3)	PK0003A
102	U3	1		UCC25630-1DDBR	Texas Instruments	Enhanced LLC Resonant Controller with Driver, DDB0014A (SOIC-14)	DDB0014A
103	U4	1		INA180A3IDBV	Texas Instruments	Low- and High-Side Measurement, Multichannel, Voltage Output, Current-Sense Amplifier, DBV0005A (SOT-5)	DBV0005A
104	U5	1		VO618A	Vishay-Semiconductor	Optocoupler, 5.3 kV, 50-600% CTR, TH	DIP, 4-Leads, Body 6.86x4.83mm, Pitch 2.54mm
105	U6	1		TL103WAID	Texas Instruments	Dual Operational Amplifier with Internal Reference, 3 to 32 V, -40 to 105 degC, 8-pin SOIC (D8), Green (RoHS & no Sb/Br)	D0008A
106	U7	1		UCC28056DBV	Texas Instruments	6-Pin Single-Phase Transition-Mode PFC Controller, DBV0006A (SOT-23-6)	DBV0006A
107	U8	1		LM258D	Texas Instruments	Dual Operational Amplifier, D0008A (SOIC-8)	D0008A

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2019, Texas Instruments Incorporated