

Bill of Materials

TI DESIGNS
TIDM-02000

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
1	1	C:C1	22uF	CAP CER 22UF 25V 10% X5R 1206	Murata	GRM31CR61E226KE15L			
2	3	C:C2-4	330uF	CAP ALUM 330UF 20% 25V RADIAL	Panasonic	ECA-1EM331			
3	1	C:C5	10uF	CAP CER 10UF 25V 10% X7R 1206	Taiyo Yuden	TMK316B7106KL-TD			
4	1	C:C6	100nF	CAP CER 0.1UF 25V 10% X7R 0805	Kemet	C0805C104K3RACTU			
5	1	C:C7	4.7uF	CAP CER 4.7UF 25V 10% X7R 0805	Taiyo Yuden	TMK212AB7475KG-T			
6	1	C:JP1	CONN_PWR_JACK_2.1	CONN PWR JACK 2.1X5.5MM HIGH CUR	CUI Inc.	PJ-002AH			
7	6	C:JPG1 E:J2-3 E:JPG1 F:JP	HEADER_1X2_100	CONN HEADER 50POS .100" SGL GOLD	Samtec Inc.	Standard	TSW-150-07-L-S		
8	2	C:LD1 E:LD1	LED_GREEN	LED GREEN 0805 SMD, Diffused	Standard	Standard			
9	1	C:M1	PTH08080WAH	MODULE PIP .9-5.5V 2.25A HORZ TH	Texas Instruments Inc.	PTH08080WAH			
10	1	C:R1	330ohm	RES 1/8W 1% 0805 SMD	Standard	Standard			
11	1	C:R2	470ohm	RES 1/8W 1% 0805 SMD	Standard	Standard			
12	1	C:SW1	TOGGLE_SWITCH	SWITCH TOGGLE SPDT 5A 120V	C&K Components	7101SD9CQE			
13	1	C:U1	IC_LDO	IC LDO REG 3.3V 500MA SOT223-6	Texas Instruments Inc.	TPS79533DCQR			
14	1	C1	220nF	CAP CER 0.22UF 100V 10% X7R 1206	AVX Corporation	12061C224KAZ2A			
15	1	C13	1000pF	CAP CER 1000PF 500V 10% RADIA	Vishay BC	D102K25Y5PL63L6R			
16	6	C14-16 C18 C27 C29	1 uF	CAP CER 1UF 50V 10% X7R 0805	Kemet	C0805C105K5RACTU			
17	1	C17	6.8nF	CAP CER 6800PF 100V 10% X7R 0805	AVX Corporation	08051C682KAT2A			
18	1	C19	22uF	CAP ALUM 22UF 20% 35V RADIAL	Panasonic	ECA-1VM220			
19	1	C2	0.47uF	CAP FILM 0.47UF 20% 300VAC RAD	Panasonic	ECQ-U3A474MG			
20	2	C20-21	1uF	CAP CER 1UF 100V 10% X7R 1210	TDK Corporation	C3225X7R2A105K200AA			
21	3	C22 C26 C33	3.3nF	CAP CER 3300PF 100V 10% X7R 0805	AVX Corporation	08051C332KAT2A			
22	1	C23	330pF	CAP CER 330PF 50V 10% X7R 0805	Kemet	C0805C331K5RACTU			
23	1	C24	220pF	CAP CER 220PF 50V 10% X7R 0603	Kemet	C0603C221K5RACTU			
24	16	C25, C31, E:C3-4, E:C8-19	100nF	CAP CER 0.1UF 16V 10% X7R 0603	AVX Corporation	0603YC104KAT2A			
25	1	C3	330uF	CAP ALUM 330UF 20% 450V SNAP	Panasonic	EET-HC2W331EA			
26	1	C30	0.1uF	CAP CER 0.1UF 200V 10% X7R 2220	Kemet	C2220X104K2RAC7800			
27	3	C34 F:C2-3	1uF	CAP CER 1UF 16V 10% X7R 0805	Kemet	C0805C105K4RACTU			
28	5	C4-8	1500uF	CAP ALUM 1500UF 20% 16V RADIAL	United Chemi-Con	EKY-160ELL152MJ30S			
29	5	C9-12 C28	1uF	CAP CER 1UF 25V 10% X7R 1206	Kemet	C1206C105K3RACTU			
30	7	D1 D14-19	D-BAT54	DIODE SCHOTTKY 30V 200MA SOT23-3	Diodes Incorporated	BAT54-7-F			
31	4	D7, D8, D12, D13	D-ZENER	DIODE ZENER 12V 500MW SOD123	ON Semiconductor	MMSZ5242BT1G			
32	3	D20 D23-24	D-SCHOTTKY	DIODE SCHOTTKY 60V 3A DO214AB	Vishay Semiconductor	SS36-E3/57T			
33	2	D21-22	D-ARRAY	DIODE ARRAY SCHOTTKY 30V SOT23-3	Diodes Incorporated	BAT54STA			
34	4	D2-3 D9-10	D-GEN	DIODE GEN PURP 100V 300MA SOD123	Diodes Incorporated	1N4148W-7-F			
35	4	D25-D28	D-SCHOTTKY	DIODE SCHOTTKY 600V 10A TO220-2	Cree Inc.	C3D10060A			
36	2	D4 D6	D-GEN	DIODE GEN PURP 100V 3A SMB	Diodes Incorporated	ES3BB-13-F			
37	2	D5 D11	D-GEN	DIODE GEN PURP 600V 3A SMC	ON Semiconductor	MURS360T3G			
38	1	E:C1	0.1uF	CAP CER 0.1UF 100V 20% AXIAL	AVX Corporation	SA111E104MAR			
39	3	E:C2 E:C5-6	1uF	CAP CER 1UF 16V 10% X7R 0603	TDK Corporation	C1608X7R1C105K080AC			
40	1	E:C7	2.2uF	CAP CER 2.2UF 16V 10% X5R 0603	Murata Electronics Nor	GRM188R61C225KE15D			
41	1	E:DA1	D-ARRAY	DIODE ARRAY GP 75V 150MA SOT363	Diodes Incorporated	BAW567DW-7-F			
42	1	E:J1	HEADER_7X2_100	Header, Male, 7x2-pin, 100mil spacing	Standard	Standard			

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
43	1	E:JP1	CONN_USB_B	Connector Receptacle USB TypeB 2.0 4 Position Thru Hole	Mill-Max Manufacturing	897-43-004-90-000000			
44	2	E:L1-2	22uH	FIXED IND 22UH 13MA 350 MOHM SMD	Murata Electronics Nor	LQM21FN220N00L			
45	1	E:R1	470ohm	RES 1/10W 1% 0603 SMD	Standard	Standard			
46	1	E:R2	1K	RES 1/10W 1% 0603 SMD	Standard	Standard			
47	1	E:R3	10K	RES 1/10W 1% 0603 SMD	Standard	Standard			
48	1	E:R4	1M	RES 1/10W 1% 0603 SMD	Standard	Standard			
49	3	E:R5 E:R10-11	2K2	RES 1/10W 1% 0603 SMD	Standard	Standard			
50	1	E:R6	47K	RES 1/10W 1% 0603 SMD	Standard	Standard			
51	2	E:R7 E:R9	27ohm	RES 1/10W 1% 0603 SMD	Standard	Standard			
52	1	E:R8	680ohm	RES SMD 680 OHM 1% 1/10W 0603	Panasonic	ERJ-3EKF6800V			
53	1	E:U1	IC_LOGIC	IC D-TYPE POS TRG SNGL SM8	Texas Instruments Inc.	SN74LVC2G74DCTR			
54	1	E:U2	IC_MEM	IC EEPROM 1KBIT 2MHZ SOT23-6	Microchip Technology	93LC46BT-I/OT			
55	1	E:U3	IC_LDO	IC REG LDO 3.3V 0.2A SOT23-5	Texas Instruments Inc.	TPS73033DBVR			
56	1	E:U4	IC_ISO	DGTL ISO 2.5KV GEN PURP 16SOIC	Texas Instruments Inc.	ISO7242CDW			
57	1	E:U5	IC_COMM	IC USB FS DUAL UART/FIFO 48-LQFP	FTDI, Future Technolog	FT232D-REEL			
58	1	E:U6	IC_ISO	DGTL ISO 2.5KV GEN PURP 16SOIC	Texas Instruments Inc.	ISO7240CDW			
59	1	E:X1	OSC_6MHz	CER RESONATOR 6.00MHZ SMD	Murata Electronics Nor	CSTCR6M00G53Z-R0			
60	1	F:C1	0.1uF	CAP CER 0.1UF 50V 10% X7R 0805	Kemet	C0805C104K5RACTU			
61	1	F:J1	CON100-3	Header, Male, 3x1-pin, 100mil spacing	Standard	Standard			
62	2	F:R1 F:R3	10ohm	RES 1/8W 1% 0805 SMD	Standard	Standard			
63	6	F:R2 R23 R32 R34 R50-51	1K	RES 1/8W 1% 0805 SMD	Standard	Standard			
64	1	F:U1	IC_ISO_CAN	IC TXRX CAN 5V 8SOP	Texas Instruments Inc.	ISO1050DUBR			
65	1	F:U2	DCH01_4PIN	Isolated DC/DC Converters Mini 1W 3kVDC Isolated	Texas Instruments Inc.	DCH010505SN7			
66	1	F1	FUSE_CLIP-250	Fuse Clip, 5mm x 20mm	Wickmann	0100056H			
67	1	H2	HEADER_DIMM100	DIMM Connectors VERT DIMM SKT 100P	Molex	87630-1001			
68	1	HS	HEATSINK	HEATSINK, 0.65 C/W, ALUMINIUM ALLOY	H S MARSTON	150CN-02000-A-200			
69		HS Assembly	HS_Socket_screw	5/16 Socket head cap screw Std, 18-8 SS, 4-40x5/16	Grainger	6XA42	U51050.011.0031		
70		HS Assembly	HS_Standoff_screw	Metric Machine Screw Pan Phillips M3	B&F Fastener Supply	MPMS 003 0012 PH			
71		HS Assembly	HS_Standoffs	Round Spacer #4 Nylon 1/4"	Bivar Inc.	9911-250			
72	23	J18, J2-9, J1, J11-17, J19-20	HEADER_1X2_100	Header, Male, 1x2-pin, 100mil spacing	Samtec Inc.	Standard	TSW-150-07-L-S		
73	1	JP1	JMP	JUMPER WIRE 0.2" LONG PKG OF 200	3M	923345-02-C			
74	1	L1	4.7uH	Inductor, 4.7uH	Vitec Electronics Corp	6193R			
75	1	L2	39uH	Inductor, 39uH	Vitec Electronics Corp	6194R			
76	2	M1-2	TBLK_15A_2X5.1MM,ED120/2	TERMINAL BLOCK 5.08MM VERT 2POS	On Shore Technology I	ED120/2DS			
77	1	M3	AUX-SUPPLY	Aux Supply 5W - 400Vin to 12V	Texas Instruments Inc.	PR798			
78	2	M4-5	CONN_LUG	Lug, Solderless, #2 - #8 AWG, 1/4", Copper	ILSCO	SLU-70			
79	4	Q1-4	FET_650V	MOSFET N-CH 650V 16A TO220-3	Infineon Technologies	IPP60R199CP			
80	3	Q5-7	FET_60V	MOSFET N-CH 60V 80A TO-220AB	Fairchild Semiconduct	FDPO50AN06A0			
81	1	R1	48.7ohm	RES SMD 48.7 OHM 1% 1/8W 0805	Panasonic	ERJ-6ENF48R7V			
82	1	R11	49.9ohm	Resistor, Chip, 1/10W, 1%	Standard	Standard			
83	4	R18-19 R35 R44	3.01ohm	RES SMD 3.01 OHM 1% 1/8W 0805	Yageo	RC0805FR-073R01L			
84	14	R2 R7 R10 R15-16 R28-31	10.0K	Resistor, Chip, 1/10W, 1%	Standard	Standard			
85	1	R20	2.37K	RES 1/8W 1% 0805 SMD	Standard	Standard			
86	1	R21	9.09K	RES 1/8W 1% 0805 SMD	Standard	Standard			
87	2	R24 R49	R0805,DNP	RES 1/8W 1% 0805 SMD	Standard	Standard			
88	2	R25-26	499ohm	RES SMD 499 OHM 1% 1/4W 1206	Panasonic	ERJ-8ENF4990V			
89	1	R27	0.0005ohm	RESISTOR CS 0.0005 3W 2% 4020	Rhopoint/Isotek	BVS-M-R0005			
90	5	R3 R5 R12-13 R41	3.01ohm	Resistor, Chip, 1/10W, 1%	Standard	Standard			
91	1	R36	10.0K	RES SMD 10K OHM 1% 1/8W 0805	Vishay Dale	CRCW080510K0FKEA			
92	1	R37	1K	RES 1/10W 1% 0603 SMD	Standard	Standard			
93	1	R38	220ohm	RES 1/10W 1% 0603 SMD	Standard	Standard			
94	1	R39	47K	RES 1/10W 1% 0603 SMD	Standard	Standard			

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
95	3	R4 R14 R17	1.00M	RES 1/8W 1% 0805 SMD	Standard	Standard			
96	1	R40	4.7ohm	RES 1/8W 5% 0805 SMD	Standard	Standard			
97	1	R47	200ohm	RES 1/8W 1% 0805 SMD	Standard	Standard			
98	1	R48	0ohm	RES 1/8W 1% 0805 SMD	Standard	Standard			
99	1	R6, R52	100K	RES SMD 100K OHM 1% 1W 2512	Panasonic	ERJ-1TNF1003U			
100	2	R8-9	1.00K	Res, Power Metal Strip, 2W, ±5%	Standard	Standard			
101	1	T1	XFMR_PE63587	1:100 Current Transformer, Current Sense	Pulse	PE-63587NL			
102	1	T2	P6524_A	12:1, Center-tapped, Main Power Transformer	MPS	P6524_A			
103	2	T3-4	XFMR_56PR3362	Transformer, Gate Drive	Vitec Electronics	56PR3362			
104	11	TP3-13	TP	PIN INBOARD .042" HOLE 1000/PKG	Vector Electronics	K24A/M			
105	4	U1-4	UCC27524A	IC, High Speed 2-ch Low Side driver, 8SOIC	Texas Instruments Inc.	UCC27524AQDRQ1			
106	1	U5	OPA345	IC SGL-SUPPLY OPAMP, 3MHz, SOT-23-5	Texas Instruments Inc.	OPA345NA/250			
107	1	U6	D-ARRAY	TVS DIODE 5VWM 16.6VC 6TSOP	ON Semiconductor	NUP4201MR6T1G			

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2020, Texas Instruments Incorporated