

Filename: IPC388BOM3files.xlsx  
 Variant: 001  
 Generated: 9/20/2013 11:03:14 AM  
 SVN path: \$URL:  
 SVN rev: \$Rev: 5

\$

DM388 IP-CAMERA

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
C1, C2, C6, C7, C24, C25, C26, C27, C28, C29, C30, C31, C32, C33, C34, C35, C36, C37, C38, C39, C40, C41, C42, C43, C44, C45, C46, C47, C48, C49, C50, C51, C52, C53, C54, C55, C56, C57, C58, C59, C60, C61, C62, C63, C64, C65, C66, C68, C69, C91, C92, C198, C200, C208, C209, C212, C213, C214, C215, C216, C217, C218, C219, C220, C221, C232, C233, C238, C242, C243, C248, C249, C250, C256, C261, C262, C263, C264, C266, C270, C271, C272, C273, C274, C282, C286, C287, C288, C296, C297, C298, C302, C303, C304, C310, C311, C312, C313, C314, C315, C316, C317, C318, C319, C320, C321, C329, C330, C331, C332, C333, C334, C335, C336, C337, C338, C339, C340, C341, C342, C343, C344, C345, C346, C347, C348, C349, C350, C351, C352, C353, C354, C355, C356, C357, C358, C359, C360, C361, C362, C363, C372, C373	143	0.1uF	Printed Circuit Board CAP, 0.1uF, 25V, 10%, X5R 0201	0201	SAT0008 C0603X5R1E104K030BB	Any TDK Corporation		
C3, C4, C5	3	0.01uF	CAP, 0.01uF, 25V, 10%, X5R 0201	0201	GRM033R61E103KA12D	Murata Electronics		
C8, C9, C202, C203, C204, C205, C206, C207	8	1uF	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	0402	GRM155R61A105KE15D	MuRata		
C10, C11, C12, C13, C14, C15, C16, C17, C18, C19, C20, C21, C23, C70, C76, C78, C80, C82	18	0.1uF	CAP, CERM, 0.1uF, 10V, +/-10%, X5R, 0402	0402	C1005X5R1A104K	TDK		
C22, C85, C210, C246	4	10uF	CAP, CERM, 10uF, 6.3V, +/-20%, X5R, 0603	0603	C0603C106M9PACTU	Kemet		
C69	1	680pF	CAP, CERM, 680pF, 25V, +/-5%, C0G/NP0, 0402	0402	C1005C0G1E681J	TDK		
C75	1	10uF	CAP, CERM, 10uF, 10V, +/-20%, X5R, 1206	1206	C3216X5R1A106M	TDK		
C79	1	1000pF	CAP, CERM, 1000pF, 50V, +/-10%, X5R, 0402	0402	GRM155R61H102KA01D	MuRata		
C81, C82, C83, C84	4	22uF	CAP, CERM, 22uF, 6.3V, +/-20%, X5R, 0805	0805	C2012X5R0J226M	TDK		
C196, C197, C199, C201	4	18pF	CAP, CERM, 18pF, 50V, +/-5%, C0G/NP0, 0402	0402	GRM1555C1H180JA01D	MuRata		
C211, C247, C268, C269, C292, C293, C294, C295, C308, C309, C328, C374	12	22uF	CAP, CERM, 22uF, 10V, +/-20%, X5R, 0805	0805	LMK212BJ226MG-T	Taiyo Yuden		
C222, C223, C224, C225, C226, C227, C228, C229, C234, C235, C239, C244, C245, C251, C252, C253, C257, C260, C265, C267, C275, C276, C277, C278, C279, C283, C289, C290, C291, C299, C300, C301, C305, C306, C307, C322, C323, C324, C325, C326, C327	41	1nF	CAP, 1000pF, 25V, 10%, X5R 0201	0201	C0603X5R1E102K030BA	TDK Corporation		
C230, C231, C236, C237, C240, C241, C254, C255, C258, C259, C280, C281, C284, C285	14	2.2uF	CAP, CERM, 2.2uF, 10V, +/-10%, X5R, 0603	0603	GRM188R61A225KE34D	MuRata		
C364, C365, C366, C367, C369, C371	6	22uF	CAP, CERM, 22uF, 6.3V, +/-10%, X5R, 0805	0805	JMK212BJ226KG-T	Taiyo Yuden		
C368	1	100uF	CAP, TA, 100uF, 6.3V, +/-20%, 0.7 ohm, SMD	3528-21	T495B107M006A7E700	Kemet		
C370	1	0.22uF	CAP, CERM, 0.22uF, 10V, +/-10%, X5R, 0402	0402	GRM155R61A224KE19D	MuRata		
FID1, FID2, FID3, FID4, FID5, FID6	6		Fiducial mark. There is nothing to buy or mount.	Fiducial		N/A		
J1, J2	2		FFC/FPC, 36Pos, Stright, Vertical, 0.5mm, Connector			3-1734742-6	TE Connectivity	
J3	1		FFC/FPC Connector, 16 Pin Right Angle, 0.5mm, SMT			54548-1671	Molex	
JSUB1, JSUB2	2		Female Dual Row Header, Board-to-Board, 72Pos, 1.27x1.27mm, SMT Connector, Alignment Holes			CLP-136-02-L-D-A	Samtec Inc	
L2	1		FILTER CHIP 75 OHM 3A 1806			BLM41PG750SN1L	Murata Electronics North America	
L3, L4, L5, L6, L7, L8, L9, L10, L11	9		INDUCTOR 2.2UH 160MA 20% 0603			GLFR1608T2R2M-LR	TDK Corporation	
L12	1		INDUCTOR 1.0UH 230MA 20% 0603			GLFR1608T1R0M-LR	TDK Corporation	
L13	1	22uH	Inductor, Shielded Drum Core, Ferrite, 22uH, 0.7A, 0.16 ohm, SMD	MSS5131		MSS5131-223MLB	Colcraft	
MH1, MH2, MH3, MH4	4		Mounting Hole, 3mm Thought Hole					
R1, R2, R3, R4, R5, R6, R7, R8, R9, R11, R19, R21, R29, R30, R31, R32, R33, R34, R35, R36, R37, R38, R39, R40, R41, R43, R82, R84, R85, R86, R87, R88, R89, R90, R91, R92, R93, R94, R95, R96, R97, R98, R99, R100, R101, R103, R104, R105, R106, R107, R108, R109, R110, R111, R112, R113, R114, R115, R116, R117, R118, R119, R120, R121, R122, R159, R160, R163, R164, R185, R187, R188, R189, R205	74	22	RES, 22 ohm, 1%, 0.05W, 0201	0201	CRCW020122R0FNED	Vishay-Dale		
R42, R44, R46, R52, R58, R68, R69, R71, R72, R74, R75, R76, R77, R78, R79, R80, R81, R129, R193, R199, R202, R207, R211	23	10k0	RES, 10k ohm, 1%, 0.05W, 0201	0201	CRCW020110K0FKED	Vishay-Dale		
R45, R47, R48, R51, R56	5	1k0	RES, 1.0k ohm, 1%, 0.05W, 0201	0201	CRCW02011K00FKED	Vishay-Dale		
R83, R102, R161, R162, R176, R177, R182, R194, R195, R204	10	0	RES, 0 ohm, jumper, 0.05W, 0201	0201	CRCW02010000Z0ED	Vishay-Dale		
R124, R125, R131, R132	4	49.9	RES, 49.9 ohm, 1%, 0.063W, 0402	0402	CRCW04024999FKED	Vishay-Dale		
R133, R134	2	240	RES, 240 ohm, 5%, 0.063W, 0402	0402	CRCW0402240RJNED	Vishay-Dale		
R157, R158, R178, R179, R180, R181, R196	7	2.2k	RES, 2.2k ohm, 1%, 0.05W, 0201	0201	CRCW02012K20FKED	Vishay-Dale		
R166	1	124	RES, 124 ohm, 1%, 0.063W, 0402	0402	CRCW0402124RFKED	Vishay-Dale		
R169, R191	2	10k	RES, 10k ohm, 5%, 0.063W, 0402	0402	CRCW040210K0JNED	Vishay-Dale		
R169	1	22	RES, 22 ohm, 5%, 0.063W, 0402	0402	CRCW040222R0JNED	Vishay-Dale		
R183	1	1.07k	RES, 1.07k ohm, 1%, 0.063W, 0402	0402	CRCW04021K07FKED	Vishay-Dale		
R184	1	2.7k	RES, 2.7k ohm, 5%, 0.063W, 0402	0402	CRCW04022K70JNED	Vishay-Dale		
R186	1	4.7k	RES, 4.7k ohm, 5%, 0.063W, 0402	0402	CRCW04024K70JNED	Vishay-Dale		
R197	1	15k	RES, 15k ohm, 5%, 0.1W, 0603	0603	CRCW060315K0JNEA	Vishay-Dale		
R198	1	54.9k	RES, 54.9k ohm, 1%, 0.1W, 0603	0603	CRCW060354K9FKEA	Vishay-Dale		
R208, R209	2	0	RES, 0 ohm, 5%, 0.063W, 0402	0402	CRCW04020000Z0ED	Vishay-Dale		
R210, R212	2	47k	RES, 47k ohm, 5%, 0.063W, 0402	0402	CRCW040247K0JNED	Vishay-Dale		
R213	1	2.21k	RES, 2.21k ohm, 1%, 0.063W, 0402	0402	CRCW04022K21FKED	Vishay-Dale		
RA1, RA2, RA3, RA4, RA5, RA6	6		Resistor Array, 51 Ohm, 25V, 5%, 0402 Array			741C083510JP	CTS Electronic Components	

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
TP1, TP2, TP3, TP4, TP5, TP8, TP10, TP11, TP12, TP13, TP14, TP15, TP16, TP17, TP18, TP19, TP20, TP21, TP22, TP23, TP24, TP25, TP26, TP27, TP28, TP29, TP30, TP31, TP32, TP33, TP34, TP35, TP36, TP37, TP38, TP39, TP40, TP41, TP42, TP43, TP44, TP45, TP46, TP47, TP48, TP49, TP50, TP51, TP52, TP_DDR0_A0, TP_DDR0_A1, TP_DDR0_A2, TP_DDR0_A3, TP_DDR0_A4, TP_DDR0_A5, TP_DDR0_A6, TP_DDR0_A7, TP_DDR0_A8, TP_DDR0_A9, TP_DDR0_A10, TP_DDR0_A11, TP_DDR0_A12, TP_DDR0_A13, TP_DDR0_A14, TP_DDR0_BA0, TP_DDR0_BA1, TP_DDR0_BA2, TP_DDR0_CASN1, TP_DDR0_CKE1, TP_DDR0_CLK0N1, TP_DDR0_CLK1, TP_DDR0_CSN1, TP_DDR0_ODT1, TP_DDR0_RASN1, TP_DDR0_WEN1, TP_DDR1_A0, TP_DDR1_A1, TP_DDR1_A2, TP_DDR1_A3, TP_DDR1_A4, TP_DDR1_A5, TP_DDR1_A6, TP_DDR1_A7, TP_DDR1_A8, TP_DDR1_A9, TP_DDR1_A10, TP_DDR1_A11, TP_DDR1_A12, TP_DDR1_A13, TP_DDR1_A14, TP_DDR1_BA0, TP_DDR1_BA1, TP_DDR1_BA2, TP_DDR1_CASN1, TP_DDR1_CKE1, TP_DDR1_CLK0N1, TP_DDR1_CLK1, TP_DDR1_CSN1, TP_DDR1_ODT1, TP_DDR1_RASN1, TP_DDR1_WEN1	101		1mm Thru-hole Testpoint		TESTPOINT			
U1	1		DaVinci Digital Media Processor		TMS320DM385AAR11F	Texas Instruments		
U2	1		OSC MEMS 24.576 MHz 1.8V SMD		TC-24.576MDD-T	TXC Corp		
U3	1		NAND FLASH,2GBit, 63 VFBGA		MT29F2G16ABBEAH4:E	Micron Technology Inc		
U4	1		SINGLE POSITIVE AND GATE SC-70		SN74LVC1G08-DCKR	Texas Instruments		
U5, U6	2		4Gbit DDR3L SDRAM 128Mx16		K4B4G1646B-HYK0	Samsung		
U16	1		IC VOLT SUPERVISOR 0.9V SOT23-6		TPS3808G09DBV	Texas Instruments		
U17	1		IC BUS TRANSCVR TRI-ST 2B 8VSSOP	8-VFSOP (0.091", 2.30mm Width)	SN74AVC2T45DCUR	Texas Instruments		
U19	1		IC REG BUCK SYNC ADJ 3A 8-SO	8-SOIC (0.154", 3.90mm Width) Exposed Pad	TPS5432DDAR	Texas Instruments		
U20	1		IC REG SINK/SOURCE DDR 10SON		TPS51206DSQR	Texas Instruments		
U21	1		IC VOLT SUPERVISOR 1.2V SOT23-6		TPS3808G12DBV	Texas Instruments		
Y1	1		Crystal Resonator 20.000MHz 10pF SMD		7M-20.000MEEQ-T	TXC Corporation		
Y2	1		Crystal Resonator 22.579MHz 8pF SMD		CX3225GB22579D0HEQ Z1	AVX Corporation		
C182, C183, C379	0	0.1uF	CAP, CERM, 0.1uF, 10V, +/-10%, X5R, 0402	0402	C1005X5R1A104K	TDK		
C378	0	1000pF	CAP, CERM, 1000pF, 25V, +/-10%, X5R, 0402	0402	GRM155R61E102KA01D	MuRata		
C380, C381	0	1uF	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0603	0603	C0603C105K8PACTU	Kemet		
D1	0		IC VREF SHUNT PREC ADJ SOT-23-3	TO-236-3, SC-59, SOT-23-3	TLV431ACDBZR	Texas Instruments		
R49, R50, R53, R54, R57, R59, R60, R61, R62, R63, R64, R65	0	1k0	RES, 1.0k ohm, 1%, 0.05W, 0201	0201	CRCW02011K00FKED	Vishay-Dale		
R55, R192	0	0	RES, 0 ohm, jumper, 0.05W, 0201	0201	CRCW02010000Z0ED	Vishay-Dale		
R66, R67, R70, R73, R203	0	10k0	RES, 10k ohm, 1%, 0.05W, 0201	0201	CRCW020110K0FKED	Vishay-Dale		
R167, R170	0	10k	RES, 10k ohm, 5%, 0.063W, 0402	0402	CRCW040210K0JNED	Vishay-Dale		
R171	0	1.00k	RES, 1.00k ohm, 1%, 0.063W, 0402	0402	CRCW04021K00FKED	Vishay-Dale		
R172	0	7.50k	RES, 7.50k ohm, 1%, 0.063W, 0402	0402	CRCW04027K50FKED	Vishay-Dale		
R173, R175, R200, R201	0	0	RES, 0 ohm, 5%, 0.063W, 0402	0402	CRCW04020000Z0ED	Vishay-Dale		
R174	0	4.99k	RES, 4.99k ohm, 1%, 0.063W, 0402	0402	CRCW04024K99FKED	Vishay-Dale		
R206	0	22	RES, 22 ohm, 1%, 0.05W, 0201	0201	CRCW020122R0FNED	Vishay-Dale		
U18	0		IC REG LDO 1.1V .15A SC70-5		TPS71711DCKR	Texas Instruments		

Notes:

Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.