

## PMP9656 REV B Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB1	1		PMP9656	Any	Printed Circuit Board	
C1, C15, C18, C19, C20, C28	6	0.1uF	C1005X7R1H104M	TDK	CAP, CERM, 0.1uF, 50V, +/-20%, C0G/NP0, 0402	0402
C2	1	1000pF	STD	STD	CAP, CERM, 1000pF, 3kV, 1808	1808
C3, C4, C5, C6, C7, C8	6	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2uF, 100V, +/-10%, X7R, 1210	1210
C9	1	330uF	16SVP330M	Sanyo	CAP, OS-CON, 330uF, 16V, +/-20%, 0.016 ohm, 10x10.3 SMD	10x10.3
C10, C11, C12, C13	4	22uF	GRM32ER61E226KE15L	MuRata	CAP, CERM, 22uF, 25V, +/-10%, X5R, 1210	1210
C14	1	0.1uF	C3216X7R2E104K	TDK	CAP, CERM, 0.1uF, 250V, +/-10%, X7R, 1206	1206
C16	1	0.047uF	C2012X7R2A473K	TDK	CAP, CERM, 0.047uF, 100V, +/-10%, X7R, 0805	0805
C21	1	220uF	EEE-FK1C221XP	Panasonic	CAP, AL, 220uF, 16V, +/-20%, 0.34 ohm, SMD	SMT Radial D8
C22	1	100pF	CC0402KRX7R9BB101	Yageo America	CAP, CERM, 100pF, 50V, +/-10%, X7R, 0402	0402
C23	1	0.22uF	GRM155R61A224KE19D	MuRata	CAP, CERM, 0.22uF, 10V, +/-10%, X5R, 0402	0402
C24, C26, C30, C31, R11, R21, R25, R27	8	DNP	N/A	N/A	Do Not Populate	0402
C25	1	0.047uF	GRM155R71E473KA88D	MuRata	CAP, CERM, 0.047uF, 25V, +/-10%, X7R, 0402	0402
C27	1	0.01uF	C1005X7R1E103K	TDK	CAP, CERM, 0.01uF, 25V, +/-10%, X7R, 0402	0402
C29	1	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	0402
C32	1	1000pF	C1005X7R1H102K	TDK	CAP, CERM, 1000pF, 50V, +/-10%, X7R, 0402	0402
C33	1	4.7uF	C3216X7R1E475K	TDK	CAP, CERM, 4.7uF, 25V, +/-10%, X7R, 1206	1206
D1, D8	2	100V	BAS316,115	NXP Semiconductor	Diode, Ultrafast, 100V, 0.25A, SOD-323	SOD-323
D2, D4, D9	3	1.25V	BAV21W-7-F	Diodes Inc.	Diode, Switching, 200V, 0.2A, SOD-123	SOD-123
D3	1	100V	US1B-13-F	Diodes Inc.	Diode, Ultrafast, 100V, 1A, SMA	SMA
D5, D6, D7, D10, D11	5	1.4V	BAS316,115	NXP Semiconductor	Diode, Ultrafast, 100V, 0.25A, SOD-323	SOD-323
D12	1	6.8V	MMSZ4692-V	Vishay-Semiconductor	Diode, Zener, 6.8V, 500mW, SOD-123	SOD-123
J1, J2	2		691214310002	Wurth Elektronik eiSos	Terminal Block, 2x1, 3.81mm, 24-16 AWG, 10A, 300VAC, TH	2x1 Terminal Block
L1	1	4uH	SER2014-402MLB	Coilcraft	Inductor, Shielded E Core, Ferrite, 4uH, 25A, 0.00194 ohm, SMD	SER2014
L5	1	1mH	LPS4414-105MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 1mH, 0.11A, 16.3 ohm, SMD	LPS4414
Q1, Q2, Q4, Q7	4	60V	CSD18532Q5B	Texas Instruments	MOSFET, N-CH, 60V, 172A, SON 5x6mm	SON 5x6mm
Q3	1	-150V	IRF6216TRPBF	International Rectifier	MOSFET, P-CH, -150V, -2.2A, SO-8	SO-8
Q5, Q6	2	150V	FDMS86200	Fairchild Semiconductor	MOSFET, N-CH, 150V, 35A, PQFN08A	PQFN08A
Q8	1	0.5V	BCX5616TA	Diodes Inc.	Transistor, NPN, 80V, 1A, SOT-89	SOT-89
R1, R9	2	5.1k	CRCW08055K10JNEA	Vishay-Dale	RES, 5.1k ohm, 5%, 0.125W, 0805	0805
R2	1	DNP	N/A	N/A	Do Not Populate	1210
R3	1	0.1	ERJ-6RSJR10V	Panasonic	RES, 0.1 ohm, 5%, 0.125W, 0805	0805
R4, R6, R24, R28	4	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0k ohm, 1%, 0.063W, 0402	0402
R5	1	1.91	RC0805FR-071R91L	Yageo America	RES, 1.91 ohm, 1%, 0.125W, 0805	0805
R7	1	20.0k	CRCW080520K0FKEA	Vishay-Dale	RES, 20.0k ohm, 1%, 0.125W, 0805	0805
R10, R26	2	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00k ohm, 1%, 0.063W, 0402	0402
R12	1	301k	CRCW0402301KFKED	Vishay-Dale	RES, 301k ohm, 1%, 0.063W, 0402	0402
R13, R16, R18	3	0	CRCW04020000ZOED	Vishay-Dale	RES, 0 ohm, 5%, 0.063W, 0402	0402
R14	1	13.0k	CRCW040213K0FKED	Vishay-Dale	RES, 13.0k ohm, 1%, 0.063W, 0402	0402
R15	1	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100k ohm, 1%, 0.063W, 0402	0402
R17	1	8.66k	CRCW04028K66FKED	Vishay-Dale	RES, 8.66k ohm, 1%, 0.063W, 0402	0402

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R19	1	80.6k	CRCW040280K6FKED	Vishay-Dale	RES, 80.6k ohm, 1%, 0.063W, 0402	0402
R20	1	2.00k	CRCW04022K00FKED	Vishay-Dale	RES, 2.00k ohm, 1%, 0.063W, 0402	0402
R22	1	124k	CRCW0402124KFKED	Vishay-Dale	RES, 124k ohm, 1%, 0.063W, 0402	0402
R23	1	4.99k	CRCW04024K99FKED	Vishay-Dale	RES, 4.99k ohm, 1%, 0.063W, 0402	0402
R29	1	2.61k	CRCW04022K61FKED	Vishay-Dale	RES, 2.61k ohm, 1%, 0.063W, 0402	0402
R100	1	4.7	CRCW04024R70JNED	Vishay-Dale	RES, 4.7 ohm, 5%, 0.063W, 0402	0402
T1	1	50uH	RA6992-BL	Coilcraft	Transformer, 50uH, SMT	1160x475x1050mil
T2	1	2000uH	CST2-100L	Coilcraft	Transformer, 2000uH, SMT	8X8.13MM-6P
TP1, TP2	2	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
TP3, TP4	2	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
U1, U3, U4	3		UCC27511DBV	Texas Instruments	Single-Channel High-Speed Low-Side Gate Driver (with 4-A Peak Source and 8-A Peak Sink), DBV0006A	DBV0006A
U5	1		UCC2897ARGPR	Texas Instruments	Advanced Active Clamp PWM Controller with Current Control, -40 to +125 degC, 20-pin QFN (RGP), Green (RoHS & no Sb/Br)	RGP0020D
U6	1		VOS617A-7X001T	Vishay-Semiconductor	OptoCoupler, Phototransistor, 80-160%, SSOP-4	7x2.12x2.6mm
U7	1		TL431AIDBZ	Texas Instruments	PRECISION PROGRAMMABLE REFERENCE, DBZ0003A	DBZ0003A

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.