

## TIDA-01415 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
PCB1	1		TIDA-01415	Any	Printed Circuit Board	
BLED+, BLED-,	40		5015	Keystone	Test Point, Miniature, SMT	Testpoint_Keystone_
GLED+, GLED-,						Miniature
GND, GND,						
GND1, GND1,						
GND1, GND1,						
IADJ1, IADJ2,						
IADJ3, IADJ4,						
PWM1, PWM2,						
PWM3, PWM4,						
RLED+, RLED-,						
SH1, SH2, SH3,						
SH4, SW1, SW2,						
SW3, SW4, SW5,						
SW6, TP1, TP3,						
VFB1, VFB2,						
VFB3, VFB4,						
VIN+, VIN-,						
WLED+, WLED-						
C1, C15, C46,	8	0.1uF	C2012X7R1H104K085AA	TDK	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0805	0805
C59, C85, C86,	_	•••••				
C87, C88						
C2, C16, C47,	4	1uF	C2012X7R1H105K125AB	ТДК	CAP, CERM, 1 µF, 50 V, +/- 10%, X7R, 0805	0805
C60		101				
C3, C14, C45,	5	1uF	C1608X7R1C105K080AC	трк	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0603	0603
C58, C74	-					
C4, C5, C17, C18,	10	2.2uF	C2012X7R1H225K125AC	TDK	CAP, CERM, 2.2 µF, 50 V, +/- 10%, X7R, 0805	0805
C34, C41, C48,						
C49, C61, C62						
,,						
C7, C20, C51,	4	470pF	CGA1A2X7R1H471K030BA	TDK	CAP, CERM, 470 pF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0201	0201
C64						
C27	1	0.33uF	C0603C334K4RACTU	Kemet	CAP, CERM, 0.33 μF, 16 V, +/- 10%, X7R, 0603	0603
C28, C29, C30,	8	2.2uF	C2012X7R1C225K125AB	TDK	CAP, CERM, 2.2 μF, 16 V, +/- 10%, X7R, 0805	0805
C31, C35, C36,						
C101, C102						
C32	1	22uF	GRM31CR61C226KE15L	MuRata	CAP, CERM, 22 μF, 16 V, +/- 10%, X5R, 1206	1206
C37	1	0.047uF	GCM188R71E473KA37D	MuRata	CAP, CERM, 0.047 µF, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C38, C43, C78	3	10uF	GRT188C81A106ME13D	MuRata	CAP, CERM, 10 µF, 10 V, +/- 20%, X6S, AEC-Q200 Grade 2, 0603	0603
C39	-	0.1uF	GRM188R71E104KA01D	MuRata	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0603	0603
C40	1	10uF	CGA4J1X7S1C106K125AC	TDK	CAP, CERM, 10 µF, 16 V, +/- 10%, X7S, AEC-Q200 Grade 1, 0805	0805
C40	1	0.056uF	GRM155R71C563KA88D	MuRata	CAP, CERM, 10 µ, 10 V, 4/- 10%, X73, AEC-0200 Glade 1, 0005	0402
C44		0.0560F	GRM155R61A104KA01D	MuRata	CAP, CERM, 0.056 μF, 10 V, +/- 10%, X/R, 0402	0402
C77, C79	2	0.1uF 0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 µF, 10 V, +/- 10%, X3R, 0402	0603
	 1					
C80		0.15uF	C1608X7R1E154K080AA	TDK	CAP, CERM, 0.15 μF, 25 V, +/- 10%, X7R, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C89, C90, C91,		0.1uF	C1005X7R1E104M050BB	TDK	CAP, CERM, 0.1 µF, 25 V, +/- 20%, X7R, 0402	0402
C92		-				
D1, D3, D4, D6,	8	10V	ZLLS410TA	Diodes Inc.	Diode, Schottky, 10 V, 0.75 A, SOD-323	SOD-323
D8, D10, D11,						
D13						
D2, D5, D9, D12	4	60V	CDBC560-G	Comchip Technology	Diode, Schottky, 60 V, 5 A, SMC	SMC
D7	1	100V	MBR1H100SFT3G	ON Semiconductor	Diode, Schottky, 100 V, 1 A, SOD-123FL	SOD-123FL
FID4, FID5, FID6	3	<u> </u>	N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
J1, J3, J6, J8, J12	5		0022284033	Molex	Header, 2.54mm, 3x1, Tin, TH	Header, 2.54mm, 3x1, TH
J2, J7, J9, J13	4		1751248	Phoenix Contact	Conn Term Block, 2POS, 3.5mm, TH	11x8.5x7.3mm
J4	1		800-10-002-10-001000	Mill-Max	Header, 100mil, 2x1, TH	Header, 2x1, 100mil, TH
J5, J10	2		PEC10DAAN	Sullins Connector Solutions	Header, 100mil, 10x2, TH	Header, 10x2,
						2.54mm, TH
J14	1		1727010	Phoenix Contact	Conn Term Block, 2POS, 3.81mm, TH	2POS Terminal Block
L1, L2, L8, L9	4	47uH	744770147	Wurth Elektronik	Inductor, Shielded Drum Core, Ferrite, 47 µH, 2.7 A, 0.076 ohm, SMD	SMD
L3	1	15uH	744053150	Wurth Elektronik	Inductor, Shielded Drum Core, Ferrite, 15 µH, 1.15 A, 0.07 ohm, SMD	WE-TPC-LH
L4, L5, L10	3	1000 ohm	742792662	Wurth Elektronik	Ferrite Bead, 1000 ohm @ 100 MHz, 0.6 A, 0603	0603
L6	1	220 ohm	BLM15AG221SN1D	MuRata	Ferrite Bead, 220 ohm @ 100 MHz, 0.45 A, 0402	0402
L7	1	330uH	SDR0403-331KL	Bourns	Inductor, Drum Core, Ferrite, 330 µH, 0.17 A, 6 ohm, SMD	4.5x3.2x4mm
LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
Q1, Q3, Q5, Q7	4	100V	CSD19538Q2	Texas Instruments	MOSFET, N-CH, 100 V, 4.5 A, DQK0006C (WSON-6)	DQK0006C
Q2, Q4, Q6, Q8	4	-70V	ZXMP7A17KTC	Diodes Inc.	MOSFET, P-CH, -70 V, -5.7 A, DPAK	DPAK
R1	1	5.62k	CRCW06035K62FKEA	Vishay-Dale	RES, 5.62 k, 1%, 0.1 W, 0603	0603
R2	1	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R3, R4, R17, R18,	8	1.0	CRCW06031R00JNEA	Vishay-Dale	RES, 1.0, 5%, 0.1 W, 0603	0603
R41, R42, R53, R54						
R5, R19, R43, R55	4	0.3	CSRN2512FKR300	Stackpole Electronics Inc	RES, 0.3, 1%, 2 W, 2512	2512
R6, R7, R20, R21,	8	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R44, R45, R56, R57						
R8, R22, R46,	4	470	CRCW0402470RJNED	Vishay-Dale	RES, 470, 5%, 0.063 W, 0402	0402
R58 R9, R23, R47,	4	3.16Meg	CRCW06033M16FKEA	Vishay-Dale	RES, 3.16 M, 1%, 0.1 W, 0603	0603
R59						
R10, R48	2	16.5k	CRCW060316K5FKEA	Vishay-Dale	RES, 16.5 k, 1%, 0.1 W, 0603	0603
R12, R25, R30, R33, R49, R61	6	110k	CRCW0603110KFKEA	Vishay-Dale	RES, 110 k, 1%, 0.1 W, 0603	0603
R14, R28, R52, R64	4	14.0k	CRCW060314K0FKEA	Vishay-Dale	RES, 14.0 k, 1%, 0.1 W, 0603	0603
R15, R16	2	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
R24	1	15.4k	CRCW060315K4FKEA	Vishay-Dale	RES, 15.4 k, 1%, 0.1 W, 0603	0603
R29, R39, R65,	8	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R71, R86, R87, R88, R89						

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R31	1	30.0k	RC0603FR-0730KL	Yageo America	RES, 30.0 k, 1%, 0.1 W, 0603	0603
R32, R94, R95,	5	100	RC0603FR-07100RL	Yageo America	RES, 100, 1%, 0.1 W, 0603	0603
R96, R97						
R34	1	887k	CRCW0402887KFKED	Vishay-Dale	RES, 887 k, 1%, 0.063 W, 0402	0402
R35	1	1.50k	RC0603FR-071K5L	Yageo America	RES, 1.50 k, 1%, 0.1 W, 0603	0603
R36	1	12.4k	CRCW060312K4FKEA	Vishay-Dale	RES, 12.4 k, 1%, 0.1 W, 0603	0603
R37	1	124k	CRCW0402124KFKED	Vishay-Dale	RES, 124 k, 1%, 0.063 W, 0402	0402
R38	1	182k	CRCW0402182KFKED	Vishay-Dale	RES, 182 k, 1%, 0.063 W, 0402	0402
R60	1	7.87k	CRCW06037K87FKEA	Vishay-Dale	RES, 7.87 k, 1%, 0.1 W, 0603	0603
R75, R76, R77, R78	4	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R81	1	412	CRCW1206412RFKEA	Vishay-Dale	RES, 412, 1%, 0.25 W, 1206	1206
R99, R100	2	10.0	CRCW060310R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.1 W, 0603	0603
SH-J3, SH-J4, SH- J5, SH-J6, SH-J7	5	1x2	969102-0000-DA	3M	Shunt, 100mil, Gold plated, Black	Shunt
U1, U4, U10, U13	4		UCC27511DBVR	Texas Instruments	Single-Channel High-Speed Low-Side Gate Driver (with 4-A Peak Source and 8-A Peak Sink), DBV0006A (SOT-6)	DBV0006A
U2, U5, U11, U14	4		LM3409MY/NOPB	Texas Instruments	PFET Buck Controller for High Power LED Drives, 10-pin eMSOP, Pb- Free	MUC10A
U7	1		LP5907SNX-3.3/NOPB	Texas Instruments	250-mA Ultra-Low-Noise, Low-IQ LDO, DQN0004A (X2SON-4)	DQN0004A
U8	1		LMR16006XDDCR	Texas Instruments	Wide Input Voltage Range Buck Regulator with High Efficiency Sleep Mode, DDC0006A (SOT-6)	DDC0006A
U9	1		LM5165DRCR	Texas Instruments	3V-65V, 150mA Synchronous Buck Converter With Ultra-Low IQ, DRC0010J (VSON-10)	DRC0010J
U17	1		DAC7564ICPWR	Texas Instruments	12-Bit, Quad Channel, Ultra-Low Glitch, Voltage Output DAC with 2.5V, 2ppm/degC Internal Reference, PW0016A (TSSOP-16)	PW0016A
C6, C19, C50, C63	0	0.01uF	885012207092	Wurth Elektronik	CAP, CERM, 0.01 μF, 50 V, +/- 10%, X7R, 0805	0805
C33	0	10uF	GRT188C81A106ME13D	MuRata	CAP, CERM, 10 µF, 10 V, +/- 20%, X6S, AEC-Q200 Grade 2, 0603	0603
C97, C98, C99, C100	0	15pF	885012005056	Wurth Elektronik	CAP, CERM, 15 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
R79, R80	0	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated