

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
None						
5/22/2018 3:09:41 PM						
N/A						
PMP20220 REV B Bill of Materials						
C31	1	100pF	C1608C0G1H101J	TDK	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C27	1	330pF	C1608C0G1H331J	TDK	CAP, CERM, 330 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C20	1	470pF	C1608C0G1H471J	TDK	CAP, CERM, 470 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C2, C3, C9, C10	4	1000pF	C1608X7R2A102K	TDK	CAP, CERM, 1000pF, 100V, +/-10%, X7R, 0603	0603
C19	1	2200pF	C1608X7R1H222K	TDK	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0603	0603
C28, C30	0	DNP	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0603	0603
C4, C5, C6, C7	4	0.01uF	C1608X7R2A103K	TDK	CAP, CERM, 0.01uF, 100V, +/-10%, X7R, 0603	0603
C32	1	0.033uF	GRM188R71E333KA01D	MuRata	CAP, CERM, 0.033uF, 25V, +/-10%, X7R, 0603	0603
C29	1	0.1uF	C1608X7R1H104K080AA	TDK	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
C25	1	0.47uF	GRM188R71C474KA88D	MuRata	CAP, CERM, 0.47 µF, 16 V, +/- 10%, X7R, 0603	0603
C23	0	DNP	GRM21A5C2E101JW01D	MuRata	CAP, CERM, 100 pF, 250 V, +/- 5%, C0G/NP0, 0805	0805
C14, C24	2	0.1uF	C2012X7R2A104K	TDK	CAP, CERM, 0.1uF, 100V, +/-10%, X7R, 0805	0805
C18, C26, C33	3	1uF	C2012X7R1C105K	TDK	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0805	0805
C16, C17	2	100uF	C3225X5R0J107M	TDK	CAP, CERM, 100 µF, 6.3 V, +/- 20%, X5R, 1210	1210
C13	1	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2uF, 100V, +/-10%, X7R, 1210	1210
C1, C8, C11, C21	4	1000pF	1812GC102KA1	AVX	CAP, CERM, 1000pF, 2000V, +/-10%, X7R, 1812	1812
C15	1	100uF	6SVP100M	Panasonic	CAP, Aluminum Polymer, 100 µF, 6.3 V, +/- 20%, 0.04 ohm, 6.3x5.8 SMD	6.3x5.8
C22	1	22uF	20TQC22MYFB	Panasonic	CAP, TA, 22 µF, 20 V, +/- 20%, 0.09 ohm, SMD	SMD, 2-Leads, Body 3.7x3mm
C12	1	22uF	EEE-FK2A220P	Panasonic	CAP, AL, 22uF, 100V, +/-20%, 1.3 ohm, SMD	SMT Radial F
D1, D2, D3, D4, D5, D6, D7, D8, D9	9	100V	B2100-13-F	Diodes Inc.	Diode, Schottky, 100 V, 2 A, SMB	SMB
D10	1	200V	MURA120T3G	ON Semiconductor	Diode, Ultrafast, 200 V, 1 A, SMA	SMA
D11, D12, D13, D14	4	100V	MMSD4148T1G	ON Semiconductor	Diode, Switching, 100V, 0.2A, SOD-123	SOD-123
D15	1	58V	SMAJ58A	Littelfuse	Diode, TVS, Uni, 58V, 400W, SMA	SMA
D16	1	30V	BAT54S-7-F	Diodes Inc.	Diode, Schottky, 30V, 0.2A, SOT-23	SOT-23
J1, J2	2		1-406541-1	TE Connectivity	RJ-45, No LED, tab up, R/A, TH	16.26x14.54x15.75
J3	1		PEC02SAAN	Sullins Connector Solutions	Header, 100mil, 2x1, Tin plated, TH	Header, 2 PIN, 100mil, Tin
J4, J5, J6	3		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
L1, L2, L3, L4	4	220 ohm	MPZ1608S221A	TDK	Ferrite Bead, 220 ohm @ 100MHz, 2.2A, 0603	0603
L5	1	3.3uH	LPS4012-332MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 3.3uH, 1.4A, 0.1 ohm, SMD	LPS4012
L6	1	180nH	XFL4015-181MEB	Coilcraft	Inductor, Shielded, Composite, 180 nH, 12 A, 0.0042 ohm, SMD	SMD, 4x4x1.5mm
Q1	1	30V	CSD17579Q3A	Texas Instruments	MOSFET, N-CH, 30 V, 20 A, SON 3.3x3.3mm	SON 3.3x3.3mm
Q2	1	40 V	MMBT3906-7-F	Diodes Inc.	Transistor, PNP, 40 V, 0.2 A, SOT-23	SOT-23
Q3	1	150V	FDS86242	Fairchild Semiconductor	MOSFET, N-CH, 150V, 4.1A, SOIC-8	SOIC-8
R1, R2, R4, R5, R6, R7, R8, R9	8	75.0	CRCW060375R0FKEA	Vishay-Dale	RES, 75.0 ohm, 1%, 0.1W, 0603	0603
R25, R27	2	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, 0603	0603
R11	1	4.7	CRCW06034R70JNEA	Vishay-Dale	RES, 4.7, 5%, 0.1 W, 0603	0603
R15	1	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, 0603	0603
R21	1	63.4	CRCW060363R4FKEA	Vishay-Dale	RES, 63.4 ohm, 1%, 0.1W, 0603	0603
R17	1	332	CRCW0603332RFKEA	Vishay-Dale	RES, 332, 1%, 0.1 W, 0603	0603
R31	1	357	CRCW0603357RFKEA	Vishay-Dale	RES, 357, 1%, 0.1 W, 0603	0603
R29	1	665	CRCW0603665RFKEA	Vishay-Dale	RES, 665, 1%, 0.1 W, 0603	0603
R33	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R28	1	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00 k, 1%, 0.1 W, 0603	0603
R34	1	3.24k	CRCW06033K24FKEA	Vishay-Dale	RES, 3.24 k, 1%, 0.1 W, 0603	0603
R23	1	4.42k	CRCW06034K42FKEA	Vishay-Dale	RES, 4.42 k, 1%, 0.1 W, 0603	0603
R14	1	4.99k	CRCW06034K99FKEA	Vishay-Dale	RES, 4.99 k, 1%, 0.1 W, 0603	0603
R30, R32	2	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R3	1	24.9k	CRCW060324K9FKEA	Vishay-Dale	RES, 24.9k ohm, 1%, 0.1W, 0603	0603
R18	1	27.4k	CRCW060327K4FKEA	Vishay-Dale	RES, 27.4 k, 1%, 0.1 W, 0603	0603
R24	1	34.0k	CRCW060334K0FKEA	Vishay-Dale	RES, 34.0 k, 1%, 0.1 W, 0603	0603
R20	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R26	0	DNP	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R22	0	DNP	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603
R19	1	0.1	ERJ-6RSFR10V	Panasonic	RES, 0.1, 1%, 0.125 W, 0805	0805
R12	1	10	CRCW080510R0JNEA	Vishay-Dale	RES, 10, 5%, 0.125 W, 0805	0805
R10	1	39k	CRCW080539K0JNEA	Vishay-Dale	RES, 39k ohm, 5%, 0.125W, 0805	0805
R13	1	3.3	CRCW12063R30JNEA	Vishay-Dale	RES, 3.3, 5%, 0.25 W, 1206	1206
R16	0	DNP	CRCW1206100RJNEA	Vishay-Dale	RES, 100, 5%, 0.25 W, 1206	1206
T1	1	350uH	H6096NL	Pulse Engineering	TRANSFORMER/CMC MOD, GIGABIT POE+, SMT	12.2X6.6X18.16 mm
T2	1	48uH	PA3855.002NLT	Pulse Engineering	Transformer, 48 uH, SMT	SMD, 10-Leads, Body 14.5x14.5mm
TP1	1		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
U1	1		PC357N4J000F	Sharp Microelectronics	Optocoupler, 3.75 kV, 300-600% CTR, SMT	4.4x2.6x3.6mm
U2	1		TPS23751PWP	Texas Instruments	IEEE 802.3at PoE Interface with Wide Range High Efficiency DC-DC Controller, PWP0016D	PWP0016D
U3	1		HMHA2801A	Fairchild Semiconductor	Optocoupler, 3.75kV RMS, SMT	Mini Flat Package
U4	1		TLV431AIDBVR	Texas Instruments	LOW-VOLTAGE ADJUSTABLE PRECISION SHUNT REGULATOR, DBV0005A	DBV0005A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated