

UCD9240 Data Sheet Errata

These are the errata for the UCD9240 64-pin and UCD9240 80-pin devices.

Erratum #1

Address arbitration for a PMBus Alert Response event may not work when there is more than one device on the bus. Specifically, if two or more devices report an alert (via the PMBus-Alert signal) to the host and the host issues an Alert Response Address command (a Receive Byte command with address 12), the device with the lower PMBus address will win the arbitration and its address will be the one received by the host. The device with the higher PMBus address will be unaware that it lost arbitration, and the next command to the device with the higher PMBus address will be ignored. If the host sends a third Alert Response Address command and this device wins the arbitration, then the host will receive the higher address in response.

A simple workaround for this issue is to follow any Alert Response Address command with a PMBus STATUS_WORD command using the address that was received in the Alert Response message. Since this address will not be the address for the device that lost arbitration, it will clear the PMBus hardware for that device, allowing it to respond to the next Alert Response Address request on the PMBus.

This affects both the 64-pin and 80-pin devices.

Erratum #2

PMBus address bins 0, 1, 2, and 3 from the PMBus Address Bins Table of the UCD9240 datasheet are not reliably detected over process, temperature and component variations and should not be used. The 62 supported addresses are shown below.

		PMBus Address							
		Addr1							
		4	5	6	7	8	9	10	
Addr0	4	52	64	76	88	100	112	124	
	5	53	65	77	89	101	113	125	
	6	54	66	78	90	102	114	126	
	7	55	67	79	91	103	115	127	
	8	56	68	80	92	104	116		
	9	57	69	81	93	105	117		
	10	58	70	82	94	106	118		
	11	59	71	83	95	107	119		

Refer to the “Resistor Programmed PMBus Address Decode” of the UCD9240 Datasheet (SLUS766) for more information about generating the supported addresses with the remaining allowed bins. Also, the restrictions regarding address 127 and 126 still apply.

This affects both the 64-pin and 80-pin devices.

Erratum #3

The Open-Drain output mode for the GPIO_SEQ_CONFIG command is not supported on the UCD9240 80-pin device. Please refer to the GPIO_SEQ_CONFIG command in the UCD92xx PMBus Command Reference ([SLUU337](#)).

Erratum #4

The Open-Drain Status output event type for the GPIO_SEQ_CONFIG command is not supported on the UCD9240 64-pin device. Refer to the GPIO_SEQ_CONFIG command in the UCD92xx PMBus Command Reference ([SLUU337](#)).

Erratum #5

A voltage offset may be introduced to the output if the AFE gain is different between CLA banks. The EADC_TRIM PMBus command was created so that the user could minimize this offset between two AFE gain settings. See the UCD92xx PMBus Command Reference ([SLUU337](#)) for more information on the EADC_TRIM command.

Erratum #6

When the AFE gain setting is different between CLA banks, there is a chance that the wrong AFE gain setting will be used to calculate the error between the reference voltage (V_{ref}) and the sensed voltage at the EAP/EAN inputs. In normal operation the error is near zero and this does not affect the system. When there is a transient that causes the difference between the reference voltage and the sensed voltage to be large, the calculated error voltage may be larger or smaller than the actual error if the wrong AFE gain is used in the calculation.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Medical	www.ti.com/medical
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2009, Texas Instruments Incorporated