

2-BIT UNIDIRECTIONAL VOLTAGE-LEVEL TRANSLATOR

 Check for Samples: [SN74AVC2T244](#)


FEATURES

- Wide Operating V_{CC} Range of 0.9 V to 3.6 V
- Low Static-Power Consumption, 6- μ A Max I_{CC}
- Output Enable Feature Allows User to Disable Outputs to Reduce Power Consumption
- ± 24 -mA Output Drive at 3.0 V
- I_{off} Supports Partial Power-Down-Mode Operation
- Input Hysteresis Allows Slow Input Transition and Better Switching Noise Immunity at Input
- Maximum Data Rates
 - 380 Mbps (1.8-V to 3.3-V Translation)
 - 200 Mbps (<1.8-V to 3.3-V Translation)
 - 200 Mbps (Translate to 2.5 V or 1.8 V)
 - 150 Mbps (Translate to 1.5 V)
 - 100 Mbps (Translate to 1.2 V)

- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
 - 5000-V Human-Body Model (A114-A)

APPLICATIONS

- Handset, Smartphone, Tablet, Server

**DQE/DQM PACKAGE
(TOP VIEW)**


DESCRIPTION/ORDERING INFORMATION

This 2-bit unidirectional translator uses two separate configurable power-supply rails. The A port is designed to track V_{CCA} . V_{CCA} accepts any supply voltage from 0.9 V to 3.6 V. The B port is designed to track V_{CCB} . V_{CCB} accepts any supply voltage from 0.9 V to 3.6 V. This allows for low-voltage translation between 0.9-V, 1.2-V, 1.5-V, 1.8-V, 2.5-V and 3.6-V voltage nodes. For the SN74AVC2T244, when the output-enable (\overline{OE}) input is high, all outputs are placed in the high-impedance state. The SN74AVC2T244 is designed so that the \overline{OE} input circuit is referenced to V_{CCA} . This device is fully specified for partial-power-down applications using I_{off} . The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

ORDERING INFORMATION⁽¹⁾

| T_A | PACKAGE ⁽²⁾ | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|---------------|------------------------|-----------------------|------------------|
| -40°C to 85°C | DQE – MicroQFN | SN74AVC2T244DQER | VA |
| | DQM – MicroQFN | SN74AVC2T244DQMR | VAH |

(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com.

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

DEVICE INFORMATION

PIN DESCRIPTION

| PIN | FUNCTION |
|------|-----------------------------|
| VCCA | Input Port DC Power Supply |
| VCCB | Output Port DC Power Supply |
| GND | Ground |
| An | Input Port |
| Bn | Output Port |
| OE | Output Enable |

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

| | | MIN | MAX | UNIT | |
|---|--|----------------------|------------|------|---|
| Voltage | DC Supply voltage, V_{CCA} , V_{CCB} | -0.5 | 4.6 | V | |
| | DC Input voltage, V_I | A_n -0.5 | 4.6 | V | |
| | Control Input, V_C | \overline{OE} -0.5 | 4.6 | V | |
| | DC Output voltage, V_O , $V_{CCA} = V_{CCB} = 0$ | (Power Down) | B_n -0.5 | 4.6 | V |
| | | (Active Mode) | B_n -0.5 | 4.6 | |
| | | 3-State Mode | B_n -0.5 | 4.6 | |
| DC Input Diode current, I_{IK} | $V_I < GND$ | | -20 | mA | |
| DC Output Diode current, I_{OK} | $V_O < GND$ | | -50 | mA | |
| DC Output Source/Sink current, I_O | | | ±50 | mA | |
| DC Supply current per supply pin, I_{CCA} , I_{CCB} | | | ±100 | mA | |
| I_{GND} | DC Ground current per ground pin | | ±100 | mA | |
| T_{stg} | Storage temperature range | -65 | 150 | °C | |

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

RECOMMENDED OPERATING CONDITIONS

| | | MIN | MAX | UNIT | |
|-----------------------|--|---------------------|-----------|-----------|---|
| V_{CCA} , V_{CCB} | Positive DC Supply voltage | 0.9 | 3.6 | V | |
| V_I | Bus input voltage | GND | 3.6 | V | |
| V_I | Input voltage | GND | 3.6 | V | |
| V_C | Control input | \overline{OE} GND | 3.6 | V | |
| V_O | Bus output voltage | (Power Down Mode) | B_n GND | 3.6 | V |
| | | (Active Mode) | B_n GND | V_{CCB} | V |
| | | 3-State Mode | B_n GND | 3.6 | V |
| T_A | Operating free-air temperature | -40 | 85 | °C | |
| $\Delta t/\Delta v$ | Input transition rise or fall rate V_I from 30% to 70% of V_{CC} ; $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$ | 0 | 10 | nS | |

ELECTRICAL CHARACTERISTICS^{(1) (2)}

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CCA} (V) | V _{CCB} (V) | –40°C to 85°C | | UNIT |
|-------------------------------------|--|--|----------------------|----------------------|-------------------------|-------------------------|------|
| | | | | | MIN | MAX | |
| V _{IH} | Input HIGH Voltage (A _n , \overline{OE}) | | 2.7 – 3.6 | 0.9 – 3.6 | 2.0 | – | V |
| | | | 2.3 – 2.7 | | 1.6 | – | |
| | | | 1.4 – 2.3 | | 0.65 × V _{CCA} | – | |
| | | | 0.9 – 1.4 | | 0.9 × V _{CCA} | – | |
| V _{IL} | Input LOW voltage (A _n , \overline{OE}) | | 2.7 – 3.6 | 0.9 – 3.6 | – | 0.8 | V |
| | | | 2.3 – 2.7 | | – | 0.7 | |
| | | | 1.4 – 2.3 | | – | 0.35 × V _{CCA} | |
| | | | 0.9 – 1.5 | | – | 0.1 × V _{CCA} | |
| V _{OH} | Output HIGH voltage | I _{OH} = –100 μA; V _I = V _H | 0.9 – 3.6 | 0.9 – 3.6 | V _{CCB} – 0.2 | – | V |
| | | I _{OH} = –0.5 mA; V _I = V _H | 0.9 | 0.9 | 0.75 × V _{CCB} | – | |
| | | I _{OH} = –2 mA; V _I = V _H | 1.4 | 1.4 | 1.05 | – | |
| | | I _{OH} = –6 mA; V _I = V _H | 1.65 | 1.65 | 1.25 | – | |
| | | I _{OH} = –12 mA; V _I = V _H | 2.3 | 2.3 | 2.0 | – | |
| | | I _{OH} = –12 mA; V _I = V _H | 2.3 | 2.3 | 1.8 | – | |
| | | I _{OH} = –18 mA; V _I = V _H | 2.7 | 2.7 | 2.2 | – | |
| | | I _{OH} = –18 mA; V _I = V _H | 2.3 | 2.3 | 1.7 | – | |
| V _{OL} | Output LOW voltage | I _{OH} = –24 mA; V _I = V _H | 3.0 | 3.0 | 2.4 | – | V |
| | | I _{OH} = 100 μA; V _I = V _H | 0.9 – 3.6 | 0.9 – 3.6 | – | 0.2 | |
| | | I _{OH} = 0.5 mA; V _I = V _H | 1.1 | 1.1 | – | 0.3 | |
| | | I _{OH} = 2 mA; V _I = V _H | 1.4 | 1.4 | – | 0.35 | |
| | | I _{OH} = 6 mA; V _I = V _H | 1.65 | 1.65 | – | 0.3 | |
| | | I _{OH} = 12 mA; V _I = V _H | 2.3 | 2.3 | – | 0.4 | |
| | | I _{OH} = 12 mA; V _I = V _H | 2.7 | 2.7 | – | 0.4 | |
| | | I _{OH} = 18 mA; V _I = V _H | 2.3 | 2.3 | – | 0.6 | |
| I _I | Input Leakage Current | V _I = V _{CCA} or GND | 0.9 – 3.6 | 0.9 – 3.6 | –1.0 | 1.5 | μA |
| | | | 0 | 0.9 – 3.6 | –1.0 | 1.3 | |
| I _{OFF} | Power-Off Leakage Current | $\overline{OE} = 0V$ | 0.9 – 3.6 | 0 | –1.0 | 1.5 | μA |
| | | | 0 | 0.9 – 3.6 | –1.0 | 1.5 | |
| I _{CCA} | Quiescent Supply Current | V _I = V _{CCA} or GND; I _O = 0 | 0.9 – 3.6 | 0.9 – 3.6 | – | 3.0 | μA |
| I _{CCB} | Quiescent Supply Current | V _I = V _{CCA} or GND; I _O = 0 | 0.9 – 3.6 | 0.9 – 3.6 | – | 3.0 | μA |
| I _{CCA} + I _{CCB} | Quiescent Supply Current | V _I = V _{CCA} or GND; I _O = 0 | 0.9 – 3.6 | 0.9 – 3.6 | – | 6.0 | μA |
| ΔI _{CCA} | Increase in I _{CC} per Input Voltage, Other inputs at V _{CCA} or GND | V _I = V _{CCA} – 0.3 V; V _I = V _{CCA} or GND | 3.6 | 3.6 | – | 5.0 | μA |

 (1) V_{CCO} is the V_{CC} associated with the output port.

 (2) V_{CCI} is the V_{CC} associated with the input port.

ELECTRICAL CHARACTERISTICS^{(1) (2)} (continued)

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | | TEST CONDITIONS | V _{CCA} (V) | V _{CCB} (V) | –40°C to 85°C | | UNIT |
|------------------|--|--|----------------------|----------------------|---------------|-----|------|
| | | | | | MIN | MAX | |
| ΔI_{CCB} | Increase in I _{CC} per Input Voltage, Other inputs at V _{CCA} or GND | V _I = V _{CCA} – 0.3 V; V _I = V _{CCA} or GND | 3.6 | 3.6 | – | 5.0 | μA |
| I _{OZ} | I/O Tri-State Output Leakage Current | T _A = 25°C, \overline{OE} = 0 V | 0.9 – 3.6 | 0.9 – 3.6 | –1.0 | 1.0 | μA |

AC ELECTRICAL CHARACTERISTICS

over operating free-air temperature range (unless otherwise noted)

| Symbol | Parameter | V _{CCA} (V) | V _{CCB} (V) | MIN | MAX | UNIT |
|---------------------------------------|---|----------------------|----------------------|-----|------|------|
| t _{PLH} , t _{PHL} | Propagation Delay, A _n to B _n | 0.9 – 3.6 | 0.9 – 3.6 | | 20 | nS |
| | | 1.2 – 3.6 | 1.2 – 3.6 | | 7 | |
| | | 1.8 – 3.6 | 1.8 – 3.6 | | 3.5 | |
| t _{PZH} , t _{PZL} | Output Enable, \overline{OE} to B _n | 0.9 – 3.6 | 0.9 – 3.6 | | 23 | nS |
| | | 1.2 – 3.6 | 1.2 – 3.6 | | 6.5 | |
| | | 1.8 – 3.6 | 1.8 – 3.6 | | 4.1 | |
| t _{PHZ} , t _{PLZ} | Output Disable, \overline{OE} to B _n | 0.9 – 3.6 | 0.9 – 3.6 | | 17 | nS |
| | | 1.2 – 3.6 | 1.2 – 3.6 | | 7 | |
| | | 1.8 – 3.6 | 1.8 – 3.6 | | 4.3 | |
| t _{OSHL} , t _{OSLH} | Output to Output Skew, Time | 0.9 – 3.6 | 0.9 – 3.6 | | 0.15 | nS |
| | | 1.2 – 3.6 | 1.2 – 3.6 | | 0.15 | |
| | | 1.8 – 3.6 | 1.8 – 3.6 | | 0.15 | |

Table 1. CAPACITANCE⁽¹⁾

| Symbol | Parameter | Test Conditions | TYP ⁽²⁾ | Unit |
|------------------|-------------------------------|--|--------------------|------|
| C _{IN} | Control Pin Input Capacitance | V _{CCA} = V _{CCB} = 3.3 V, V _I = 0 V or V _{CCA/B} | 3.5 | pF |
| C _{I/O} | I/O Pin Input capacitance | V _{CCA} = V _{CCB} = 3.3 V, V _I = 0 V or V _{CCA/B} | 5.0 | pF |
| C _{PD} | Power Dissipation Capacitance | V _{CCA} = V _{CCB} = 3.3 V, V _I = 0 V or V _{CCA/B} , f = 10 MHz | 33 | pF |

- (1) C_{PD} is defined as the value of the IC's equivalent capacitance from which the operating current can be calculated from: I_{CC(operating)} ≈ C_{PD} × V_{CC} × f_{IN} × N_{SW} where I_{CC} = I_{CCA} + I_{CCB} and N_{SW} = total number of outputs switching.
- (2) Typical values are at TA = +25°C.

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead/Ball Finish (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|---------------|--------------|-----------------|------|-------------|-------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| SN74AVC2T244DQER | ACTIVE | X2SON | DQE | 8 | 5000 | Green (RoHS & no Sb/Br) | NIPDAUAG | Level-1-260C-UNLIM | -40 to 85 | VA | Samples |
| SN74AVC2T244DQMR | ACTIVE | X2SON | DQM | 8 | 3000 | Green (RoHS & no Sb/Br) | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | VA | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION



QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AVC2T244DQER | X2SON | DQE | 8 | 5000 | 180.0 | 8.4 | 1.2 | 1.6 | 0.55 | 4.0 | 8.0 | Q1 |
| SN74AVC2T244DQMR | X2SON | DQM | 8 | 3000 | 180.0 | 8.4 | 1.57 | 2.21 | 0.59 | 4.0 | 8.0 | Q1 |


TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AVC2T244DQER | X2SON | DQE | 8 | 5000 | 202.0 | 201.0 | 28.0 |
| SN74AVC2T244DQMR | X2SON | DQM | 8 | 3000 | 202.0 | 201.0 | 28.0 |


DQM (R-PX2SON-N8)

PLASTIC SMALL OUTLINE NO-LEAD





4210302/A 06/2009

- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 - B. This drawing is subject to change without notice.
 - C. SON (Small Outline No-Lead) package configuration.



- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
 - D. Customers should contact their board fabrication site for recommended solder mask tolerances.



4225204/A 08/2019

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package complies to JEDEC MO-287 variation X2EAF.

EXAMPLE BOARD LAYOUT


DQE0008A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 40X



SOLDER MASK DETAILS

4225204/A 08/2019

NOTES: (continued)


- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

EXAMPLE STENCIL DESIGN

DQE0008A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.075 MM THICK STENCIL
SCALE: 40X

4225204/A 08/2019

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2020, Texas Instruments Incorporated