

## **TPS40074 Errata**

---



---

### **1 Parts Affected**

- TPS40074

The new data sheets address some known issues and work arounds.

### **2 Symptoms**

#### **2.1 Soft-Start Latch Off During Over Current**

- **Cause:** A glitch occurs on the internal run signal which causes the device to latch off.
- **Corrective Action:** Limit soft-start capacitor to 22 nF maximum.

#### **2.2 Cross Conduction During Start Up**

- **Cause:** Predictive gate drive timing issue with low pulse width.
- **Corrective Action:** Limit maximum soft start time per formula found in data sheet.

$$t_{START} \leq \frac{D_{MIN}}{f_{SW} \times 10^{-7}} \text{ ms}$$

Where:

- $D_{MIN}$  is the minimum operating duty cycle.
- $F_{SW}$  is the converter switching frequency.

#### **2.3 Low Frequency Ripple on Output Voltage**

- **Cause:** Internal charge pump causes ripple on the unbuffered reference.
- **Corrective Action:** None with current silicon. Effect has been noted on the data sheet.

##### **2.3.1 Output Ripple Consideration**

In addition to the typical output ripple associated with switching converters, which can vary from 5 mV to 150 mV, the TPS40070/71 exhibits a low-frequency ripple from 5 mV to 50 mV. The ripple, a consequence of the charge pump in the driver supply regulator, is well bounded under changes in line, load and temperature. The ripple frequency does vary with the converter switching frequency and can vary from 10 kHz to 60 kHz.

#### **2.4 Cross Conduction During Marginal Over Current**

- **Cause:** Over current pulse shifts predictive gate drive timing. This produces short pulse/long pulse.
- **Corrective Action:** OCP set point should be at least 20% higher than the maximum output current.

#### **2.5 High-Side FET Latches On when Starting Up into a Short Circuit**

- **Cause:** Substrate injection from SW pin can cause shoot through.
- **Corrective Action:** Add 1.5-Ω resistor between switch node and SW pin of device.

## Symptoms

### 2.6 Low-Side Gate Charge Limitation

- **Cause:** Max predictive gate drive delay can be as low as 100 ns - this limits size of power FETs (<50-nC FETs).
- **Corrective Action:** Maximum sync FET gate charge is 50 nC.

### 2.7 High Slew Rate Input Voltage can cause Overshoot and Damage the Device

- **Cause:** If input rises too quickly the device's internal 10-V regulator can over shoot which will damage the device.
- **Corrective Action:** Add a small RC on the VDD pin of the device. Details can be found in the data sheet.

#### 2.7.1 SLEW RATE LIMIT ON VDD

The regulator that supplies power for the drivers on the TPS40070/1 requires a limited rising slew rate on VDD for proper operation if the input voltage is above 10 V. If the slew rate is too great, this regulator can over shoot and damage to the part can occur. To ensure that the part operates properly, limit the slew rate to no more than 0.12 V/ $\mu$ s as the voltage at VDD crosses 8 V. If necessary, an R-C filter can be used on the VDD pin of the device. Connect the resistor from the VDD pin to the input supply of the converter. Connect the capacitor from the VDD pin to PGND. There should not be excessive (more than a 200-mV) voltage drop across the resistor in normal operation. This places some constraints on the R-C values that can be used. is a schematic fragment that shows the connection of the R-C slew rate limit circuit.




Figure 1. Limiting the Slew Rate

### 2.8 Overshoot on Output During Shutdown When UVLO is Set Less than 6.5 V

- **Cause:** A race condition exists in the device which will cause the output to over shoot.
- **Corrective Action:** Add a 330-k $\Omega$  resistor in parallel with the soft start capacitor.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
Low Power Wireless	<a href="http://www.ti.com/lpw">www.ti.com/lpw</a>

### Applications

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Broadband	<a href="http://www.ti.com/broadband">www.ti.com/broadband</a>
Digital Control	<a href="http://www.ti.com/digitalcontrol">www.ti.com/digitalcontrol</a>
Military	<a href="http://www.ti.com/military">www.ti.com/military</a>
Optical Networking	<a href="http://www.ti.com/opticalnetwork">www.ti.com/opticalnetwork</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Telephony	<a href="http://www.ti.com/telephony">www.ti.com/telephony</a>
Video & Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless">www.ti.com/wireless</a>

Mailing Address: Texas Instruments  
Post Office Box 655303 Dallas, Texas 75265