

CSD19506KCS 80V N-Channel NexFET™ Power MOSFET

1 Features




- Ultra-low Q_g and Q_{gd}
- Low thermal resistance
- Avalanche rated
- Pb-free terminal plating
- RoHS compliant
- Halogen free
- TO-220 plastic package

2 Applications

- Secondary side synchronous rectifier
- Motor control

3 Description

This 80V, 2.0m Ω , TO-220 NexFET™ power MOSFET is designed to minimize losses in power conversion applications.



Product Summary

| $T_A = 25^\circ\text{C}$ | | TYPICAL VALUE | | UNIT |
|--------------------------|-------------------------------|-----------------------|-----|------------|
| V_{DS} | Drain-to-Source Voltage | 80 | | V |
| Q_g | Gate Charge Total (10V) | 120 | | nC |
| Q_{gd} | Gate Charge Gate to Drain | 20 | | nC |
| $R_{DS(on)}$ | Drain-to-Source On Resistance | $V_{GS} = 6\text{V}$ | 2.2 | m Ω |
| | | $V_{GS} = 10\text{V}$ | 2.0 | m Ω |
| $V_{GS(th)}$ | Threshold Voltage | 2.5 | | V |

Ordering Information

| Device | Package ⁽¹⁾ | Media | Qty | Ship |
|-------------|------------------------|-------|-----|------|
| CSD19506KCS | TO-220 Plastic Package | Tube | 50 | Tube |

- (1) For all available packages, see the orderable addendum at the end of the data sheet.

Absolute Maximum Ratings

| $T_A = 25^\circ\text{C}$ | | VALUE | UNIT |
|--------------------------|---|------------|------------------|
| V_{DS} | Drain-to-Source Voltage | 80 | V |
| V_{GS} | Gate-to-Source Voltage | ± 20 | V |
| I_D | Continuous Drain Current (Package limited) | 150 | A |
| | Continuous Drain Current (Silicon limited), $T_C = 25^\circ\text{C}$ | 273 | |
| | Continuous Drain Current (Silicon limited), $T_C = 100^\circ\text{C}$ | 193 | |
| I_{DM} | Pulsed Drain Current ⁽¹⁾ | 400 | A |
| P_D | Power Dissipation | 375 | W |
| T_J , T_{stg} | Operating Junction and Storage Temperature Range | -55 to 175 | $^\circ\text{C}$ |
| E_{AS} | Avalanche Energy, single pulse $I_D = 129\text{A}$, $L = 0.1\text{mH}$, $R_G = 25\Omega$ | 832 | mJ |

- (1) Max $R_{\theta JC} = 0.4^\circ\text{C/W}$, pulse duration $\leq 100\mu\text{s}$, duty cycle $\leq 1\%$



Table of Contents

| | | | |
|---|---|--|---|
| 1 Features | 1 | 5.1 Third-Party Products Disclaimer..... | 7 |
| 2 Applications | 1 | 5.2 Receiving Notification of Documentation Updates..... | 7 |
| 3 Description | 1 | 5.3 Support Resources..... | 7 |
| 4 Specifications | 3 | 5.4 Trademarks..... | 7 |
| 4.1 Electrical Characteristics..... | 3 | 5.5 Electrostatic Discharge Caution..... | 7 |
| 4.2 Thermal Information..... | 3 | 5.6 Glossary..... | 7 |
| 4.3 Typical MOSFET Characteristics..... | 4 | 6 Revision History | 7 |
| 5 Device and Documentation Support | 7 | 7 Mechanical, Packaging, and Orderable Information | 8 |

4 Specifications

4.1 Electrical Characteristics

($T_A = 25^\circ\text{C}$ unless otherwise stated)

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|--------------------------------|----------------------------------|---|-----|------|-------|------------|
| STATIC CHARACTERISTICS | | | | | | |
| BV_{DSS} | Drain-to-Source Voltage | $V_{GS} = 0V, I_D = 250\mu A$ | 80 | | | V |
| I_{DSS} | Drain-to-Source Leakage Current | $V_{GS} = 0V, V_{DS} = 64V$ | | | 1 | μA |
| I_{GSS} | Gate-to-Source Leakage Current | $V_{DS} = 0V, V_{GS} = 20V$ | | | 100 | nA |
| $V_{GS(th)}$ | Gate-to-Source Threshold Voltage | $V_{DS} = V_{GS}, I_D = 250\mu A$ | 2.1 | 2.5 | 3.2 | V |
| $R_{DS(on)}$ | Drain-to-Source On-Resistance | $V_{GS} = 6V, I_D = 100A$ | | 2.2 | 2.8 | m Ω |
| | | $V_{GS} = 10V, I_D = 100A$ | | 2.0 | 2.3 | m Ω |
| g_{fs} | Transconductance | $V_{DS} = 8V, I_D = 100A$ | | 297 | | S |
| DYNAMIC CHARACTERISTICS | | | | | | |
| C_{iss} | Input Capacitance | $V_{GS} = 0V, V_{DS} = 40V, f = 1MHz$ | | 9380 | 12200 | pF |
| C_{oss} | Output Capacitance | | | 2260 | 2940 | pF |
| C_{rss} | Reverse Transfer Capacitance | | | 42 | 55 | pF |
| R_G | Series Gate Resistance | | | 1.3 | 2.6 | Ω |
| Q_g | Gate Charge Total (10V) | $V_{DS} = 40V, I_D = 100A$ | | 120 | 156 | nC |
| Q_{gd} | Gate Charge Gate to Drain | | | 20 | | nC |
| Q_{gs} | Gate Charge Gate to Source | | | 37 | | nC |
| $Q_{g(th)}$ | Gate Charge at V_{th} | | | 25 | | nC |
| Q_{oss} | Output Charge | $V_{DS} = 40V, V_{GS} = 0V$ | | 345 | | nC |
| $t_{d(on)}$ | Turn On Delay Time | $V_{DS} = 40V, V_{GS} = 10V,$ $I_{DS} = 100A, R_G = 0\Omega$ | | 19 | | ns |
| t_r | Rise Time | | | 11 | | ns |
| $t_{d(off)}$ | Turn Off Delay Time | | | 30 | | ns |
| t_f | Fall Time | | | 10 | | ns |
| DIODE CHARACTERISTICS | | | | | | |
| V_{SD} | Diode Forward Voltage | $I_{SD} = 100A, V_{GS} = 0V$ | | 0.9 | 1.1 | V |
| Q_{rr} | Reverse Recovery Charge | $V_{DS} = 40V, I_F = 100A,$ $di/dt = 300A/\mu s$ | | 525 | | nC |
| t_{rr} | Reverse Recovery Time | | | 107 | | ns |

4.2 Thermal Information

($T_A = 25^\circ\text{C}$ unless otherwise stated)⁽¹⁾

| THERMAL METRIC | | MIN | TYP | MAX | UNIT |
|-----------------|--|-----|-----|-----|--------------------|
| $R_{\theta JC}$ | Junction-to-Case Thermal Resistance | | | 0.4 | $^\circ\text{C/W}$ |
| $R_{\theta JA}$ | Junction-to-Ambient Thermal Resistance | | | 62 | |

(1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](#).

4.3 Typical MOSFET Characteristics

($T_A = 25^\circ\text{C}$ unless otherwise stated)




Figure 4-1. Transient Thermal Impedance




Figure 4-2. Saturation Characteristics










Figure 4-3. Transfer Characteristics

4.3 Typical MOSFET Characteristics (continued)

($T_A = 25^\circ\text{C}$ unless otherwise stated)



4.3 Typical MOSFET Characteristics (continued)

($T_A = 25^\circ\text{C}$ unless otherwise stated)




Figure 4-10. Maximum Safe Operating Area




Figure 4-11. Single Pulse Unclamped Inductive Switching




Figure 4-12. Maximum Drain Current vs Temperature

5 Device and Documentation Support

5.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

5.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

5.3 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

5.4 Trademarks

NexFET™ and TI E2E™ are trademarks of Texas Instruments.
All trademarks are the property of their respective owners.

5.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

5.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

6 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision B (October 2014) to Revision C (May 2024) Page

- Updated the numbering format for tables, figures, and cross-references throughout the document..... 1

Changes from Revision A (February 2014) to Revision B (October 2014) Page

- Changed Pulsed Drain Current Conditions 1
- Updated the SOA in [Figure 4-10](#) 4

Changes from Revision * (December 2013) to Revision A (February 2014) Page

- Increased Package Current Limit to 150A 1
- Increased Pulsed Drain Current to 400A 1
- Updated SOA Curve 4

7 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead finish/ Ball material (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|---------------|--------------|-----------------|------|-------------|---------------------|--------------------------------------|----------------------|--------------|-------------------------|---------|
| CSD19506KCS | ACTIVE | TO-220 | KCS | 3 | 50 | RoHS-Exempt & Green | SN | N / A for Pkg Type | -55 to 175 | CSD19506KCS | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=100ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TUBE


*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CSD19506KCS | KCS | TO-220 | 3 | 50 | 532 | 34.1 | 700 | 9.6 |
| CSD19506KCS | KCS | TO-220 | 3 | 50 | 534.5 | 33 | 7000 | 3.4 |


KCS0003B



PACKAGE OUTLINE

TO-220 - 19.65 mm max height

TO-220



422214/B 08/2018

NOTES:

1. Dimensions are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC registration TO-220.

EXAMPLE BOARD LAYOUT

KCS0003B

TO-220 - 19.65 mm max height

TO-220



LAND PATTERN EXAMPLE
NON-SOLDER MASK DEFINED
SCALE:15X

4222214/B 08/2018

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated