







DS90UH988-Q1 SNLS765 - FEBRUARY 2024

# DS90UH988-Q1 Automotive FPD-Link IV to OpenLDI Deserializer With HDCP

#### 1 Features

- OpenLDI (OLDI) transmitter
  - 2 Port OLDI output (Dual Pixel Link) up to 420MHz OLDI clock
  - Each Port supports 8MHz to 210MHz OLDI
  - Configurable 18-bit, 24-bit, 30-bit RGB
  - Stream synchronization and splitting
- FPD-Link IV interface
  - Up to 13.5/12.528/10.8/6.75/3.375Gbps per channel; Up to 27Gbps over dual channels
  - Coax/STP interconnect support
  - Selectable 1, 2 channels
  - Daisy-chain and splitting
  - Adaptive equalization
- Optional digital RGB parallel output interface supports 8MHz to 125MHz PCLK
- Ultra-low latency control channel
  - Two fast-mode plus I2C up to 1MHz (up to 3.4MHz for local bus access)
  - High-speed GPIOs
  - Supports SPI and UART pass-through GPIOs
- Backwards compatibility
  - Integrated HDCP v1.4 with on-chip keys
  - 720p 92x and 1080p/2K 94x FPD-Link III product families
- Security and diagnostics
  - Link diagnostics
  - Voltage and temperature monitoring
  - BIST and pattern generation
  - CRC and error diagnostics
  - ECC on control bits
  - Unique ID for counterfeit protection
- Advanced link robustness and EMC control
  - Spread Spectrum Clocking Generation (SSCG)
  - Adaptive Receiver Equalization (AEQ)
- Low power operation
  - 1.8V and 1.15V dual power supply
- AEC-Q100 qualified for automotive applications
  - AEC-Q Grade-Level 2, –40°C to 105°C
  - ISO 10605 and IEC 61000-4-2 ESD compliant

## 2 Applications

- Automotive Displays:
  - Central Information Displays (CID)
  - Rear Seat Entertainment (RSE)
  - Digital instrument clusters
  - Head units and HMI modules
  - Head Up Display (HUD)
  - Rear view and side mirror displays

## 3 Description


The DS90UH988-Q1 is an FPD-Link IV to OpenLDI bridge device. In conjunction with an FPD-Link IV serializer, the chipset receives a high-speed serialized interface over low-cost 50Ω coax or STP/STQ cables. The DS90UH988-Q1 supports OpenLDI (10 LVDS data lanes + 2 clocks) interface with video up to 420MHz PCLK. This provides a bridge between sources such as GPUs to connect to existing LVDS based displays or application processors.

The FPD-Link IV interface supports video and audio data transmission and full duplex control, including I2C, and GPIO data over the same link. Consolidation of video and control data over FPD-Link IV lanes reduces the interconnect size and weight and simplifies system design. EMI is minimized by the use of low voltage differential signaling, data scrambling, and randomization. In backward compatible FPD-Link III mode, the device supports up to 2K resolutions with 24-bit color depth over a single/dual link as well as HDCP v1.4 support when paired with an HDCP capable serializer.

#### **Package Information**

PART NUMBER	PACKAGE (1)	PACKAGE SIZE <sup>(2)</sup>		
DS90UH988-Q1	RUR (VQFNP, 88)	12mm × 12mm		

- For all available packages, see Section 6. (1)
- The package size (length × width) is a nominal value and (2) includes pins, where applicable.



**Applications Diagram** 



# **Table of Contents**

1 Features	4.2 Community Resources
2 Applications	4.3 Trademarks
3 Description	
4 Device and Documentation Support3	
4.1 Documentation Support3	



## **4 Device and Documentation Support**

### 4.1 Documentation Support

#### 4.1.1 Related Documentation

For related documentation see the following:

- Texas Instruments, Soldering Specifications application note
- Texas Instruments, Semiconductor and IC Package Thermal Metrics application note
- Texas Instruments, Leadless Leadframe Package (LLP) application note
- · Texas Instruments, LVDS Owner's Manual
- Texas Instruments, I2C Communication Over FPD-Link III with Bidirectional Control Channel application note
- Texas Instruments, Exploring the Internal Test Pattern Generation Feature of 720p FPD-Link III Devices application note
- Texas Instruments, I2C Bus Pullup Resistor Calculation application note
- · Texas Instruments FPD-Link Learning Center, FPD-Link Fundamental Material video series
- Texas Instruments, Ten tips for successfully designing with automotive EMC/EMI requirements
- Texas Instruments, Serial Line-Fault Detection (Contact TI)

### **4.2 Community Resources**

#### 4.3 Trademarks

All trademarks are the property of their respective owners.

#### 5 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

DATE	REVISION	NOTES					
February 2024	*	Initial Release					



# 6 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated

www.ti.com 24-Apr-2024

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
DS90UH988RURRQ1	ACTIVE	VQFNP	RUR	88	2500	RoHS & Green	NIPDAUAG	Level-3-260C-168 HR	-40 to 105	UH988	Samples
DS90UH988RURTQ1	ACTIVE	VQFNP	RUR	88	250	RoHS & Green	NIPDAUAG	Level-3-260C-168 HR	-40 to 105	UH988	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



# **PACKAGE OPTION ADDENDUM**

www.ti.com 24-Apr-2024

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 25-Apr-2024

### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DS90UH988RURRQ1	VQFNP	RUR	88	2500	330.0	24.4	12.3	12.3	1.1	16.0	24.0	Q2
DS90UH988RURTQ1	VQFNP	RUR	88	250	180.0	24.4	12.3	12.3	1.1	16.0	24.0	Q2

www.ti.com 25-Apr-2024




#### \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
DS90UH988RURRQ1	VQFNP	RUR	88	2500	367.0	367.0	35.0
DS90UH988RURTQ1	VQFNP	RUR	88	250	210.0	185.0	35.0

12 x 12, 0.5 mm pitch

PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated