

LM741QML Operational Amplifier

Check for Samples: [LM741QML](#)

FEATURES

The amplifier offers many features which make their application nearly foolproof: overload protection on the input and output, no latch-up when the common mode range is exceeded, as well as freedom from oscillations

DESCRIPTION

The LM741 is a general purpose operational amplifier which features improved performance over industry standards such as the LM709. They are direct, plug-in replacements for the 709C, LM201, MC1439 and 748 in most applications.

Connection Diagrams




Figure 1. Metal Can Package
See Package Number LMC0008C




Figure 2. Dual-In-Line Package
See Package Number NAB0008A




Figure 3. Ceramic Flatpak and SOIC Package
See Package Number NAD0010A & NAC0010A




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 2005–2013, Texas Instruments Incorporated

Schematic Diagram



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

Absolute Maximum Ratings⁽¹⁾

Supply Voltage			±22V
Power Dissipation ⁽²⁾			500 mW
Differential Input Voltage			±30V
Input Voltage ⁽³⁾			±15V
Output Short Circuit Duration			Continuous
Operating Temperature Range			−55°C ≤ T _A ≤ +125°C
Storage Temperature Range			−65°C ≤ T _A ≤ +150°C
Junction Temperature (T _J)			150°C
Lead Temperature (Soldering, 10 Seconds)			300°C
Thermal Resistance	θ _{JA}	Metal Can (Still Air)	167°C/W
		Metal Can (500LF / Min Air Flow)	100°C/W
		CERDIP (Still Air)	TBD
		CERDIP (500LF / Min Air Flow)	TBD
		CERPACK (Still Air)	228°C/W
		CERPACK (500LF / Min Air Flow)	154°C/W
		Ceramic SOIC (Still Air)	228°C/W
		Ceramic SOIC (500LF / Min Air Flow)	154°C/W
	θ _{JC}	Metal Can	44°C/W
		CERDIP	TBD
		CERPACK	27°C/W
		Ceramic SOIC	27°C/W
Package Weight (typical)	Metal Can		1000mg
	CERDIP		1100mg
	CERPACK		260mg
	Ceramic SOIC		225mg
ESD Tolerance ⁽⁴⁾			400V

- (1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not ensure specific performance limits. For ensured specifications and test conditions, see the Electrical Characteristics. The ensured specifications apply only for the test conditions listed. Some performance characteristics may degrade when the device is not operated under the listed test conditions.
- (2) The maximum power dissipation must be derated at elevated temperatures and is dictated by T_{Jmax} (maximum junction temperature), θ_{JA} (package junction to ambient thermal resistance), and T_A (ambient temperature). The maximum allowable power dissipation at any temperature is P_{Dmax} = (T_{Jmax} - T_A)/θ_{JA} or the number given in the Absolute Maximum Ratings, whichever is lower.
- (3) For supply voltages less than ±15V, the absolute maximum input voltage is equal to the supply voltage.
- (4) Human body model, 1.5 kΩ in series with 100 pF.

Quality Conformance Inspection

Mil-Std-883, Method 5005 - Group A

Subgroup	Description	Temp °C
1	Static tests at	25
2	Static tests at	125
3	Static tests at	-55
4	Dynamic tests at	25
5	Dynamic tests at	125
6	Dynamic tests at	-55
7	Functional tests at	25
8A	Functional tests at	125
8B	Functional tests at	-55
9	Switching tests at	25
10	Switching tests at	125
11	Switching tests at	-55
12	Settling time at	25
13	Settling time at	125
14	Settling time at	-55

Electrical Characteristics DC Parameters

The following conditions apply to all the following parameters, unless otherwise specified.

DC: $V_{CC} = \pm 15V$, $V_{CM} = 0V$

Symbol	Parameter	Conditions	Notes	Min	Max	Unit	Sub-group
V_{IO}	Input Offset Voltage	$V_{CM} = -12V$		-5.0	5.0	mV	1
				-6.0	6.0	mV	2, 3
		$V_{CM} = 12V$		-5.0	5.0	mV	1
				-6.0	6.0	mV	2, 3
		$+V_{CC} = \pm 5V$		-5.0	5.0	mV	1
				-6.0	6.0	mV	2, 3
				-5.0	5.0	mV	1
				-6.0	6.0	mV	2, 3
$-V_{IO} \text{ Adj}$	Offset Null				-6.0	mV	1, 2, 3
$+V_{IO} \text{ Adj}$	Offset Null			6.0		mV	1, 2, 3
I_{IO}	Input Offset Current	$V_{CM} = -12V$		-200	200	nA	1
				-500	500	nA	2, 3
		$V_{CM} = 12V$		-200	200	nA	1
				-500	500	nA	2, 3
		$V_{CC} = \pm 5V$		-200	200	nA	1
				-500	500	nA	2, 3
				-200	200	nA	1
				-500	500	nA	2, 3
$\pm I_{IB}$	Input Bias Current	$V_{CM} = -12V$		0.0	500	nA	1
				0.0	1500	nA	2, 3
		$V_{CM} = 12V$		0.0	500	nA	1
				0.0	1500	nA	2, 3
		$V_{CC} = \pm 5V$		0.0	500	nA	1
				0.0	1500	nA	2, 3
				0.0	500	nA	1
				0.0	1500	nA	2, 3

Electrical Characteristics DC Parameters (continued)

The following conditions apply to all the following parameters, unless otherwise specified.

DC: $V_{CC} = \pm 15V$, $V_{CM} = 0V$

Symbol	Parameter	Conditions	Notes	Min	Max	Unit	Sub-group
I_{CC}	Power Supply Current				2.8	mA	1
					2.5	mA	2
					3.5	mA	3
$+A_{VS}$	Open Loop Voltage Gain	$R_L = 2K\Omega$, $V_O = 0$ to $10V$	See ⁽¹⁾	50		V/mV	1
			See ⁽¹⁾	25		V/mV	2, 3
$-A_{VS}$	Open Loop Voltage Gain	$R_L = 2K\Omega$, $V_O = 0$ to $-10V$	See ⁽¹⁾	50		V/mV	1
			See ⁽¹⁾	25		V/mV	2, 3
$+PSRR$	Power Supply Rejection Ratio	$+V_{CC} = 15V$ to $5V$, $-V_{CC} = -15V$		77		dB	1, 2, 3
$-PSRR$	Power Supply Rejection Ratio	$-V_{CC} = -15V$ to $-5V$, $+V_{CC} = +15V$		77		dB	1, 2, 3
$CMRR$	Common Mode Rejection Ratio	$-12V \leq V_{CM} \leq 12V$		70		dB	1, 2, 3
$+I_{OS}$	Output Short Circuit Current			-45	-5.0	mA	1,2
				-50	-5.0	mA	3
$-I_{OS}$	Output Short Circuit Current			5.0	45	mA	1,2
				5.0	50	mA	3
$+V_{Opp}$	Output Voltage Swing	$R_L = 10K\Omega$		12		V	1, 2, 3
		$R_L = 2K\Omega$		10		V	1, 2, 3
		$V_{CC} = \pm 20V$, $R_L = 10K\Omega$		16		V	1, 2, 3
		$V_{CC} = \pm 20V$, $R_L = 2K\Omega$		15		V	1, 2, 3
$-V_{Opp}$	Output Voltage Swing	$R_L = 10K\Omega$			-12	V	1, 2, 3
		$R_L = 2K\Omega$			-10	V	1, 2, 3
		$V_{CC} = \pm 20V$, $R_L = 10K\Omega$			-16	V	1, 2, 3
		$V_{CC} = \pm 20V$, $R_L = 2K\Omega$			-15	V	1, 2, 3
R_i	Input Resistance		See ⁽²⁾	0.3		M Ω	1
V_I	Input Voltage Range	$V_{CC} = \pm 15V$	See ⁽³⁾	± 12		V	1, 2, 3
V_O	Output Voltage Swing	$V_{CC} = \pm 5V$	See ⁽²⁾	± 2.0		V	1, 2, 3

(1) Datalog reading in K = V/mV

(2) Specified parameter, not tested.

(3) Ensured by CMRR, I_B , I_O , V_{IO}

Electrical Characteristics AC Parameters

The following conditions apply to all the following parameters, unless otherwise specified.

AC: $V_{CC} = \pm 15V$, $V_{CM} = 0V$

Symbol	Parameter	Conditions	Notes	Min	Max	Unit	Sub-group
$+SR$	Slew Rate	$V_I = -5V$ to $5V$, $A_V = 1$, $R_L = 2K\Omega$		0.2		V/ μ S	7
$-SR$	Slew Rate	$V_I = 5V$ to $-5V$, $A_V = 1$, $R_L = 2K\Omega$		0.2		V/ μ S	7
t_R	Rise Time	$R_L = 2K\Omega$, $A_V = 1$, $C_L = 100pF$			1.0	μ S	7
OS	Overshoot	$R_L = 2K\Omega$, $A_V = 1$, $C_L = 100pF$			30	%	7
GBW	Gain Bandwidth	$V_I = 50mV_{RMS}$, $f = 20KHz$, $R_L = 2K\Omega$		250		KHz	-

Typical Application




Figure 4. Offset Nulling Circuit

REVISION HISTORY

Date Released	Revision	Section	Originator	Changes
08/22/05	A	New Release to the corporate format	L. Lytle	1 MDS datasheet converted into one corporate datasheet format. Since drift is not performed on 883 product, the table was removed. MNLM741-X Rev 1A0 will be archived.
03/26/13	A	All	-	Changed layout of National Data Sheet to TI format.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
LM741 MD8	Active	Production	DIESALE (Y) 0	400 JEDEC TRAY (5+1)	Yes	Call TI	Level-1-NA-UNLIM	-55 to 125	
LM741H/883	Active	Production	TO-99 (LMC) 8	20 JEDEC TRAY (5+1)	No	Call TI	Call TI	-55 to 125	LM741H/883 Q ACO LM741H/883 Q >T
LM741J/883	Active	Production	CDIP (NAB) 8	40 TUBE	No	Call TI	Call TI	-55 to 125	LM741J /883 Q ACO /883 Q >T

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μm)	B (mm)
LM741J/883	NAB	CDIP	8	40	506.98	15.24	13440	NA

TRAY




Chamfer on Tray corner indicates Pin 1 orientation of packed units.



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	Unit array matrix	Max temperature (°C)	L (mm)	W (mm)	K0 (μm)	P1 (mm)	CL (mm)	CW (mm)
LM741H/883	LMC	TO-CAN	8	20	2 X 10	150	126.49	61.98	8890	11.18	12.95	18.54

NAB0008A



CONTROLLING DIMENSION IS INCH
VALUES IN [] ARE MILLIMETERS



J08A (Rev M)

LMC0008A

TO-CAN - 5.72 mm max height

TRANSISTOR OUTLINE




1. All linear dimensions are in inches [millimeters]. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Pin numbers shown for reference only. Numbers may not be marked on package.
4. Reference JEDEC registration MO-002/TO-99.

EXAMPLE BOARD LAYOUT

LMC0008A

TO-CAN - 5.72 mm max height

TRANSISTOR OUTLINE



LAND PATTERN EXAMPLE
NON-SOLDER MASK DEFINED
SCALE: 12X

4220610/B 09/2024

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025