



**OPA4243** 

For most current data sheet and other product information, visit www.burr-brown.com

# Quad OPERATIONAL AMPLIFIER *Micro*POWER, Single-Supply

## **FEATURES**

- MICRO-SIZE, TSSOP PACKAGE
- SINGLE-SUPPLY OPERATION
- WIDE SUPPLY RANGE: 2.2V to 36V
- LOW QUIESCENT CURRENT: 45µA/chan
- WIDE BANDWIDTH: 430kHzWIDE INPUT/OUTPUT SWING


## **APPLICATIONS**

- LCD DISPLAY DRIVERS
- BATTERY POWERED SYSTEMS
- PORTABLE EQUIPMENT
- PCMCIA CARDS
- BATTERY PACKS AND POWER SUPPLIES
- CONSUMER PRODUCTS

### DESCRIPTION

The OPA4243 is a four-channel op amp specifically designed for high density, space-limited applications, such as LCD bias drivers, PCMCIA cards, battery-packs and portable instruments. In addition to small size, this part features wide output swing, very low quiescent current, and low bias current. Other features include unity gain stability and the best speed power ratio available. Power supplies in the range of 2.2V to 36V (±1.1V to ±18V) can be used.

Each channel uses completely independent circuitry for lowest crosstalk and freedom from interaction, even when overloaded. In addition, the amplifier is free from output inversion when the inputs are driven to the rail. The OPA4243EA is supplied in the miniature TSSOP-14 surface mount package. Specifications apply from -40°C to +85°C. However, as the extensive typical performance curves indicate, the OPA4243 can be used over the full -55°C to +125°C range. A SPICE macromodel is available for design analysis.



International Airport Industrial Park • Mailing Address: PO Box 11400, Tucson, AZ 85734 • Street Address: 6730 S. Tucson Blvd., Tucson, AZ 85706 • Tel: (520) 746-1111

Twx: 910-952-1111 • Internet: http://www.burr-brown.com/ • Cable: BBRCORP • Telex: 066-6491 • FAX: (520) 889-1510 • Immediate Product Info: (800) 548-6132

# SPECIFICATIONS: $V_S = +2.6V$ to +36V

Boldface limits apply over the specified temperature range,  $T_A = -40^{\circ}C$  to  $+85^{\circ}C$ 

At  $T_A$  = +25°C,  $R_L$  = 20k $\Omega$  connected to ground, unless otherwise noted.

	OPA4243EA					
PARAMETER		CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNITS
OFFSET VOLTAGE Input Offset Voltage Over Temperature vs Temperature vs Power Supply Over Temperature Channel Separation	V <sub>OS</sub> dV <sub>OS</sub> /dT PSRR	$V_S = \pm 7.5V$ , $V_{CM} = 0$ $T_A = -40^{\circ}C$ to $+85^{\circ}C$ $V_S = +2.6V$ to $+36V$ $V_S = +2.6V$ to $+36V$		±2 ± <b>2.5</b> 2.5	±5 ±6 100 100	mV mV μV/°C μV/V μV/V dB
INPUT BIAS CURRENT Input Bias Current Input Offset Current	I <sub>R</sub> I <sub>OS</sub>	$V_{CM} = V_S/2$ $V_{CM} = V_S/2$		-10 ±1	-25 ±10	nA nA
NOISE Input Noise Voltage, f = 0.1 to 10Hz Input Noise Voltage Density, f = 1kHz Current Noise Density, f = 1kHz	e <sub>n</sub> i <sub>n</sub>			0.4 22 40		μVp-p nV/√Hz fA/√Hz
INPUT VOLTAGE RANGE Common-Mode Voltage Range Common-Mode Rejection Over Temperature	V <sub>CM</sub> CMRR	$V_S = \pm 18V, \ V_{CM} = -18V \ to \ +17.1V$ $V_S = \pm 18V, \ V_{CM} = -18V \ to \ +17.1V$	0 82 <b>82</b>	104	(V+) - 0.9	V dB dB
INPUT IMPEDANCE Differential Common-Mode				10 <sup>6</sup>    2 10 <sup>9</sup>    2		Ω    pF Ω    pF
OPEN-LOOP GAIN Open-Loop Voltage Gain Over Temperature	A <sub>OL</sub>	$V_O = 0.5V$ to $(V+) - 0.9$ $V_O = 0.5V$ to $(V+) - 0.9$	86 <b>86</b>	104		dB dB
FREQUENCY RESPONSE Gain-Bandwidth Product Slew Rate Setting Time, 0.01% Overload Recovery Time	GBW SR	G = 1 10V Step V <sub>IN</sub> • Gain = V <sub>S</sub>		430 -0.1, ±0.16 150 8		kHz V/μs μs μs
OUTPUT Voltage Output, Positive Over Temperature Voltage Output, Negative Over Temperature Voltage Output, Positive Over Temperature Voltage Output, Negative Over Temperature Short-Circuit Current Capacitive Load Drive	V <sub>O</sub> I <sub>SC</sub> C <sub>LOAD</sub>	$\begin{array}{l} A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;V_S/2\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;V_S/2\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;V_S/2\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;V_S/2\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;Ground\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;Ground\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;Ground\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;Ground\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;Ground\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;Ground\\ A_{OL\geq}\:80dB,\;R_L=20k\Omega\;to\;Ground\\ \end{array}$	(V+) - 0.9 (V+) - 0.9 0.5 0.5	(V+) - 0.75 (V+) - 0.75 0.2 0.2 (V+) - 0.75 (V+) - 0.75 0.1 0.1 -25, +12 See Typical Curv	/e	V V V V V V mA
POWER SUPPLY Specified Voltage Range Minimum Operating Voltage Quiescent Current Over Temperature	V <sub>s</sub>	Over Temperature $I_O = 0$ $I_O = 0$	+2.6	+2.2 45	<b>+36</b> 60 <b>70</b>	V V μΑ μΑ
TEMPERATURE RANGE Specified Range Operating Range Storage Range Thermal Resistance	$ heta_{\sf JA}$		-40 -55 -65		85 125 150	°C °C °C
TSSOP-14 Surface Mount	VJA			100		°C/W

NOTE: (1)  $V_S = +15V$ .



#### ABSOLUTE MAXIMUM RATINGS(1)

Supply Voltage, V+ to V	36V
Input Voltage Range <sup>(2)</sup>	
Input Current <sup>(2)</sup>	10mA
Output Short-Circuit <sup>(3)</sup>	Continuous
Operating Temperature	55°C to +125°C
Storage Temperature	65°C to +150°C
Junction Temperature	150°C
Lead Temperature (soldering, 10s)	300°C
ESD Capability	2000V

NOTES: (1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. (2) Inputs are diode-clamped to the supply rails and should be current-limited to 10mA or less if input voltages can exceed rails by more than 0.3V. (3) Short-circuit to ground, one amplifier per package.



This integrated circuit can be damaged by ESD. Burr-Brown recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.


#### PACKAGE/ORDERING INFORMATION


PRODUCT	PACKAGE	PACKAGE DRAWING NUMBER	SPECIFIED TEMPERATURE RANGE	PACKAGE MARKING	ORDERING NUMBER <sup>(1)</sup>	TRANSPORT MEDIA
OPA4243EA	TSSOP-14	357 "	-40°C to +85°C	OPA4243EA "	OPA4243EA/250 OPA4243EA/2K5	Tape and Reel Tape and Reel


NOTE: (1) Models with a slash (/) are available only in Tape and Reel in the quantities indicated (e.g., /2K5 indicates 2500 devices per reel). Ordering 2500 pieces of "OPA4243EA" will get a single 2500-piece Tape and Reel.


## **TYPICAL PERFORMANCE CURVES**


At  $T_A = +25$ °C,  $R_1 = 20$ k $\Omega$  connected to ground, unless otherwise noted.


















## **TYPICAL PERFORMANCE CURVES (Cont.)**


At  $T_A$  = +25°C,  $R_L$  = 20k $\Omega$  connected to ground, unless otherwise noted.


















## **TYPICAL PERFORMANCE CURVES (Cont.)**


At  $T_A$  = +25°C,  $R_L$  = 20k $\Omega$  connected to ground, unless otherwise noted.
















## TYPICAL PERFORMANCE CURVES (Cont.)

At  $T_A = +25$ °C,  $R_L = 20$ k $\Omega$  connected to ground, unless otherwise noted.





### APPLICATION INFORMATION

The OPA4243 is unity-gain stable and suitable for a wide range of general-purpose applications. The power supply pins should be bypassed with 0.01µF ceramic capacitors.

#### **OPERATING VOLTAGE**

The OPA4243 can operate from single supply (2.2V to 36V) or dual supplies  $(\pm 1.1V \text{ to } \pm 18V)$  with excellent performance. Unlike most op amps which are specified at only one supply voltage, the OPA4243 is specified for real world applications; a single set of specifications applies throughout the 2.6V to 36V supply range. This allows the designer to have the same assured performance at any supply voltage within this range.

In addition, many key parameters are guaranteed over the specified temperature range, -40°C to +85°C. Most behaviors remain unchanged throughout the full operating voltage range. Parameters, which vary significantly with operating voltage or temperature, are shown in the typical performance curves.

#### PRINTED CIRCUIT BOARD LAYOUT

See Burr-Brown Application Note AB-132 for specific PC board layout recommendations.

#### INPUT PROTECTION

Rail-to-rail input signals will not cause damage or invert the output of the OPA4243. To protect against ESD and excessive input voltage (beyond the supply rails) the OPA4243 includes diodes from the input terminals to the power supply rails. Normally, these diodes are reversed biased and have negligible effect on circuit operation. However, if the input voltage is allowed to exceed the supply voltages by enough to forward bias these diodes (generally, 0.3V to 0.6V) excessive input current could flow. If this condition could occur (for example, if an input signal is applied when the op amp supply voltage is zero), care should be taken to limit the input current to less than 10mA to avoid damage. An input signal beyond the supplies, with power applied, can cause an unexpected output inversion.

7

www.ti.com 30-Jul-2024

#### PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
OPA4243EA/250	OBSOLETE	TSSOP	PW	14		TBD	Call TI	Call TI	-40 to 85	OPA 4243EA	
OPA4243EA/2K5	ACTIVE	TSSOP	PW	14	2500	RoHS & Green	NIPDAU	Level-3-260C-168 HR	-40 to 85	OPA 4243EA	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



## **PACKAGE OPTION ADDENDUM**

www.ti.com 30-Jul-2024

## **PACKAGE MATERIALS INFORMATION**

www.ti.com 30-May-2024

### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers


#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

Device	U	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
OPA4243EA/2K5	TSSOP	PW	14	2500	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1

www.ti.com 30-May-2024



#### \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
OPA4243EA/2K5	TSSOP	PW	14	2500	356.0	356.0	35.0

### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated