

































































































































































































































































































































































































































































































































**ARM Core Cortex™-A8 (AT400/AT401) Errata Notice.** Provides a list of advisories for the different revisions of the Cortex-A8 processor. Contact your TI representative for a copy of this document. Please see the *OMAP35x Applications Processor Silicon Errata* (literature number [SPRZ278](#)) to determine the revision of the Cortex-A8 core used on your device.

**PACKAGING INFORMATION**

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins           | Package qty   Carrier     | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------|---------------|----------------------|--------------------------|---------------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">OMAP3503ECBB</a>   | Active        | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | 0 to 90      | 3503ECBB            |
| OMAP3503ECBB.B                 | Active        | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | 0 to 90      | 3503ECBB            |
| <a href="#">OMAP3503ECBBA</a>  | Active        | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | -40 to 105   | 3503ECBB<br>A       |
| OMAP3503ECBBA.B                | Active        | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | -40 to 105   | 3503ECBB<br>A       |
| OMAP3503ECBBALPD               | Active        | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | -40 to 105   | 3503ECBB<br>A       |
| <a href="#">OMAP3503ECUS</a>   | Active        | Production           | FCCSP (CUS)   423        | 90   JEDEC<br>TRAY (5+1)  | Yes         | SNAGCU                               | Level-4-260C-72 HR                | 0 to 90      | 3503ECUS            |
| OMAP3503ECUS.B                 | Active        | Production           | FCCSP (CUS)   423        | 90   JEDEC<br>TRAY (5+1)  | Yes         | SNAGCU                               | Level-4-260C-72 HR                | 0 to 90      | 3503ECUS            |
| <a href="#">OMAP3503ECUS72</a> | Active        | Production           | FCCSP (CUS)   423        | 90   JEDEC<br>TRAY (5+1)  | Yes         | SNAGCU                               | Level-4-260C-72 HR                | 0 to 90      | 3503ECUS72          |
| OMAP3503ECUS72.B               | Active        | Production           | FCCSP (CUS)   423        | 90   JEDEC<br>TRAY (5+1)  | Yes         | SNAGCU                               | Level-4-260C-72 HR                | 0 to 90      | 3503ECUS72          |
| <a href="#">OMAP3503ECUSA</a>  | Active        | Production           | FCCSP (CUS)   423        | 90   JEDEC<br>TRAY (5+1)  | Yes         | SNAGCU                               | Level-4-260C-72 HR                | -40 to 105   | 3503ECUS<br>A       |
| OMAP3503ECUSA.B                | Active        | Production           | FCCSP (CUS)   423        | 90   JEDEC<br>TRAY (5+1)  | Yes         | SNAGCU                               | Level-4-260C-72 HR                | -40 to 105   | 3503ECUS<br>A       |
| OMAP3515ECBB                   | NRND          | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | 0 to 0       | 3515ECBB            |
| OMAP3515ECBB.B                 | NRND          | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | 0 to 0       | 3515ECBB            |
| <a href="#">OMAP3515ECBBA</a>  | Active        | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | -40 to 105   | 3515ECBB<br>A       |
| OMAP3515ECBBA.B                | Active        | Production           | POP-FCBGA<br>(CBB)   515 | 168   JEDEC<br>TRAY (5+1) | -           | SNAGCU                               | Level-3-260C-168 HR               | -40 to 105   | 3515ECBB<br>A       |
| <a href="#">OMAP3515ECUS</a>   | Active        | Production           | FCCSP (CUS)   423        | 90   JEDEC<br>TRAY (5+1)  | Yes         | SNAGCU                               | Level-4-260C-72 HR                | 0 to 90      | 3515ECUS            |

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins    | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------|---------------|----------------------|-------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| OMAP3515ECUS.B                 | Active        | Production           | FCCSP (CUS)   423 | 90   JEDEC TRAY (5+1) | Yes         | SNAGCU                               | Level-4-260C-72 HR                | 0 to 90      | 3515ECUS            |
| <a href="#">OMAP3515ECUS72</a> | Active        | Production           | FCCSP (CUS)   423 | 90   JEDEC TRAY (5+1) | Yes         | SNAGCU                               | Level-4-260C-72 HR                | 0 to 90      | 3515ECUS72          |
| OMAP3515ECUS72.B               | Active        | Production           | FCCSP (CUS)   423 | 90   JEDEC TRAY (5+1) | Yes         | SNAGCU                               | Level-4-260C-72 HR                | 0 to 90      | 3515ECUS72          |
| <a href="#">OMAP3515ECUSA</a>  | Active        | Production           | FCCSP (CUS)   423 | 90   JEDEC TRAY (5+1) | Yes         | SNAGCU                               | Level-4-260C-72 HR                | -40 to 105   | 3515ECUS<br>A       |
| OMAP3515ECUSA.B                | Active        | Production           | FCCSP (CUS)   423 | 90   JEDEC TRAY (5+1) | Yes         | SNAGCU                               | Level-4-260C-72 HR                | -40 to 105   | 3515ECUS<br>A       |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.


<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**TRAY**


Chamfer on Tray corner indicates Pin 1 orientation of packed units.


\*All dimensions are nominal

| Device           | Package Name | Package Type | Pins | SPQ | Unit array matrix | Max temperature (°C) | L (mm) | W (mm) | K0 (μm) | P1 (mm) | CL (mm) | CW (mm) |
|------------------|--------------|--------------|------|-----|-------------------|----------------------|--------|--------|---------|---------|---------|---------|
| OMAP3503ECBB     | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3503ECBB.B   | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3503ECBBA    | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3503ECBBA.B  | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3503ECBBALPD | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3503ECUS     | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3503ECUS.B   | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3503ECUS72   | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3503ECUS72.B | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3503ECUSA    | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3503ECUSA.B  | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3515ECBB     | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3515ECBB.B   | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3515ECBBA    | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3515ECBBA.B  | CBB          | FCCSP        | 515  | 168 | 8X21              | 150                  | 315    | 135.9  | 7620    | 14.65   | 11      | 11.95   |
| OMAP3515ECUS     | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3515ECUS.B   | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |

| Device           | Package Name | Package Type | Pins | SPQ | Unit array matrix | Max temperature (°C) | L (mm) | W (mm) | K0 (µm) | P1 (mm) | CL (mm) | CW (mm) |
|------------------|--------------|--------------|------|-----|-------------------|----------------------|--------|--------|---------|---------|---------|---------|
| OMAP3515ECUS72   | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3515ECUS72.B | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3515ECUSA    | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |
| OMAP3515ECUSA.B  | CUS          | FCCSP        | 423  | 90  | 6 X 15            | 150                  | 315    | 135.9  | 7620    | 20      | 17.5    | 15.45   |

CBB (S-PBGA-N515)

PLASTIC BALL GRID ARRAY




4207818-2/H 06/09

- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Flip chip application only.
  - D. Pb-free die bump and solder ball.

CUS (S-PBGA-N423)

PLASTIC BALL GRID ARRAY




4207880/C 12/07

- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Flip chip application only.
  - D. Lead-free die bump and solder ball.

CBC (S-PBGA-N515)

PLASTIC BALL GRID ARRAY



4208336/C 04/08

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025