

New Product Update

Low-power, 77-GHz mmWave radar sensors level up industrial sensing

Trevor Dowd

Radar Industrial

What is mmWave radar?

mmWave radar is used to sense people and objects:


- Range
- Velocity
- Angle

Traditionally, 77-GHz radar has been used in automotive applications but has also been growing for non-automotive applications like:

- Level sensing
- Off-highway vehicles
- Parking barriers
- ebikes and other mobility solutions



Industrial radar 60GHz/77GHz | portfolio overview



- **Frequency regulation agnostic design** : Pin-to-pin compatibility with 60GHz and 77GHz sensors.
- **One Software Investment**: Common software API and framework across 60GHz/77GHz devices make software re usable and portable across devices.
- **Safety story**: SIL 2 level for Industrial safety applications

IWRL1432 | product overview

Designed for **small form factor**, **low BOM** cost and **lower power** applications

Integrated transceivers:

- 3 Rx and 2 Tx

Integrated frequency synthesizer:

- 77GHz to 81GHz

Processing:

- Arm® Cortex®-M4F MCU @ 160 MHz
- Integrated FFT, CFAR-CA HWAs

Memory:

- 1.0 MB SRAM

Interfaces:


- SPI, UART, I2C, QSPI, GPIOs

System simplification:

- Multiple power modes to enable ultra-low power
- One, two or three power-rail topologies (1.8V, 1.2V, 3.3V)

Package:

- 6.45 x 6.45 mm FCCSP (0.5mm pitch) -- [Samples Now](#)



Sample/EVM: Now

Production: 2024

* Early production options available

Level sensing



- Contactless measurement of liquids, solids, and powders up to 100m
- Immune to foam, vapor, powder, dust, condensates
- Minimal influence by temperature and pressure
- Targeting 4-20mA loop powered systems
- <4mJ / measurement
- <1mm accuracy
- SIL-2 certified

Other applications

Off-highway vehicles

- Agriculture
- Construction
- Forklifts
- Etc.


Mobility solution sensors

- ebikes
- Scooters
- Etc.

Parking barrier sensors



High accuracy low power sensor | lab



High accuracy example uses a ZoomFFT

ZoomFFTs use 2 FFTs

- 1 coarse FFT to find a peak (or multiple)
- A zoomed-in FFT, analyzing a portion of the peak at much higher resolution

This is how to achieve accuracy of <1mm

IWRL1432BOOST | evaluation module

Operates in the 76-81 GHz band



Compatible with

- DCA1000 EVM for raw ADC data capture
- MCU LaunchPad™ development kit ecosystem

Interfaces:

- LIN
- CAN
- UART
- SPI
- LVDS
- DCA1000 data capture interface
- Booster / LaunchPad connector

Angular resolution of 29° in azimuth and 58° in elevation



Development resources



Radar Academy

Learn mmWave radar fundamentals
Modules, videos, app notes

The screenshot shows the 'Resource Explorer' interface with the 'Radar Academy' page selected. The left sidebar lists various development resources. The main content area features a header 'Radar Academy' with a description: 'The Radar Academy is a collection of training modules for all developers to learn about TI's radar sensor offering and the underlying mmWave Radar technology. The academy explores the technical foundation of mmWave sensing and demonstrates how this can be leveraged with TI's radar sensor portfolio.' Below this is a search bar and a section titled 'Introduction' with three modules: 'MODULE 1 Overview', 'MODULE 2 Fundamentals of FMCW Radar', and 'MODULE 3 Terminology'.



Radar Toolbox

Demonstrate and develop radar solutions
Examples, software, labs

The screenshot shows the 'Resource Explorer' interface with the 'Radar Toolbox' page selected. The left sidebar lists various development resources. The main content area features a header 'Radar Toolbox for mmWave Sensors' with buttons for 'Discover', 'Evaluate', and 'Design'. Below this is a section titled 'Featured Content' with three featured items: 'IWRL6432 Now Available!', 'Radar for Video Doorbells', and 'In-Cabin Radar Sensing'. Each item includes a brief description and a 'Works with' link. At the bottom, there is a section for 'Application Overviews'.

Links to learn more

Content type	Title	Link to content / details
Product page	IWRL1432	Link
Evaluation module	IWRL1432BOOST EVM	Link
Development tools	Radar Toolbox	Link
Radar education modules	Radar Academy	Link

Visit **www.ti.com/npu**

For more information on the New Product Update series, calendar and archived recordings



© Copyright 2023 Texas Instruments Incorporated. All rights reserved.

This material is provided strictly “as-is,” for informational purposes only, and without any warranty.
Use of this material is subject to TI’s **Terms of Use**, viewable at [TI.com](https://www.ti.com)

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2023, Texas Instruments Incorporated