

Variant: 001
 Generated: 1/2/2025 3:35 PM
 TID #: N/A



PMP411145 REV E1 Bill of Materials

| Item # | Designator | Quantity | Value | PartNumber | Manufacturer | Description | PackageReference |
|--------|-------------|----------|-------------|-------------------------|---------------------------|--|------------------|
| 1 | C1 | 1 | 330nF | MX2334KQ3B83YB2000R | DongGuan Chengxi | X2 Film Capacitor, THT, 330nF, 275V | 10*14*6mm |
| 2 | C2 | 1 | 0.033uF | CGA2B3X7R1H333K050BB | TDK | CAP, CERM, 0.033 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402 | 0402 |
| 3 | C3 | 1 | 1000pF | GRM31BR72J102KW01L | MuRata | CAP, CERM, 1000 pF, 630 V, +/- 10%, X7R, 1206 | 1206 |
| 4 | C4 | 1 | 10uF | TMK212BBJ106KG-T | Taiyo Yuden | CAP, CERM, 10 uF, 25 V, +/- 10%, X5R, 0805 | 0805 |
| 5 | C6 | 1 | 100nF | CGA3E2X8R1E104K080AD | TDK Corporation | 0.1µF ±10% 25V Ceramic Capacitor X8R 0603 (1608 Metric) | 0603 |
| 6 | C8, C9, C64 | 3 | 33uF | KCMD2002G330MF | Yongming | KCMD2002G330MF Aluminum Electrolytic Capacitor, Radial, THT, D8 x H20mm, 33µF, 400V | D8*20mm |
| 7 | C13 | 1 | 220pF | GRM1885C2A221JA01D | MuRata | CAP, CERM, 220 pF, 100 V, +/- 5%, COG/NP0, 0603 | 0603 |
| 8 | C14 | 1 | 1uF | CGA3E1X7R1E105K080AC | TDK | CAP, CERM, 1 µF, 25 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0603 | 0603 |
| 9 | C15 | 1 | 22uF | CL10A226MP8NUNE | Samsung Electro-Mechanics | CAP, CERM, 22 uF, 10 V, +/- 20%, X5R, 0603 | 0603 |
| 10 | C16 | 1 | 330pF | GRM155R71H331KA01D | MuRata | CAP, CERM, 330 pF, 50 V, +/- 10%, X7R, 0402 | 0402 |
| 11 | C17 | 1 | 1uF | C1608X7R1E105K080AB | TDK | CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603 | 0603 |
| 12 | C19, C22 | 2 | 0.1uF | C3216X7T2W104M160AA | TDK | CAP, CERM, 0.1 uF, 450 V, +/- 20%, X7T, 1206 | 1206 |
| 13 | C20 | 1 | 4700pF | GRM155R71H472KA01D | MuRata | CAP, CERM, 4700 pF, 50 V, +/- 10%, X7R, 0402 | 0402 |
| 14 | C21 | 1 | 100pF | 8.85012E+11 | Würth Elektronik | CAP, CERM, 100 pF, 50 V, +/- 10%, X7R, 0402 | 0402 |
| 15 | C24, C25 | 2 | 8.85352E+12 | 8.85352E+12 | Würth Elektronik | WCAP-CSSA Multilayer Ceramic Chip Safety Capacitor, size 1808, X7R Class II, 1nF, 250VAC | |
| 16 | D1 | 1 | | Z4DGP406L-HF | Comchip | Bridge Rectifier Single Phase Standard 600 V Surface Mount Z4-D | SMT_8MM1_10MM5 |
| 17 | D3 | 1 | 1000V | MRA4007T3G | ON Semiconductor | Diode, Standard Recovery Rectifier, 1000 V, 1 A, AEC-Q101, SMA | SMA |
| 18 | D4, D5 | 2 | 600V | ES1JFL | ON Semiconductor | Diode, Switching, 600 V, 1 A, SOD-123 | SOD-123 |
| 19 | EC6, EC7 | 2 | 470uF | NPXC1001E471MJTM | Yongming | 25V/470uF D5.5*11mm | D5.5*11 |
| 20 | F1 | 1 | | RSTA 3.15-BULK | Bel Fuse | Fuse, 3.15 A, 250 VAC, 63 VDC, TH | 8.35x4mm |
| 21 | L1 | 1 | 33uH | RL0612-330K-HF | Huizhou Deli Electronics | Inductor, Unshielded Drum Core, 6*12mm, 33 uH, 2 A, TH RL0612-330K-HF | D6mm x 12mm |
| 22 | L2 | 1 | 22uH | TCB8X4X3-8R0MINX2-JS-HF | Huizhou Deli Electronics | 8*5mm CM choke 22uH, 0.5 wire* 6T, TCB8X4X3-8R0MINX2-JS-HF | 8mm*5mm |
| 23 | Q1 | 1 | 150V | ISC030N10NM6 | Infineon Technologies | MOSFET, N-CH, 100 V, 3.3mR, PG-TDSON-8 | PG-TDSON-8 |
| 24 | R1 | 1 | 470k | CRCW0805470KJNEA | Vishay-Dale | RES, 470 k, 5%, 0.125 W, AEC-Q200 Grade 0, 0805 | 0805 |
| 25 | R3, R17 | 2 | 30 | RC1206FR-0730RL | Yageo America | RES, 30.0, 1%, 0.25 W, 1206 | 1206 |
| 26 | R4 | 1 | 300 | RC0603FR-07300RL | Yageo | RES, 300, 1%, 0.1 W, 0603 | 0603 |
| 27 | R5 | 1 | 4.7k | CRCW1206470KJNEA | Vishay-Dale | RES, 4.7 k, 5%, 0.25 W, 1206 | 1206 |
| 28 | R6 | 1 | 47.0k | CRCW060347K0FKEA | Vishay-Dale | RES, 47.0 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603 | 0603 |
| 29 | R7, R8 | 2 | 28.7k | CRCW0402287FKED | Vishay-Dale | RES, 28.7 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402 | 0402 |
| 30 | R9, R12 | 2 | 0 | CRCW04020000Z0EDHP | Vishay Dale | RES Thick Film, 0Ω, 0.2W, 0402 | 0402 |
| 31 | R10 | 1 | 3.01k | CRCW04023K01FKED | Vishay-Dale | RES, 3.01 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402 | 0402 |
| 32 | R11 | 1 | 232k | RC0603FR-07232KL | Yageo America | RES, 232 k, 1%, 0.1 W, 0603 | 0603 |
| 33 | R14 | 1 | 15.0k | CRCW040215K0FKED | Vishay-Dale | RES, 15.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402 | 0402 |
| 34 | R15 | 1 | 4.70k | RC0402FR-074K7L | Yageo America | RES, 4.70 k, 1%, 0.0625 W, 0402 | 0402 |
| 35 | R18 | 1 | 1.2k | CRCW04021K20JNED | Vishay-Dale | RES, 1.2 k, 5%, 0.063 W, 0402 | 0402 |
| 36 | R19 | 1 | 33.0k | CRCW060333K0FKEA | Vishay-Dale | RES, 33.0 k, 1%, 0.1 W, 0603 | 0603 |
| 37 | R21 | 1 | 0 | CRCW02010000Z0ED | Vishay-Dale | RES, 0, 5%, 0.05 W, 0201 | 0201 |
| 38 | R42 | 1 | 11.5k | CRCW040211K5FKED | Vishay-Dale | RES, 11.5 k, 1%, 0.063 W, 0402 | 0402 |
| 39 | R43 | 1 | 25.5k | CRCW040225K5FKED | Vishay-Dale | RES, 25.5 k, 1%, 0.063 W, 0402 | 0402 |
| 40 | R50 | 1 | 12 | CRCW060312R0JNEA | Vishay-Dale | RES, 12, 5%, 0.1 W, 0603 | 0603 |
| 41 | T1 | 1 | | ATQ23-14 | Fort Electronics | ATQ23_14 4 4 Pin | 23*14*18mm |
| 42 | U1 | 1 | | MP6908GJ-Z | Monolithic Power Systems | FAST TURN-OFF INTELLIGENT RECTIF | TSOT23-6 |
| 43 | U2 | 1 | | ATL431AIDBZR | Texas Instruments | 2.5V Low Iq Adjustable Precision Shunt Regulator, DBZ0003A (SOT-23-3) | DBZ0003A |
| 44 | U3 | 1 | | VOL618A-2T | Vishay-Semiconductor | Optocoupler, 5 kV, 63-125% CTR, SMT | 8x2x4mm |
| 45 | U8 | 1 | | UCG28826 | Texas Instruments | UCG28826 | VQFN12 |
| 46 | C222 | 0 | 100pF | 8.85012E+11 | Würth Elektronik | CAP, CERM, 100 pF, 50 V, +/- 10%, X7R, 0402 | 0402 |
| 47 | R2 | 0 | 0 | CRCW04020000Z0EDHP | Vishay Dale | RES Thick Film, 0Ω, 0.2W, 0402 | 0402 |
| 48 | R16 | 0 | 1 | CRCW04021R00JNED | Vishay-Dale | RES, 1.0, 5%, 0.063 W, 0402 | 0402 |
| 49 | RT1 | 0 | 100k | NCP15WF104F03RC | MuRata | Thermistor NTC, 100k ohm, 1%, 0402 | 0402 |

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2025, Texas Instruments Incorporated

DRAFT
TI Confidential – NDA Restrictions

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2025, Texas Instruments Incorporated