

**UC3840/UC3841/UC3851 PWM CONTROLLERS
SUMMARY OF FUNCTIONS AND DIFFERENCES**

The UC3840/UC3841 and UC3851 PWM controllers incorporate numerous protection features for switch mode power supplies. The list includes programmable undervoltage lockout thresholds, programmable current limit thresholds, overvoltage protection, soft-start and external stop/reset capability. While these controllers are similar in concept, there are subtle differences amongst

them in the operation of the error latch circuitry, specifically, the external stop and reset inputs. The UC3841 and UC3851 ICs feature an improved circuit design which simplifies the interface to the internal protection circuitry. A summary of the functions and modes of operation is listed below.

EXTERNAL STOP

	UC3840	UC3841/51
Low (<0.8V)	Stop	Defeat E/L Operation
High	Normal	Stop
Open	Normal	Normal
Cap. to GND During Power-up	Not Recommended	Delay E/L Operation at $\approx 13\text{msec}/\mu\text{F}$

E/L= Error Latch

RESET

	UC3840	UC3841/51
High (>3.2V)	Latch	Latch
Low (<2.8V)	Requires UV Cycle to Reset	Reset

SOFT START

	UC3840	UC3841/51
After UV or Reset	Unlatched	Latched ($V_{ss} \leq 0.40\text{V}$)

The UC3851 controller incorporates two additional features, a toggle flip-flop for an accurate 50% maximum duty cycle clamp, and a 1 amp peak totem-pole output for

driving power MOSFETs. Maximum duty cycles and output configurations for each device is shown below.

MAXIMUM DUTY CYCLE ($T_J = 25^\circ\text{C}$)

	UC3840/41	UC3851
$R_T = 20\text{k}$, $C_T = 1\text{nF}$	0-95%	0-46%

PWM OUTPUT

	UC3840/41	UC3851
1A (PK)	Open Collector Active Low	Totem Pole Active High

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.