Bill Of Materials December 7,2005 12:47:46

Item		Reference	Part		ootprint	Part Description	Power			Manufacturer
	1 27	7 C2,C4,C6,C7,C8,C9,C11,	0.1uF	SN	MD0603-A-1	CAP, SMD, Ceramic, 0603	1	20%	16V	
		C12,C14,C15,C52,C53,C54,								
		C55,C56,C57,C59,C60,C89,								
		C90,C92,C93,C94,C103,								
		C104,C107,C108								
	2	1 C3	10uF	SI	MD07343					
		C28,C29,C30,C31	33U-7343		MD07343	C/C/ SMD, Tan, 7343		20%	25\/	
	-	2 C33,C35	33PF		MD0805-A-1	CAP, SMD, Ceramic, 0805		10%		
		1 C40	33uF			CAF, SIVID, Ceramic, 0005		10 /6	30 V	
					MD3528-B-1					
		1 C41	68uF		MD3528-B-1					
	l l	2 C87,C88	1500pF		MD1808-A-1	CAP, SMD, Ceramic, 1808		10%		
	-	1 C91	10uF		MD3528-B-1	CAP, SMD, Tant, 3528		10%		
		C105,C106,C109,C110	0.001uF		MD0603-A-1	CAP, SMD, Ceramic, 0603		20%	16V	
1		C111,C112,C113	100nF	SN	MD0603-A1					
1	1 1	1 C114	10uF	SN	MD3528-B-1					
1	2 6	D2,D3,D4,D5,D6,D7	Bicolor-LEDs	70	011X5/7	Digikey L61057CT_ND				
1	3 2	2 D9,D8	Ultra Bright Red	Pa	anasonic LNJ211R82RA					
1		1 D10	LTM673		SRAM LTM673	Hyper-Bright LED				OSRAM/LTM673-R1S2-35
1	l l	1 J 1	HDR-3X3		DR-3X3	7, 3				
1	-		CON2x5 TH		n-hdr2x5					
1		7 J4,J23,J36,J37,J40,J41,	HDR-1X2		N-HDR1X2					
	'l ''	J48,J49,J50,J51,J52,J55,	TIDIT-TAZ	01	N-HBICIA2					
		J56,J57,J58,J90,J92	LIDD OVOC	C.	N-MII-40P-RA-M					
1		2 J13,J7	HDR-2X20	-						
1	9 2	2 J8,J10	HDR-1X3		N-HDR1X3					
2		2 J9,J14	CON-MII-MALE		N-MII-40P-RA-M					
2		1 J26	HDR2X2		N-HDR2X2					
2		3 J42,J43,J44,J45,J46,J47	HDR_1X3		N-HDR1X3					
2		2 J84,J85	CON-RJ45	CN	N-PHONE8P8C-RA-SHLD	RJ-45 Connector				
2	4 1	1 J89	HFBR-5803	HF	FBR-5803 SC Connector					
2	5	1 J91	POE Connector	Su	ullins PPPC071LGBN					
2		1 J93	HDR2X5	CN	N-HDR2X5					
2	7 2	2 L1,L2	1uH	Мі	urata LQM21N Series	LQM21NN1R0K10D Ferrite Inductor				Murata LQM21NN1R0K10D
2		1 R1	1.5K		MD805-A-1	RES, SMD, 0805	1/10W	1%		
2		1 R20	4.87K 1%		MD0603-A-1	RES, SMD, 0603	1/16W	1%		
3		R43,R44,R45,R46,R47,R50,	1.0710 170		MD0603-A-1	RES, SMD, 0603	1/16W	5%		
3		R51,R52,R53,R54		33 31	WID0003-A-1	INES, SIMD, 0003	17 10 00	370		
3	4	7 R56,R92,R96,R101,R110,	Open	CV	MD0603 A 1	DES SMD 0603	1/16W	5%		
3	'  '		Open	SI	MD0603-A-1	RES, SMD, 0603	1/1000	3%		
		R112,R128	4014	٥.	150000 1 1					
		1 R63	10K		MD0603-A-1					
3	3 25	R86,R87,R88,R93,R94,R95,	2.2K	SN	MD0603-A-1	RES, SMD, 0603	1/16W	5%		
		R97,R98,R103,R104,R105,								
		R106,R111,R113,R117,R118,								
		R119,R120,R125,R126,R127,								
		R129,R133,R134,R149								
3	4 13	R89,R91,R99,R102,R107,		165 SN	MD0603-A-1	RES, SMD, 0603	1/16W	1%		
		R109,R114,R116,R122,R124,								
		R130,R132,R236								
3	5 8	R135,R136,R137,R138,R143,	4	49.9 SN	MD0603-A-1	RES, SMD, 0603	1/16W	1%		
		R144,R145,R146				, in the second		.,.		
3	6 8	R157,R158,R159,R160,R161,		75 SN	MD0603-A-1	RES, SMD, 0603	1/16W	1%		
3	i i	R162,R163,R164		75 01	WID0003-A-1	TCO, GWID, GGGG	17 10 00	1 70		
3	7 .	R162,R163,R164 2 R166,R165		50 64	MD0603-A-1	RES, SMD, 0603	1/16W	1%		
	l l									
		R167,R168,R171,R172,R217	0		MD0603-A-1	RES, SMD, 0603	1/16W	1%		
3	9 12	2 R169,R170,R181,R182,R185,	Open	SN	MD0603-A-1	RES, SMD, 0603	1/16W	1%		
		R186,R226,R227,R228,R229,					1			
		R237,R238								
4	0 9	R173,R174,R175,R176,R177,		0 SN	MD0603-A-1	RES, SMD, 0603	1/16W	1%		
		R178,R179,R180,R239								

41	5 R183,R184,R187,R188,R218	80	SMD0603-A-1	RES, SMD, 0603	1/16W	1%	
42	2 R223,R224	22	SMD0603-A-1	RES, SMD, 0603	1/16W	5%	
43	1 R225	10	SMD0603-A-1	RES, SMD, 0603	1/16W	5%	
44	1 R231	100	SMD0603-A1				
45	1 R232	1200	SMD0603-A1				
46	1 R233	33	SMD0603-A1				
47	2 R234,R235	210	SMD0603-A-1	RES, SMD, 0603	1/16W	5%	
48	2 T1,T2	H2019 (POE)	Pulse H1102/H2019	Magnetic			Pulse/H1102/H2019
49	1 U1	DP83849	VHB80A				
50	1 U3	LP3964 - 3.3V - 800mA	SOT223-5	Voltage Regulator 5V-3.3V			NSC/LP3964EMP-3.3
51	3 U4,U5,U6	NC7SZ126	SOT23-5				
52	1 X1	50 MHz	OSC14-4P	50 MHz Oscillator (50 ppm), 3.3V			
53	1 Y1	XTAL - 25M	HC49-US	Crystal, 25.000M			
54	14 J1 : 2-3, 5-6, 8-9 ; J8 MII_5V						Jumper setting
-	J23 MII_3V3; J92 MII_3V3				·	•	
	J10 : MII_VDD_B						

MII with Copper Configuration - Do Not Stuff Components

X1 R223, R224, R225, J90

J41; J42 HI; J43 HI; J44 HI J45 HI; J46 HI; J47 HI

R174, R175, R178, R179, R239

188

MII with Fiber Configuration - Do Not Stuff Components

X1 R223, R224, R225, J90 R173, R176, R177, R180

RMII with Copper Configuration - Do Not Stuff Components

Y1 C33, C35 J90 R174, R175, R178, R179, R239 J89

RMII with Fiber Configuration - Do Not Stuff Components

Y1 C33, C35 J90 R173, R176, R177, R180

## **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

Applications

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

**Products** 

OMAP Mobile Processors www.ti.com/omap

www.ti.com/wirelessconnectivity

Wireless Connectivity

		· ·pp···ou.io	
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		

TI E2E Community Home Page

e2e.ti.com