

TP3420

Interconnecting National's TP3420A SID to Motorola SCP/HDLC Devices



Literature Number: SNOA825

Interconnecting National Semiconductor's TP3420A SID to Motorola SCP/HDLC Devices

National Semiconductor
 Application Note 931
 Raj Paripatyadar
 Victor Thang Van
 July 1994



Interconnecting National Semiconductor's TP3420A SID to Motorola SCP/HDLC Devices AN-931

AN-931

When interconnecting the National Semiconductor's TP3420A to a Motorola SCP/HDLC device (such as the MC68302), it is necessary to consider the timings for two separate ports. The MICROWIRE™ to SCP connections for the device control and secondly the transfer to B and D channel data between the HDLC ports and the TP3420A Digital System Interface prot.

MICROWIRE/SCP CONNECTIONS

NSC MICROWIRE and Motorola Serial Control Port (SCP) are examples of serial communication formats typically used to configure Telecom/ISDN components. They both consist of a 5-pin port.

- Clock pin CCLK/SPCKL,
- Data input pin CI/SPRXD
- Data output pin CO/SPTXD
- A chip select pin/CS
- An interrupt line from the transceiver TP3420A to the controller to indicate a change of status.

There are 4 different modes for the relationship between the clock edges and data input/output for a serial communications port.

1. CCLK idling LOW, pulsing HIGH, then returning back to LOW for idle condition; data output on CO pin on the negative edge and data sampled in on the positive edge of CCLK (normal MICROWIRE mode).

2. CCLK idling HIGH, pulsing LOW, then returning back to HIGH for idle condition; data output on CO pin on the negative edge and data sampled in on the positive edge of CCLK (supported by enhanced MICROWIRE on TP3420A and SCP).
3. CCLK idling LOW pulsing HIGH, then returning back to LOW for idle condition; data output on CO pin on the positive edge and data sampled in on the negative edge of CCLK (supported only on the SCP).
4. CCLK idling HIGH, pulsing LOW, then returning back to HIGH for idle condition; data output on CO pin on the positive edge and data sampled in on the negative edge of CCLK.

The TP3420A SID supports modes 1 (NORMAL MICROWIRE mode) and mode 2. The SCP port of Mot 68302 supports modes 2 and 3. Hence set the SCP clock master to run in mode 2 above when interworking with the TP3420A (see *Figure 1* and *Figure 2*).

Set the 68302 SCP Master as follows:

Set CI = 1 in SPMODE register

Set the PM3-PM0 in SPMODE register to select clock rate (up to 2.048 MHz)

Use an I/O pin to perform chip select function \overline{CS} .

SCP port generates 8 clocks per command transfer which is compatible with the TP3420A.




FIGURE 1. MICROWIRE to SCP Connections

TRI-STATE® is a registered trademark of National Semiconductor Corporation.
 COMBO II™ and MICROWIRE™ are trademarks of National Semiconductor Corporation.




FIGURE 2. TP3420A MICROWIRE/SCP Timing

B AND D CHANNELS CONNECTIONS BETWEEN TP3420A AND MOTOROLA HDLC DEVICES

The 2B channel data and the D-Channel data can be connected between the TP3420A (Rev 3.6) and the Motorola devices without any additional glued logic (TP3420A Rev 3.5 or prior revision devices when used in TEM application, will take a package of NOR gates and a TRI-STATE® buffer as shown in Appendix A). The following configurations should be used for the TP3420A (Rev 3.6) and the Motorola devices:

FOR TEM APPLICATIONS ONLY:

Settings For TP3420A:

- TEM (TE Clock Master) Mode
- DIF4A (Digital Interface Format 5) If the MC68302 operates in PCM Highway mode, the TP3420A may be set in DIF1 instead of DIF4A.
- D-Channel Clock Enable, DCKE.

Settings for MC145488:

- Channel 0 routed to the IDL interface to cover a B channel
- Channel 1 routed to the NMSI interface to cover the D channel

Its connection with the TP3420A (Rev 3.6) is shown in Figure 3.

Settings for MC68302:

One SCC routed to the IDL interface to cover a B channel. For datacom applications, 2 SCCs routed to the same IDL interface to cover both B channels.

One SCC routed to the NMSI interface.

It is also possible to use PCM Highway Interface instead of the IDL interface in the MC68302, but this is not shown here.

Its connection with the TP3420A (Rev 3.6) is shown in Figure 4.




FIGURE 3. 2B+D Interconnection between the TP3420A (Rev 3.6) and the MC145488




FIGURE 4. 2B+D Interconnection between the TP3420A (Rev 3.6) and the MC68302

The digital interconnection signals are shown in *Figure 3* and *Figure 4* and the relevant timings are shown in *Figure 5*. The Motorola devices operate on the B-Channel data via its IDL interface, and on D-Channel data via its NMSI interface. For

voice applications, one B-Channel data can be directly connected to a NSC COMBO such as the TP3076. For Datacom applications, both B-Channel data can be connected to the MC68302 to the same IDL interface.




FIGURE 5. Timing Diagrams

The B-Channel connection is straight forward, since DIF5 in the TP3420A is compatible with the IDL mode, its detailed operation is discussed in both the TP3420A Data Sheet, and the Motorola device Data Sheet. For the D-Channel connection, however, its data is shifted out from the TP3420A on BR output rising edge of the BCLK, and shifted into the TP3420A on the TxD input on the falling edge of BCLK. They both occur on the D-Channel timeslot. The RxCLK output generates 2 clock pulses every 125 μ s frame (2 D bits per frame) on the assigned D-Channel timeslot. The Motorola uses this as its external clock input to shift D-Channel data in from BR. However, in TEM mode, the number of clock pulses the TxCLK output generates are controlled by the internal D-Channel Access circuitry. They can be 0, 1, or 2 clock pulses. For example, a DREQ1 (DREQ2) command is sent to the TP3420A to begin a packet transmission, the TxCLK starts pulsing (2 BCLKs per frame) and the TP3420A waits for an opening flag on TxD pin. During this time, the TxCLK may stay idle (no pulses at all). It then checks to see if the D-Channel timeslot on the S-Bus is available by counting the consecutive number of binary 1's present the Echoed bit. If these

conditions are met, the TP3420A will transmit the packet data by again pulsing the TxCLK until it detects a closing flag at TxD pin or a collision is detected on the S-Bus. Notice that TxCLK and RxCLK phases are inverted from the BCLK's.

Recommended Software Steps:

1. Prepare the Packet for transmission on the D-Channel. Setup the DMA and HDLC registers and start the transmitter. The \overline{RTS} will become active forcing its own \overline{CTS} and the HDLC hardware is primed.
2. Send the DREQ1 (or DREQ2) Command to TP3420 via MICROWIRE/SCP port. This will cause TxCLK to generate clock pulses, when D-channel is available, to shift the data out.
3. At the End of successful transmission of Packet. The SID will generate the EOM Interrupt status (serviced via MICROWIRE/SCP port). The software now knows about the successful transmission of the packet and may send the next one. Also the HDLC0 hardware will reset the \overline{RTS} and thus \overline{CTS} signals.

- If a D-channel Contention occurs, the SID will generate a CON interrupt status (serviced via the MICROWIRE/SCP port). The software must Reset the HDLC and DMA hardware and preset the buffer pointers. Note that the CTS does not indicate contention (CON interrupt) in this scheme (as it normally works in a complete Motorola architecture). When the HDLC hardware is set, the RTS goes inactive.

SID can inter-work directly with HDLC controllers from Motorola (MC145488 or the MC68302). This allows the user more flexibility in the choice of Microprocessor while gaining

the benefits of good transceiver performance of the TP3420A SID and the programmable features of NSC COMBO II™ TP3076.

FOR NT OR TES APPLICATIONS:

When the TP3420As are used in these applications, the D-Channel Access algorithm is disabled. The 2B+D Channel data can be connected between the TP3420A and the Motorola via the IDL bus. (Other physical interfaces are also possible). The connection diagrams are shown in *Figure 6* and *Figure 7*.




FIGURE 6. 2B+D Interconnection between the TP3420A (either in NT or TES Mode) and the MC68302





FIGURE 7. 2B+D Interconnection between the TP3420A (either in NT or TES Mode) and the MC145488

APPENDIX A

TP3420A REV 3.5 AND MC68302 INTERCONNECTION



Book
Extract
End

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

 **National Semiconductor Corporation**
Americas
Tel: 1-800-272-9959
Fax: 1-800-737-7018
Email: support@nsc.com
www.national.com

National Semiconductor Europe
Fax: +49 (0) 1 80-530 85 86
Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 1 80-530 85 85
English Tel: +49 (0) 1 80-532 78 32
Français Tel: +49 (0) 1 80-532 93 58
Italiano Tel: +49 (0) 1 80-534 16 80

National Semiconductor Asia Pacific Customer Response Group
Tel: 65-2544466
Fax: 65-2504466
Email: sea.support@nsc.com

National Semiconductor Japan Ltd.
Tel: 81-3-5620-6175
Fax: 81-3-5620-6179

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated