

AC-3 Decoder

CAPABILITY SUPPORTED (V1.00) FEATURES

- Supports 32, 44.1 and 48 kHz Output Sampling Rates and 32-600 kbps Input Bit Rates
- Supports All Specified Audio Coding Modes Namely Dual Mono (1+1), 1/0, 2/0, 3/0, 2/1, 3/1, 2/2, 3/2
- Dialog Norm., Dynamic Range Control, Peak Level Control
- Dual-Mono Modes: Stereo, Ch1 Mono, Ch2 Mono, Mix Mono
- Compliant With Dolby Digital Development Kit Version 3.0 (7.1.0)
- Karaoke Aware and Karaoke Capable
- Supports the Dolby Digital Extended Bit Stream Syntax
- Supports Output 24-Bit PCM Samples
- Supports Only Block Format Data Output and Does Not Support Sample-Interleaved Data Format
- Does Not Support DRM

BACKGROUND

AC-3, also known as Dolby Digital, is an audio codec designed to compress multichannel audio data for the sake of transferring from one location to another. The data layout of AC-3 is described by simplified "C" like language in official specifications, and is most commonly configured in 2 channel or 5.1 channel modes. An AC-3 stream is made up of a series of synchronization frames, which are composed of six audio blocks. Each audio block contains 256 audio samples per channel. AC-3 audio is used on DVD-Video and other purely digital media, like home cinema. In this format, the AC-3 bitstream is interleaved with the video and control bitstreams. AC-3 is also used in many bandwidth-limited applications other than DVD-Video, such as digital TV.

DESCRIPTION

The AC-3 decoder is a proven module. The ready-to-implement AC-3 decoder reduces time-to-market because it can be treated as a tested module and integrated into a software system. TI's AC-3 is a multi-channel audio decoder that is xDM compliant, and it has been certified by Dolby Labs to meet the specifications of the standard. It is available in system tested codec combinations with Codec Engine, DSP/BIOS, DSPLink and Framework components. Combinations include MPEG-2 main profile decoder together with the AC-3 decoder in an audio/video application.



PRODUCT PREVIEW



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Software Architecture

The overall software architecture for the DaVinci Technology-based TMS320DM644x processors are shown in Figure 1. TI digital media encoders and decoders seamlessly plug into the signal processing layer architecture; the right side of the above diagram. The codec engine framework includes code for different classes of TI digital media software. It connects to the application layer and exposes user control through the VISA API; a high level interface that allows developers to control and operate the software from a high level Operating System (OS) environment. TI digital media encoders, such as the AAC encoder, allow developers to focus design efforts on differentiating features at the application layer, while DaVinci's open software environment allows developers to include differentiating IP on any of the DSP, application, or IO layers shown above.

NOTE:

Dolby requires a development license with the OEM prior to TI fulfilling the evaluation request. Please provide proof of license with request.




Figure 1. Software Architecture

need some text here...

Commonly Used Terms:

API – Application Programming Interface

DMAN – Direct Memory Access Manager

EPSI – Easy Peripheral Software Interface


MEM - Memory

TSK – Task

VISA – Video Imaging Speech Audio

xDM – eXpressDSP Algorithm Interoperability Standard for Digital Media

PRODUCT PREVIEW



A. Available via a secure website to which registered DVEVM users are granted access

For Protection:



Figure 2. Required Tools

NOTE:

Dolby requires a development license with the OEM prior to TI fulfilling the evaluation request. Please provide proof of license with request.

Performance Summary

need some text here too...

Table 1. Performance Summary

Criteria	PERFORMANCE
MIPS at Typical Configuration	<ul style="list-style-type: none"> • 32 MHz Typical • 57 MHz Peak
Memory	<ul style="list-style-type: none"> • 232 kB External • 0 kB Internal Data • 46 kB Program

Availability and Pricing

- Available stand alone or in combinations
- Available now, v1.00
- Price: AC-3 Up front fee \$15,000 + \$.30 per unit royalty @ 10 KU, for further pricing information, contact your TI representative or visit www.ti.com/digitalmediasoftware

Future Features

- Error Resiliency changes
- MISRAC compliant
- Support for building big endian library

GET STARTED TODAY

Request an evaluation from your TI representative or a TI Authorized Software Provider www.ti.com/asp. Dolby requires a development license with the OEM prior to TI fulfilling the evaluation request. Please provide proof of license with request. To receive future updates or more information, complete the contact me information form at www.ti.com/digitalmediasoftware.

PRODUCT PREVIEW

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Medical	www.ti.com/medical
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2008, Texas Instruments Incorporated