



Certificate: 70082130

Master Contract: 220991

Project: 80291165

Date Issued: 2026-03-31

Device (SOIC 16W DW-16)	Ratings		Clauses of Standard/Notice	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
ISO7710DW ISO7710FDW ISO7710QDWQ1 ISO7710FQDWQ1 ISO7720DW ISO7720FDW ISO7720QDWQ1 ISO7720FQDWQ1 ISO7721DW ISO7721FDW ISO7721QDWQ1 ISO7721FQDWQ1 ISO7730DW ISO7730FDW ISO7730QDWQ1 ISO7730FQDWQ1 ISO7731DW ISO7731FDW ISO7731QDWQ1 ISO7731FQDWQ1 ISO7740DW ISO7740FDW ISO7740QDWQ1 ISO7740FQDWQ1 ISO7741DW ISO7741FDW ISO7741QDWQ1 ISO7741FQDWQ1 ISO7742DW ISO7742FDW ISO7742QDWQ1 ISO7742FQDWQ1 SN7741FQDWRQ1 SN7742FQDWRQ1 SN7742QDWRQ1	5.0	125	CSA 14-18+UPD1(R2022) Tbl 35, 6.2.1, 6.2.1/6.2.12, 6.8.1, 6.21.4.1 62368-1:25, 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, .4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1-12+UPD1:2015; UPD2:2016; AMD1:2018,UPD3:2023,UPD4: 2024 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1:14 (R2022) 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 62368-1:2023 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 4.5.8, 5.4.9.1, 5.4.1.4 61010-1 Ed.3+A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1+A2 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 62368-1:2024+A11:2024 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2	-	-	8.0
ISO7741EDWQ1 ISO7741EDWRQ1 ISO7741FEDWQ1 ISO7741FEDWRQ1	5.0	150				

Suffix B may be used before DW. Suffix R (R may be placed before Q1) is optional and used for reel shipping packing type.

1. The devices meet basic insulation requirements for 800Vrms and reinforced insulation requirements for 400Vrms for CSA 62368-1:25, IEC 62368-1:2023 Ed. 3 and 62368-1:2024+A11:2024. (pollution degree 2, material group III)
2. For CSA 61010-1-12+UPD1:2015; UPD2:2016; UPD3:2023, UPD4:2024, AMD1:2018 and IEC 61010-1 Ed.3+A1, the devices meet



Certificate: 70082130

Master Contract: 220991

Project: 80291165

Date Issued: 2026-03-31

600Vrms for basic insulation and 300V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)

3. For CSA 60601-1:14 (R2022) and IEC 60601-1 Ed.3+A1+A2 for 2 MOPP for 250V, the devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.

4. Evaluated by thermal cycling and other tests for a temperature rating of 125C.

5. The creepage and clearance has been evaluated for altitudes $\leq 2000\text{m}$, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

APPLICABLE REQUIREMENTS

Standards Used	Description
CSA C22.2 No. 14-18 - Thirteenth Edition	Industrial control equipment
CSA C22.2 NO. 62368-1:25 - Fourth Edition	Audio/video, information and communication technology equipment — Part 1: Safety requirements
CSA-C22.2 No. 60601-1:14	Medical electrical equipment — Part 1: General requirements for basic safety and essential performance - Consolidated Edition 3.2
CAN/CSA C22.2 No. 61010-1-12, UPD1:2015, UPD2:2016, AMD1:2018, UPD3:2023, UPD4:2024	Safety requirements for electrical equipment for measurement, control, and laboratory use — Part 1: General requirements - Third Edition
IEC 62368-1:2023	Audio/video, information and communication technology equipment – Part 1: Safety requirements - Edition 4.0
IEC 61010-1:2010/AMD1:2016	Safety requirements for electrical equipment for measurement, control, and laboratory use - Part 1: General requirements
IEC 60601-1:2005/AMD1:2012/AMD2:2020	Medical electrical equipment – Part 1: General requirements for basic safety and essential performance - Edition 3.2; Consolidated Reprint; Incorporates Amendment 1: 2012, Corrigenda 1: 12/2012, Corrigenda to Amendment 1: 07/2014, Interpretation 1: 04/2008, Interpretation 2: 01/2009, and Interpretation 3: 05/2013 and Amendment 2: 08/2020
EN 62368-1:2024/A11:2024	Audio/video, information and communication technology equipment - Part 1: Safety requirements



Certificate: 70082130


Master Contract: 220991

Project: 80291165

Date Issued: 2026-03-31

Notes:

Products certified under Class(es) C907330 have been certified under CSA's ISO/IEC 17065 accreditation with the Standards Council of Canada (SCC). www.scc.ca



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025