Filename:
 ProB3B5.tmp

 Variant:
 001

 Generated:
 2/19/2019
 11:10:19

 TID #:
 N/A

SENS040 REV A Bill of Materials



Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	IPCB1	1		SENS040	Any	Printed Circuit Board	
2	C1	1	0.1uF	CGA2B3X7R1H104K050BB	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
3	C2, C6	2	0.1uF	CL05B104KP5NNNC	Samsung Electro-Mechanics	CAP, CERM, 0.1 uF, 10 V, +/- 10%, X7R, 0402	0402
4	C3	1	3900pF	CGA3E1C0G2A392J080AC		CAP, CERM, 3900 pF, 100 V,+/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0603	0603
5	C5	1	100uF	EEE-FK1V101XP	Panasonic	CAP, AL, 100 uF, 35 V, +/- 20%, 0.34 ohm, AEC-Q200 Grade 2, SMD	SMT Radial D8
6	C7	1	330pF	C1005C0G2A331J050BE	TDK	CAP, CERM, 330 pF, 100 V,+/- 5%, C0G/NP0, 0402	0402
7	C8	1	0.033uF	GRM155R71A333KA01D	MuRata	CAP, CERM, 0.033 uF, 10 V, +/- 10%, X7R, 0402	0402
8	C9, C10	0	180pF	GRM1555C1H181JA01D	MuRata	CAP, CERM, 180 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
9	D1	1	40V	SS14FL	Fairchild Semiconductor	Diode, Schottky, 40 V, 1 A, AEC-Q101, SOD-123F	SOD-123F
10	D2	1	27V	MMBZ27VCL-7-F	Diodes Inc.	Diode, TVS, Uni, 27 V, 38 Vc, SOT-23	SOT-23
11	J1	0		TSW-103-07-G-S	Samtec	Header, 100mil, 3x1, Gold, TH	3x1 Header
12	J2	1		TSW-105-07-G-S	Samtec	Header, 100mil, 5x1, Gold, TH	5x1 Header
13	R1	1	10	CRCW060310R0JNEAHP	Vishay-Dale	RES, 10, 5%, 0.25 W, AEC-Q200 Grade 0, 0603	0603
14	R2, R4, R5	3	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
15	R3	1	3.9k	CRCW06033K90JNEA	Vishay-Dale	RES, 3.9 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
16	R6	1	0	CRCW04020000Z0EDHP	Vishay-Dale	RES, 0, 0%, 0.2 W, AEC-Q200 Grade 0, 0402	0402
17	T1	1	3mH	750317161	Wurth Elektronik	Transformer, 3000 uH, SMD	8.26x6.6mm
18	U1	1		PGA460TPWRQ1	Texas Instruments	PGA460TPWRQ1, PW0016A (TSSOP-16)	PW0016A
19	U2	1		UTR-1440K-TT-R	PUI Audio	Ultrasonic Xmr/Receiver, TH	Dia 14.4mm

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2019, Texas Instruments Incorporated