

Bill of Materials

PMP10558

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	PCB Footprint	Note
Transformer 750314463								
1	3	C1, C2, C3	2.2uF	CAP, CERM, 2.2 µF, 35 V, +/- 10%, X7R, 0805	TDK	C2012X7R1V225K085AC	0805_HV	
2	2	C4, C5	0.01uF	CAP, CERM, 0.01 µF, 25 V, +/- 5%, COG/NPO, 0603	TDK	C1608COG1E103J	0603	
3	1	C6	1000pF	CAP, CERM, 1000 pF, 25 V, +/- 5%, COG/NPO, 0603	MuRata	GRM1885C1E102JA01D	0603	
4	2	C7, C8	10uF	CAP, CERM, 10 µF, 25 V, +/- 20%, X7R, 1210	TDK	C3225X7R1E106M	1210	
5	1	C9	1uF	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0603	TDK	C1608X5R1C105K	0603	
6	1	C10	1uF	CAP, CERM, 1 µF, 100 V, +/- 10%, X7R, 1210	TDK	C3225X7R2A105K200AA	1210	
7	1	C11	0.1uF	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	TDK	C2012X7R2A104K	0805_HV	
8	1	C12	1000pF	CAP, CERM, 1000 pF, 1000 V, +/- 5%, COG/NPO, 1210	Vishay-Vitramon	VJ1210A102JXGATSZ	1210	
9	1	D1	200V	Diode, Fast Rectifier, 200 V, 0.8 A, SOD-123	Rohm	RF081M2STR	SOD-123	
10	2	D2, D3	100V	Diode, Schottky, 100 V, 1 A, SOD-123FL	ON Semiconductor	MBR1H100SFT3G	SOD-123FL	
11	1	D4	45V	Diode, Schottky, 45 V, 0.1 A, SOD-523	Diodes Inc.	SDM10U45-7-F	SOD-523	
12	2	FB, SW	Red	Test Point, Miniature, Red, TH	Keystone	5000	Keystone5000	
13	1	GND	Black	Test Point, Miniature, Black, TH	Keystone	5001	Keystone5001	
14	9	GND, GND, IGND, IGND, Vin, Vopri, Vout1, Vout2, Vout3	Double	Terminal, Turret, TH, Double	Keystone	1502-2	Keystone1502-2	
15	1	R1	24.3k	RES, 24.3 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060324K3FKEA	0603	
16	2	R2, R3	5.23k	RES, 5.23 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06035K23FKEA	0603	
17	1	R4	40.2k	RES, 40.2 k, 1%, 0.1 W, 0603	Yageo America	RC0603FR-0740K2L	0603	
18	1	R5	100k	RES, 100 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603100KFKEA	0603	
19	1	R6	332k	RES, 332 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603332KFKEA	0603	
20	1	R7	154k	RES, 154 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603154KFKEA	0603	
21	1	R8	8.87k	RES, 8.87 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06038K87FKEA	0603	
22	1	R9	20.0k	RES, 20.0 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060320K0FKEA	0603	
23	1	U1		100V Constant On-Time PFET Buck Switching Controller, 8-pin PSOP, Pb-Free	Texas Instruments	LM5017MRX/NOPB	MRA08A_N	
24	1	T1	45uH	XFMR, SMT 45uH, 750314463	Würth Elektronik	750314463	XFMR_Wurth_ER11p5_12pin_SMT	
Transformer 750314462								
1	1	C1	4.7uF	CAP, CERM, 4.7 µF, 16 V, +/- 5%, COG/NPO, 0805	MuRata	GRM21BR71C475KA73L	0805	
2	2	C2, C3	2.2uF	CAP, CERM, 2.2 µF, 25 V, +/- 5%, COG/NPO, 0805	MuRata	GRM21BR61E225KA12L	0805	
3	2	C4, C5	0.01uF	CAP, CERM, 0.01 µF, 25 V, +/- 5%, COG/NPO, 0603	TDK	C1608COG1E103J	0603	
4	1	C6	1000pF	CAP, CERM, 1000 pF, 25 V, +/- 5%, COG/NPO, 0603	MuRata	GRM1885C1E102JA01D	0603	
5	2	C7, C8	10uF	CAP, CERM, 10 µF, 25 V, +/- 20%, X7R, 1210	TDK	C3225X7R1E106M	1210	
6	1	C9	1uF	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0603	TDK	C1608X5R1C105K	0603	
7	1	C10	1uF	CAP, CERM, 1 µF, 100 V, +/- 10%, X7R, 1210	TDK	C3225X7R2A105K200AA	1210	
8	1	C11	0.1uF	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	TDK	C2012X7R2A104K	0805_HV	
9	1	C12	1000pF	CAP, CERM, 1000 pF, 1000 V, +/- 5%, COG/NPO, 1210	Vishay-Vitramon	VJ1210A102JXGATSZ	1210	
10	1	D1	60V	Diode, Schottky, 60 V, 1 A, SOD-123FL	Diodes Inc.	DFLS160-7	SOD 123	
11	2	D2, D3	100V	Diode, Schottky, 100 V, 0.15 A, SOD-123	Diodes Inc.	BAT46W-7-F	SOD-123	
12	1	D4	45V	Diode, Schottky, 45 V, 0.1 A, SOD-523	Diodes Inc.	SDM10U45-7-F	SOD-523	
13	2	FB, SW	Red	Test Point, Miniature, Red, TH	Keystone	5000	Keystone5000	
14	1	GND	Black	Test Point, Miniature, Black, TH	Keystone	5001	Keystone5001	
15	9	GND, GND, IGND, IGND, Vin, Vopri, Vout1, Vout2, Vout3	Double	Terminal, Turret, TH, Double	Keystone	1502-2	Keystone1502-2	
16	1	R1	5.1k	RES, 5.1 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06035K10JNEA	0603	
17	2	R2, R3	10k	RES, 10 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060310K0FKEA	0603	
18	1	R4	40.2k	RES, 40.2 k, 1%, 0.1 W, 0603	Yageo America	RC0603FR-0740K2L	0603	
19	1	R5	100k	RES, 100 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603100KFKEA	0603	
20	1	R6	316k	RES, 316 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603316KFKEA	0603	
21	1	R7	154k	RES, 154 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603154KFKEA	0603	
22	1	R8	8.87k	RES, 8.87 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06038K87FKEA	0603	
23	1	R9	21k	RES, 21 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060321K0FKEA	0603	
24	1	U1		100V Constant On-Time PFET Buck Switching Controller, 8-pin PSOP, Pb-Free	Texas Instruments	LM5017MRX/NOPB	MRA08A_N	
25	1	T1	45uH	XFMR, SMT 45uH, 750314463	Würth Elektronik	750314463	XFMR_Wurth_ER11p5_12pin_SMT	

Transformer 750314461

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	PCB Footprint	Note
1	1	C1	2.2uF	CAP, CERM, 2.2 µF, 25 V, +/- 5%, COG/NPO, 0805	MuRata	GRM21BR61E225KA12L	0805	
2	2	C2, C3	4.7uF	CAP, CERM, 4.7 µF, 16 V, +/- 5%, COG/NPO, 0805	MuRata	GRM21BR71C475KA73L	0805	
3	2	C4, C5	0.01uF	CAP, CERM, 0.01 µF, 25 V, +/- 5%, COG/NPO, 0603	TDK	C1608COG1E103J	0603	
4	1	C6	1000pF	CAP, CERM, 1000 pF, 25 V, +/- 5%, COG/NPO, 0603	MuRata	GRM1885C1E102JA01D	0603	
5	2	C7, C8	10uF	CAP, CERM, 10 µF, 25 V, +/- 20%, X7R, 1210	TDK	C3225X7R1E106M	1210	
6	1	C9	1uF	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0603	TDK	C1608X5R1C105K	0603	
7	1	C10	1uF	CAP, CERM, 1 µF, 100 V, +/- 10%, X7R, 1210	TDK	C3225X7R2A105K200AA	1210	
8	1	C11	0.1uF	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	TDK	C2012X7R2A104K	0805_HV	
9	1	C12	1000pF	CAP, CERM, 1000 pF, 1000 V, +/- 5%, COG/NPO, 1210	Vishay-Vitramon	VJ1210A102JXGAT5Z	1210	
10	1	D1	200V	Diode, Fast Rectifier, 200 V, 0.8 A, SOD-123	Rohm	RF081M25TR	SOD-123	
11	2	D2, D3	60V	Diode, Schottky, 60 V, 1 A, SOD-123FL	Diodes Inc.	DFLS160-7	SOD 123	
12	1	D4	45V	Diode, Schottky, 45 V, 0.1 A, SOD-523	Diodes Inc.	SDM10U45-7-F	SOD-523	
13	2	FB, SW	Red	Test Point, Miniature, Red, TH	Keystone	5000	Keystone5000	
14	1	GND	Black	Test Point, Miniature, Black, TH	Keystone	5001	Keystone5001	
15	9	GND, GND, IGND, IGND, Vin, Vopri, Vout1, Vout2, Vout3	Double	Terminal, Turret, TH, Double	Keystone	1502-2	Keystone1502-2	
16	1	R1	15k	RES, 15 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060315K0FKFA	0603	
17	2	R2, R3	5.23k	RES, 5.23 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06035K23FKFA	0603	
18	1	R4	40.2k	RES, 40.2 k, 1%, 0.1 W, 0603	Yageo America	RC0603FR-0740K2L	0603	
19	1	R5	100k	RES, 100 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603100KFKA	0603	
20	1	R6	332k	RES, 332 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603332KFKA	0603	
21	1	R7	150k	RES, 150 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603150KFKA	0603	
22	1	R8	8.87k	RES, 8.87 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06038K87FKFA	0603	
23	1	R9	20.5k	RES, 20.0 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060320K5FKFA	0603	
24	1	U1		100V Constant On-Time PFET Buck Switching Controller, 8-pin PSOP, Pb-Free	Texas Instruments	LM5017MRX/NOPB	MRA08A_N	
25	1	T1	45uH	XFMR, SMT 45uH, 750314463	Würth Elektronik	750314463	XFMR_Wurth_ER11p5_12pin_SMT	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.