Filename: BOM-PMP9738A\_Jan7\_2015.xls 

C46, C47, R68 updated January 7, 2015

12Vin 1Vout 200/240A 6 Phases TPS53661 / CSD95372B(x6)										
Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer		
!PCB1	1		Printed Circuit Board		PMP9738	Any	-	-		
C1, C2, C3 C4, C5, C6,	3	470uF 0.1uF	CAP, AL, 470uF, 35V, +/-20%, TH CAP, CERM, 0.1uF, 50V, +/-20%, X7R, 0402	10x20 0402	35ZL470MEFC10X20 C1005X7R1H104M	Rubycon TDK				
C7										
C8	1	1uF	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	0402	GRM155R61A105KE15	MuRata				
C9, C10, C11, C12, C13, C14,	10	470uF	CAP, AL, 470uF, 2.5V, +/-20%, 9 ohm, SMD	7.3x1.8x4.3mm	EEFSX0E471ER	Panasonic				
C15, C16, C17, C18 C19, C20, C21, C22,	10	100uF	CAP, CERM, 100uF, 6.3V, +/-20%, X5R, 1210	1210	C1210C107M9PACTU	Kemet				
C23, C24, C25, C26, C27, C28 C29, C31	2	10uF	CAP, CERM, 10uF, 25V, +/-20%, X7R, 1210	1210	C3225X7R1E106M	TDK				
C30	1	1uF	CAP, CERM, 1uF, 25V, +/-10%, X7R, 0603	0603	GRM188R71E105KA12 D	MuRata				
C32	1	15pF	CAP, CERM, 15pF, 50V, +/-5%, C0G/NP0, 0402	0402	GRM1555C1H150JA01 D	MuRata				
C41	1	6800pF	CAP, CERM, 6800pF, 100V, +/-10%, X7R, 0603	0603	06031C682KAT2A	AVX				
C42 C43, C44,	1	1000pF 1uF	CAP, CERM, 1000pF, 50V, +/-10%, X7R, 0402 CAP, CERM, 1uF, 25V, +/-10%, X5R, 0603	0402 0603	C1005X7R1H102K C1608X5R1E105K080A	TDK TDK				
C45, C48 C46	1	10pF	CAP, CERM, 10pF, 50V, +/-5%, C0G/NP0, 0402	0402	C GRM1555C1H100JA01	MuRata				
C47	1	1500pF	CAP, CERM, 1500pF, 50V, +/-10%, X7R, 0402	0402	D GRM155R71H152KA01	MuRata				
C49	1	0.33uF	CAP, CERM, 0.33uF, 6.3V, +/-10%, X5R, 0402	0402	D GRM155R60J334KE01	MuRata				
C50, C51	2	4.7uF	CAP, CERM, 4.7uF, 10V, +/-20%, X5R, 0402	0402	D GRM155R61A475M	MuRata				
C50, C51	1	2200pF	CAP, CERM, 4.7ur, 10V, +/-20%, ASR, 0402 CAP, CERM, 2200pF, 50V, +/-10%, X7R, 0402	0402	C1005X7R1H222K	TDK				
C100, C200, C300, C400,	6	1000pF	CAP, CERM, 1000pF, 25V, +/-5%, C0G/NP0, 0402	0402	C1005C0G1E102J	TDK				
C500, C600 C101,	30	10uF	CAP, CERM, 10uF, 25V, +/-10%, X7R, 1206	1206	GRM31CR71E106KA12	MuRata				
C102, C103, C104, C105, C201, C202, C203, C204, C205, C301, C302, C303, C304, C401, C402, C403, C401, C502, C503, C501, C502, C601, C602, C603, C304, C106, C206, C106, C206, C106, C206, C106, C206, C106, C106, C406,	6	3300pF 0.1uF	CAP, CERM, 3300pF, 50V, +/-10%, X7R, 0402  CAP, CERM, 0.1uF, 25V, +/-5%, X7R, 0603	0402 0603		TDK Kemet				
C111, C211, C311, C411,	Ü	10uF	CAP, CERM, 10uF, 6.3V, +/-20%, X5R, 0603	0003	COOOSC TOOMSE ACTO	remet				
C511, C611	_	0.45	LOAD OFFIN A 4-F 4014 4400 1477 2477	0.400	ODIMEEDOLOGE	MuData				
C112, C212, C312, C412, C512, C612	6	0.1uF	CAP, CERM, 0.1uF, 16V, +/-10%, X5R, 0402	0402	GRM155R61C104KA88 D	MuRata				
C113, C213, C313, C413, C513, C613		1500pF	CAP, CERM, 1500pF, 100V, +/-10%, X7R, 0805	0805	08051C152KAT2A	AVX				
D1, D3 D2	2	30V 30V	Diode, Schottky, 30V, 0.5A, SOD-123 Diode, Schottky, 30V, 0.2A, SOD-323	SOD-123 SOD-323	MBR0530T1G BAT54WS-7-F	ON Semiconductor Diodes Inc.				
D4		Red	LED, Red, SMD	LED 0805	LTST-C170KRKT	Lite-On				
H1, H2, H3,	4		Machine Screw, Round, #4-40 x 1/4, Nylon, Philips	Screw	NY PMS 440 0025 PH	B&F Fastener Supply	-	-		
H4 H5, H6, H7,	4		panhead Standoff, Hex, 0.5"L #4-40 Nylon	Standoff	1902C	Keystone	-	-		
H8 H9, H10,	4		Bumpon, Hemisphere, 0.44 X 0.20, Clear	Transparent Bumpon	SJ-5303 (CLEAR)	3M				
H11, H12 J1, J2, J5,	7	GSLU-70	Lug, Solderless, #2 - #8 AWG, 1/4", Copper	1.55 x 0.50 inch	GSLU-70	ILSCO				
J1, J2, J5, J6, J7, J8, J10	,		209, Johnson #2 - #0 AVVO, 1/4 , Cupper	1.00 A 0.00 INCH		112000				

Declarates	0	. V-t	December 1997	D1D-f	Double and a	M	Alta-mata Danthiamia	A14
J3, J47	Quantity 2	Value PEC02SAAN	Description Header, Male 2-pin, 100mil spacing,	PackageReference 0.100 inch x 2	PartNumber PEC02SAAN	Manufacturer Sullins	Alternate PartNumber	Alternate Manufacturer
J4, J9, J45	3	PECUZSAAN	Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH	7.0x8.2x6.5mm	ED555/2DS	On-Shore Technology		
J4, J9, J45 J41	1		Header (shrouded), 100mil, 5x2, Gold, TH	5x2 Shrouded header	5103308-1	TE Connectivity		
041			ricador (silloddod), roomii, oxz, cold, rrr	ONE OFFICIACE FICAGE	01000001	12 0000		l
J42, J46	2	PEC05DAAN	Header, Male 2x5-pin, 100mil spacing	0.100 inch x 5 X 2	PEC05DAAN	Sullins		
J43	1	1x3	Header, TH, 100mil, 1x3, Gold plated, 230 mil above	PBC03SAAN	PBC03SAAN	Sullins Connector Solutions		
			insulator					
J44	1	PEC03SAAN	Header, Male 3-pin, 100mil spacing,	0.100 inch x 3	PEC03SAAN	Sullins		
L1	1	6.8 uH	Inductor, SMT, yyA, zzmilliohm	0.276 sq inch	SLF7032T-xxx	TDK		
L100, L200,	6	210 uH	Inductor, Low-Profile, High-Current ±20%	2525/5050	FP1308R3-R21	Cooper Bussman		l
L300, L400, L500, L600								l
LBL1,	2		Thermal Transfer Printable Labels, 0.650" W x 0.200"	PCB Label 0.650"H x	THT-14-423-10	Brady		1
LBL1, LBL41	2		H - 10,000 per roll	0.200"W	111-14-423-10	brady	-	Ī
Q1	1	25V	MOSFET, N-CH, 25V, 40A, SON 5x6mm	SON 5x6mm	CSD16556Q5B	Texas Instruments		None
R1, R2, R3,	8	0.002	RES, 0.002 ohm, 1%, 2W, 2512	2512	CSNL2512FT2L00	Stackpole Electronics Inc		110.10
R4, R6, R7,	Ü	0.002	1120, 0.002 0mm, 170, 244, 2012	2012	OONEZOTZI TZEOO	Chackpoid Electronico inc		l
R12, R13								l
R5	1	8.06k	RES, 8.06k ohm, 1%, 0.063W, 0402	0402	CRCW04028K06FKED	Vishay-Dale		
R8, R51,	4	10.0k	RES, 10.0k ohm, 1%, 0.063W, 0402	0402	CRCW040210K0FKED	Vishay-Dale		
R52, R53								
R9, R11	2	1.00k	RES, 1.00k ohm, 1%, 0.063W, 0402	0402	CRCW04021K00FKED	Vishay-Dale		
R10	1	200k	RES, 200k ohm, 1%, 0.063W, 0402	0402	CRCW0402200KFKED	Vishay-Dale		
R14	1	330	RES, 330 ohm, 5%, 0.063W, 0402	0402	CRCW0402330RJNED	Vishay-Dale		
R15, R16	2	49.9	RES, 49.9 ohm, 1%, 0.063W, 0402	0402	CRCW040249R9FKED	Vishay-Dale		
R17, R18,	6	1.00Meg	RES, 1.00Meg ohm, 1%, 0.063W, 0402	0402	CRCW04021M00FKED	Vishay-Dale		
R19, R20,					1			
R22, R23			DE0 54 1 50/	0.400	0000000	Vi-h D-/		
R21	1	51	RES, 51 ohm, 5%, 0.063W, 0402	0402	CRCW040251R0JNED	Vishay-Dale		
R24	1	261k	RES, 261k ohm, 1%, 0.063W, 0402	0402	CRCW0402261KFKED	Vishay-Dale		
R25	1	294k	RES, 294k ohm, 1%, 0.063W, 0402	0402	CRCW0402294KFKED	Vishay-Dale		
R44	1	402k	RES, 402k ohm, 1%, 0.063W, 0402	0402	CRCW0402402KFKED	Vishay-Dale	<del>                                     </del>	
R45		16.5k	RES, 16.5k ohm, 1%, 0.063W, 0402	0402	CRCW04020K31EKED	Vishay-Dale		
R46, R49	2	9.31k 14.0k	RES, 9.31k ohm, 1%, 0.063W, 0402	0402	CRCW04029K31FKED	Vishay-Dale		
R47	1		RES, 14.0k ohm, 1%, 0.063W, 0402	0402	CRCW040214K0FKED	Vishay-Dale	+	
R48 R55, R56,	1 5	1.15k 20.0k	RES, 1.15k ohm, 1%, 0.063W, 0402 RES, 20.0k ohm, 1%, 0.063W, 0402	0402 0402	CRCW04021K15FKED CRCW040220K0FKED	Vishay-Dale		
R55, R56, R57, R60,	5	20.0K	NEO, 20.0K 01111, 1%, 0.003W, 0402	0402	ONOW040220KUFKED	Vishay-Dale		
R62								
R58, R61	2	150k	RES, 150k ohm, 1%, 0.063W, 0402	0402	CRCW0402150KFKED	Vishay-Dale		
R63	1	24.3k	RES, 24.3k ohm, 1%, 0.063W, 0402	0402	CRCW0402150KFKED	Vishay-Dale Vishay-Dale		
R64, R65,	10	100	RES, 100 ohm, 5%, 0.063W, 0402	0402	CRCW0402100RJNED	Vishay-Dale		
R66, R71,		100	1120, 100 01111, 070, 0.00011, 0.102	0.102	01101101021001101125	Violity Balo		
R81, R82,								
R83, R84,								
R85, R86								l
R67	1	100k	RES, 100k ohm, 1%, 0.063W, 0402	0402	CRCW0402100KFKED	Vishay-Dale		
R68	1	19.1k	RES, 19.1k ohm, 1%, 0.063W, 0402	0402	CRCW040219K1FKED	Vishay-Dale		
R69	1	2.43k	RES, 2.43k ohm, 1%, 0.063W, 0402	0402	CRCW04022K43FKED	Vishay-Dale		
R70	1	121k	RES, 121k ohm, 1%, 0.063W, 0402	0402	CRCW0402121KFKED	Vishay-Dale		
R72, R73	2	10	RES, 10 ohm, 5%, 0.063W, 0402	0402	CRCW040210R0JNED	Vishay-Dale		
R74	1	1.0	RES, 1.0 ohm, 5%, 0.063W, 0402	0402	CRCW04021R00JNED	Vishay-Dale		
R100,	6	0	RES, 0 ohm, 5%, 0.063W, 0402	0402	RC0402JR-070RL	Yageo America		
R200,								
R300,								
R400,								
R500, R600			DEC 0.0 1 50/ 0.000W 0.400	0.400		V. 1. D. 1	<del></del>	
R110,	6	2.2	RES, 2.2 ohm, 5%, 0.063W, 0402	0402	CRCW04022R20JNED	Vishay-Dale		l
R210,								l
R310,								l
R410, R510, R610								l
R113,	6	1.0	RES, 1.0 ohm, 5%, 0.5W, 1206	1206	CRM1206-JW-1R0ELF	Bourns		
R213,	U	1.0	KES, 1.0 01111, 576, 0.544, 1200	1200	CIXIWI 200-3W-IIXOLLI	Dourns		
R313,								
R413,								
R513, R613								
TH1, TH2	2		Thru Hole, 15 mil, plated					
TP1, TP3,	4	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone		
TP4, TP6			·					
TP2, TP5,	3	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone		
TP7			-			-		
TP8	1	131-4244-00	Adaptor, 3.5-mm probe clip (or 131-5031-00)	0.200 inch	131-4244-00	Tektronix		
TP100,	6	SMT	Test Point, Miniature, SMT	Testpoint_Keystone_	5015	Keystone		<u> </u>
TP200,				Miniature	1			
TP300,					1			
TP400,								i l
TP500,								i l
TP600	_	5040	Total Police OM 0.450 0.000	0.405 0.405	5040	Manage and		
TP301,	2	5016	Test Point, SM, 0.150 x 0.090	0.185 x 0.135 inch	5016	Keystone		
TP601		TLOSSECO	IC Times Law Power CMCC	000	TLOSSECD	TI		None
U1	1	TLC555CD UCC37324D	IC, Timer, Low-Power CMOS	SO8	TLC555CD UCC37324D	TI		None
U2		UCC3/324D	IC, Dual 4-A High Speed Low-Side Power MOSFET	SO-8	000373240	TI		None
U3	1		Drivers  Buck Adjustable Regulator with 3.1 to 17 V Input and	RSA0016B	TPS62110RSAR	Texas Instruments	Equivalent	None
US	1		1.2 to 16 V Output, -40 to 85 degC, 16-Pin QFN (RSA),	NOAUU IOB	IF SOZIIUKSAK	reads instruments	Equivalent	INUTE
1			1.2 to 16 V Output, -40 to 85 degC, 16-Pin QFN (RSA), Green (RoHS & no Sb/Br)					i l
U41	1		6-Phase, D-CAP+ Step-Down VR12.x Server CPU	RSB0040E	TPS53661RSB	Texas Instruments		None
041			VCORE and DDR Memory Controller with PMBus	N3B0040E	11.00000 LKOD	1 exas moduments		NOTE
			Interface, RSB0040E					
U42	1		Cap-Free, NMOS, 250mA Low Dropout Regulator with	DBV0005A	TPS73233DBV	Texas Instruments	+	None
042	'		Reverse Current Protection, DBV0005A	PP 400024	11 3/3233DDV	rozas motruments		140110
U100,	6		Synchronous Buck NexFET Power Stage, DMC0012A	DMC0012A	CSD95372BQ5M	Texas Instruments		None
	J		5,	SINIOUVIZA	CODOGGI ZDQJIVI	. Oxao modumento		
(1200								
U200, U300.								1
U300,								
U300, U400,								
U300,	0		Fiducial mark. There is nothing to buy or mount.	Fiducial	N/A	N/A		
U300, U400, U500, U600	0		Fiducial mark. There is nothing to buy or mount.	Fiducial	N/A	N/A		

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.