PMP9490_BOM.xls A 3/11/2015 7:12:42 PM

PMP9490 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB1	1	74.45	PMP9490	Any	Printed Circuit Board	. dellagortererere
C1, C2, C3, C4,	5	10uF	C3225X7R1E106M	TDK	CAP, CERM, 10 µF, 25 V, +/- 20%, X7R, 1210	1210
C5						
C6, C7, C8, C9	4	470uF	EEU-FM1E471LBJ	Panasonic	CAP, AL, 470 µF, 25 V, +/- 20%, 0.03 ohm, TH	8.0x20mm
C10, C11	2	330uF	EEE-FP1V331AP	Panasonic	CAP, AL, 330 μF, 35 V, +/- 20%, 0.06 ohm, SMD	10 x 10
C12	1	1uF	GRM21BR71H105KA12L	MuRata	CAP, CERM, 1uF, 50V, +/-10%, X7R, 0805	0805
C13, C14, C15,	6	1uF	GRM188R71C105KA12D	MuRata	CAP, CERM, 1uF, 16V, +/-10%, X7R, 0603	0603
C16, C17, C21						
C18	1	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1uF, 25V, +/-5%, X7R, 0603	0603
C19	1	100pF	06035A101FAT2A	AVX	CAP, CERM, 100 pF, 50 V, +/- 1%, C0G/NP0, 0603	0603
C20	1	1000pF	GRM188R71H102KA01D	MuRata	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0603	0603
C22	1	0.1uF	06035C104KAT2A	AVX	CAP, CERM, 0.1 μF, 50 V, +/- 10%, X7R, 0603	0603
C23	1	4700pF	06031C472KAT2A	AVX	CAP, CERM, 4700 pF, 100 V, +/- 10%, X7R, 0603	0603
C24, C26, C28, C29	4	2.2uF	C0603C225K9PACTU	Kemet	CAP, CERM, 2.2uF, 6.3V, +/-10%, X5R, 0603	0603
C25	1	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	0603
C27	1	0.01uF	06031C103KAT2A	AVX	CAP, CERM, 0.01 µF, 100 V, +/- 10%, X7R, 0603	0603
Cin1, Cin2, Cin3,	4	2.2uF	GRM31CR61H225KA88L	MuRata	CAP, CERM, 2.2uF, 50V, +/-10%, X5R, 1206	1206
Cin4						
COMP1, SS1, SW1, SW2	4	White	5007	Keystone	Test Point, Compact, White, TH	White Compact Testpoint
Cx1	1	1500pF	06031C152KAT2A	AVX	CAP, CERM, 1500 pF, 100 V, +/- 10%, X7R, 0603	0603
D1, D2, D3	3	100V	MBR1H100SFT3G	ON Semiconductor	Diode, Schottky, 100V, 1A, SOD-123FL	SOD-123FL
D101, D102,	4	30V	MBR130T1G	ON Semiconductor	Diode, Schottky, 30 V, 1 A, SOD-123	SOD-123
D103, D104	-					
FID1, FID2, FID3,	6		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
FID4, FID5, FID6						
Gnd1, Gnd2, ICGnd1	3	Black	5006	Keystone	Test Point, Compact, Black, TH	Black Compact Testpoint
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
H13, H14, H15,	4		634-10ABP	Wakefield Solutions	Heat Sink, TO-220, TH	16.26x25.4x16.26 mm
H16						
J1, J2, J3, J4	4	50A	CB35-36-CY	Panduit	Terminal 50A Lug	CB35-36-CY
J5	1	1x3	PBC03SAAN	Sullins Connector Solutions	Header, 100mil, 3x1, Gold, TH	PBC03SAAN
L1	1	1.3uH	7443556130	Wurth Elektronik eiSos	Inductor, Shielded Drum Core, WE-Superflux200, 1.3 µH, 34.5 A, 0.0009 ohm, SMD	18.3x8.9x18.2mm
LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
Q3, Q4, Q9, Q10	4	40V	CSD18502KCS	Texas Instruments	MOSFET, N-CH, 40 V, 100 A, KCS0003A	KCS0003A
R1, R2	2	0.005	KRL7638-C-R005-F-T1	Susumu Co Ltd	RES, 0.005, 1%, 4 W, 3015 WIDE	3015 WIDE
R3, R10	2	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, 0603	0603
R4, R15, R18	3	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
R5	1	249k	CRCW0805249KFKEA	Vishay-Dale	RES, 249k ohm, 1%, 0.125W, 0805	0805
R6	1	39.0k	RC0603FR-0739KL	Yageo America	RES, 39.0 k, 1%, 0.1 W, 0603	0603
R7	1	10.0	CRCW080510R0FKEA	Vishay-Dale	RES, 10.0 ohm, 1%, 0.125W, 0805	0805
R8	1	0	CRCW08050000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.125W, 0805	0805

PMP9490_BOM

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R9	1	DNP	CRCW06030000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.1W, 0603	0603
R11, R16, R17	3	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.1W, 0603	0603
R12	1	189k	RT0805BRD07189KL	Yageo America	RES, 189k ohm, 0.1%, 0.125W, 0805	0805
R13	1	24.3k	CRCW080524K3FKEA	Vishay-Dale	RES, 24.3 k, 1%, 0.125 W, 0805	0805
R14	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
R19, R20	2	0.006	KRL7638-C-R006-F-T1	Susumu Co Ltd	RES, 0.006, 1%, 4 W, 3015 WIDE	3015 WIDE
R22	1	20.0k	CRCW080520K0FKEA	Vishay-Dale	RES, 20.0k ohm, 1%, 0.125W, 0805	0805
R25	1	1.15k	CRCW08051K15FKEA	Vishay-Dale	RES, 1.15k ohm, 1%, 0.125W, 0805	0805
R101, R102,	4	10.0k	CRCW080510K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.125W, 0805	0805
R103, R104						
Rh1, Rh2	2	10.0	RC0603FR-0710RL	Yageo America	RES, 10.0, 1%, 0.1 W, 0603	0603
RI1, RI2	2	4.70	RT0603DRE074R7L	Yageo America	RES, 4.70, 0.5%, 0.1 W, 0603	0603
Rx1, Rx2	2	1.78	CRCW12061R78FKEA	Vishay-Dale	RES, 1.78, 1%, 0.25 W, 1206	1206
U1	1		LM5175	Texas Instruments Inc	60V, Wide VIN, 4 switch Sync Buck-Boost Controller TSSOP28	TSSOP-28
Vin1, Vout1	2	Red	5005	Keystone	Test Point, Compact, Red, TH	Red Compact
						Testpoint
C30, C34, C36	0(DNP)		08053D105KAT2A	AVX	CAP, CERM, 1 µF, 25 V, +/- 10%, X5R, 0805	0805
C31, C32, C33,	0(DNP)	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 μF, 25 V, +/- 5%, X7R, 0603	0603
C37, C38, C39,						
C40, C43, C44,						
C45						
C35	0(DNP)		08051C103JAT2A	AVX	CAP, CERM, 0.01 μF, 100 V, +/- 5%, X7R, 0805	0805
C41, C42	0(DNP)		06033C473JAT2A	AVX	CAP, CERM, 0.047 μF, 25 V, +/- 5%, X7R, 0603	0603
D4		30V	BAT54A-7-F	Diodes Inc.	Diode, Schottky, 30V, 0.2A, SOT-23	SOT-23
Q1, Q2, Q7, Q8		0.2V	MMBT3904T-7-F	Diodes Inc.	Transistor, NPN, 20V, 0.2A, SOT-523	SOT-523
Q5, Q6, Q11, Q12	0(DNP)	0.25V	MMBT3906T-7-F	Fairchild Semiconductor	TRANS PNP 40V 200MA SOT523	SOT-523
Q13	0(DNP)	40 V	2N2222A	STMicroelectronics	Transistor, NPN, 40 V, 0.6 A, TO-18	TO-18
R21, R26, R27,	0(DNP)	10.0k	CRCW080510K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.125W, 0805	0805
R28, R29, R33,						
R36, R39, R49,						
R51						
R23	0(DNP)		CRCW080578K7FKEA	Vishay-Dale	RES, 78.7k ohm, 1%, 0.125W, 0805	0805
R24	0(DNP)		CRCW080520K0FKEA	Vishay-Dale	RES, 20.0k ohm, 1%, 0.125W, 0805	0805
R30		51.1	RT0805BRD0751R1L	Yageo America	RES, 51.1 ohm, 0.1%, 0.125W, 0805	0805
R31, R34, R37, R42	0(DNP)	1.0k	CRCW06031K00JNEA	Vishay-Dale	RES, 1.0k ohm, 5%, 0.1W, 0603	0603
R32, R40	0(DNP)	100k	CRCW0805100KFKEA	Vishay-Dale	RES, 100k ohm, 1%, 0.125W, 0805	0805
R35, R41	0(DNP)	1.00Meg	CRCW08051M00FKEA	Vishay-Dale	RES, 1.00Meg ohm, 1%, 0.125W, 0805	0805
R38	0(DNP)		CRCW08054K32FKEA	Vishay-Dale	RES, 4.32k ohm, 1%, 0.125W, 0805	0805
R43, R44	0(DNP)		3314J-x-yyyz	Bourns	Potentiometer, 4mm Sq, 0.25W, ±20%	0.197 x 0.197 inch
R46, R47, R48, R50	0(DNP)	2.21k	CRCW08052K21FKEA	Vishay-Dale	RES, 2.21k ohm, 1%, 0.125W, 0805	0805
R52, R53	0(DNP)	470k	RG2012P-474-B-T5	Susumu Co Ltd	RES, 470k ohm, 0.1%, 0.125W, 0805	0805
R54, R55	0(DNP)		CRCW0805150KFKEA	Vishay-Dale	RES, 150k ohm, 1%, 0.125W, 0805	0805
R56, R57, R58, R59, R60, R61	0(DNP)		ERJ-6ENF4752V	Panasonic	RES, 47.5k ohm, 1%, 0.125W, 0805	0805
R62	0(DNP)	1.00k	CRCW08051K00FKEA	Vishay-Dale	RES, 1.00k ohm, 1%, 0.125W, 0805	0805
R63	0(DNP)		CRCW08051K50FKEA	Vishay-Dale	RES, 1.50k ohm, 1%, 0.125W, 0805	0805
R64	0(DNP)		RT0805BRD074K7L	Yageo America	RES, 4.70k ohm, 0.1%, 0.125W, 0805	0805
TP1, TP2, TP3	0(DNP)		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
, , ,	-()			.,	,,	Testpoint

PMP9490_BOM

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
U2	0(DNP)	INA194AID	INA194AIDBV	TI	IC, Current Shunt Monitor, -16V to 80V Common-Mode Range	SOT23-5
		BV				
U3	0(DNP)		TLV274CDA	Texas Instruments	550 uA/Ch, 3 MHz, Rail-to-Rail Output Operational Amplifier, 2.7 to 16 V, 0	D0014A
					to 70 degC, 14-pin SOIC (D0014A), Green (RoHS & no Sb/Br)	
U4, U5	0(DNP)		TLC274ACD	Texas Instruments	LinCMOS(TM) Precision Quad Operational Amplifier, 3 to 16 V, 0 to 70	D0014A
					degC, 14-pin SOIC (D0014A), Green (RoHS & no Sb/Br)	
U6	0(DNP)		TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85	DBZ0003A
					degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.