

Bill of Materials

TI DESIGNS

TIDA-00576

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
		TP_T_D1,TP1,TP_T_D2,TP2,TP_T_D3,T							
		P_T_3D,TP3,TP_T_D4,TP4,TP_T_D5,TP							
		5,PWR5V,DST5V,TP_T_D6,TP6,TP_T_D							
		7,TP7,TP_T_D8,TP8,TP_T_D9,TP9,TP_T _D10,TP10,TP_T_D11,TP11,1P1V,TP_T							
		D12,TP12,TP_T_D13,TP13,TP_T_D14,							
		TP14,TP_T_D15,TP15,TP_T_D16,TP16,							
		TP_T_D17,TP17,TP_T_D18,TP18,1P8V,							
		TP_T_D19,TP19,TP_T_D20,TP20,TP_T_ D21,TP21,TP_T_D22,TP22,TP_T_D23,T							
		P23,TP24,TP25,TP26,TP27,TP28,TP29,T							
		P30,TP31,TP32,3P3V,ILL5P5V,TP_T_VS,							
1	0	TP_T_HS,TP_T_DE,TP_T_D0,PCLKS,PCL KM,LS_WD,LS_SRD,LS_RD,LS_CK,ARSTZ	EM TERM TESTPOINT	hole,plated	NOT A PART			Plated Drill Hole, EM,TERM,TESTPOINT	
	U		Empression out	Потерриятел	NOTA FAINT			Plated Drill Hole,	
		GP5V,TP12V,RGATE,REDC,LSG,I_SW,HS						20mil_Drill_Hole_Plate	
2	0	G,GRNC,GGATE,BLUC,BGATE	20mil_Drill_Hole_Plated	hole,plated	NOT A PART			d	
		S_HP,S_HN,S_FP,S_FN,S_CP,S_CN,S_CK						20mils Test Pad,	
3	0	P,S_CKN,HP,HN,FP,FN,CP,CN,CKP,CKN	20mil_Test_Pad	hole,plated	NOT A PART			20mil_Test_Pad	
		C_QHS1,C_AN1,C_QHS2,C_AN2,C_QHS							
4		3,C_AN3,C_AN4,C149,C153,C158,C161 ,C162,C163,C_ILL	22uF		_				
4	14	,C162,C163,C_ILL	ZZUF	capacitor	Samsung	CL21A226MAQNNNE		805	
		C1,C2,C3,C5,C6,C7,C8,C10,C12,C14,C15 ,C16,C18,C22,C23,C24,C25,C26,C27,C2							
		8,C30,C31,C32,C33,C34,C35,C38,C40,C							
		42,C43,C44,C45,C46,C47,C48,C49,C50,							
		C51,C52,C53,C54,C55,C56,C57,C61,C63							
		,C64,C65,C66,C67,C68,C69,C70,C71,C7 2,C73,C74,C75,C77,C78,C79,C80,C81,C							
		82,C84,C85,C86,C87,C89,C91,C93,C94,							
		C95,C96,C97,C98,C99,C100,C101,C102,							
		C103,C104,C105,C106,C107,C108,C110							
		,C111,C112,C113,C115,C116,C117,C11 8,C119,C120,C121,C122,C123,C124,C1							
		25,C126,C127,C132,C133,C137,C148,C							
5	113	156,C157,C169,C178,C179,C184	0.1uF	capacitor	TDK	CGA2B3X7R1H104K050BB		402	
6	13	88,C109,C114,C144	2.2uF	capacitor	Taiyo Yuden	TMK107ABJ225KA-T		603	
7	2	C19,C21	18pF	capacitor	Murata	GRM1555C1H180JA01D		402	

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
8	15	C147,C151,C152,C154,C155,C166,C167	10uF	capacitor	Murata	GRM21BR61E106KA73L		805	
9	7	C39,C62,C76,C90,C92,C181,C185	10nF	capacitor	Murata	GRM155R71E103KA01D		402	
10	0	C41,C180,C182	0.1uF	capacitor	TDK	CGA2B3X7R1H104K050BB		402	
11	3	C58,C59,C60	10pF	capacitor	Kemet	C0402C100J5GACTU		402	
12	2	C129,C173	15pF	capacitor	TDK	C1005C0G1H150J050BA		402	
13	2	C134,C135	100uF	capacitor	Kemet	T491X107K025AT		2917	
14	0	C136	100uF	capacitor	Kemet	T491X107K025AT		2917	
15	10	C138,C139,C140,C143,C164,C165,C168 ,C172,C175,C176	1.0uF	capacitor	Taiyo Yuden	UMK107BJ105KA-T		603	
16	1	C145	4.7uF	capacitor	TDK	C1608X5R1C475M080AC		603	
17	3	C150,C159,C160	470pF	capacitor	TDK	C1608C0G1H471J080AA		603	
18	0	C170,C177	680pF	capacitor	TDK	C1608C0G1H681J080AA		603	
19	1	C171	1200pF	capacitor	AVX	12065A122JAT2A		1206	
20	1	C174	0.47uF	capacitor	Taiyo Yuden	UMK107ABJ474KA-T		603	
21	1	DN1	BAT54C	Diode Dual	Diodes Inc.	BAT54C-7-F		SOT23	
22	10	D_PROJON,D_MSPREQ,D_MSPACK,D_	LG M67K-G1J2-24-Z	LED Green	OSRAM	LG M67K-G1J2-24-Z		603	
23	1	D_GP5V	LB Q39G-L2N2-35-1	LED Blue	OSRAM	LB Q39G-L2N2-35-1		603	
24	1	D_RSTZ	LS M67K-J2L1-1-Z	LED Red	OSRAM	LS M67K-J2L1-1-Z		603	
25	3	D1,D2,D3	DF3A6.8FUT1G	Diode	ON Semi	DF3A6.8FUT1G		SOT323	
26	1	D4	SMCJ15CA	Diode	Littlefuse	SMCJ15CA		DO-214AB, SMC	
27	2	D5,D7	B240A-13-F	Diode	Diodes Inc.	B240A-13-F		DO-214AC, SMA	
28	1	D6	MBR0540	Diode	Fairchild	MBR0540		SOD123	
29	3	D8,D9,D10	ESDA18-1K	Diode	STM	ESDA18-1K		SOD523	
30	6	D11,D12,D13,D14,D15,D16	DFLS230L-7	Diode	Diodes Inc.	DFLS230L-7		POWERDI123	
31	12	FB1,FB2,FB3,FB4,FB5,FB6,FB7,FB8,FB9, FB10,FB11,FB12	BKP1005EM121-T	Ferrite	Taiyo Yuden	BKP1005EM121-T		402	
32	1	FB13	HI1612X560R-10	Ferrite	Laird SI Products	HI1612X560R-10		1612	
33	1	F1	2410SFV10.0FM/125-2	Fuse	TE	2410SFV10.0FM/125-2		2410 Plated Drill Hole,	
34	0	GP1,GP2,GP3,GP4,GP5,GP6,GP7,GP8	EM,TERM,GOUNDPOINT	hole,plated	NOT A PART			EM,TERM,GROUNPOIN T	
35	0	LSEL1,1P2V,3P3V_SB,TP_VRST,TP_VOF S,TP_VBIAS,RSTZ,RLIM,PROJON,LSEL0,L ED_A,INTZ	tp50rd30	hole,plated	NOT A PART			Plated Drill Hole, tp50rd30,	
36	2	J_PEDID,JRST	M20-8770246	2pos Header	Harwin	M20-8770246		грэогизо,	
37	2	J RED,J GRN,J BLU	874381043	CONN HEADER 10pos	Molex	874381043		1	-
38	0	J DEV	S4B-EH(LF)(SN)	CONN HEADER 1000S CONN HEADER 4pos	JST	874381043 S4B-EH(LF)(SN)		+	
39	4	J_FAN1,J_FAN2,J_FAN3,J_FAN4	B2B-EH	CONN HEADER 2pos				1	-
40	1	J_FAN1,J_FAN2,J_FAN3,J_FAN4 J_FLEX	FH28H-80S-0.5SH(05)	CONN FFC 80pos	JST	B2B-EH-A(LF)(SN)		+	
41	1	J_HDMI	HDMI Type C (Mini)	HDMI-MINI CONN	Hirose TE	FH28H-80S-0.5SH(05)		+ +	
42	4	J_3DG,J_WPC,J_TMP,J_LABB	B3B-ZR	CONN HEADER 3pos	JST	2013978-1		1	-
43	1	J MSPJTAG	5103308-2	CONN HEADER SPOS CONN HEADER LOPRO STR 14POS		B3B-ZR-SM4-TF(LF)(SN 5103308-2		1	-
43	1	J_MSPJTAG J_PWR	PJ-082BH	CONN PWR JACK	TE Connectivity CUI Inc	PJ-082BH		+	
45	1	J_USB		CONN PWR JACK CONN RCPT MICRO USB R/A SMD					-
46	1	L1,L DRST	USB Micro B Rcpt 10uH	Inductor	Molex	1050170001		+	
46	1	L ILLM		Inductor	CoilCraft	LPS4018-103MLB		+	
48	1	-	1.4uH		Coilcraft	MLC1565-142MLB		+	
	3	L2,L3,L4	4.7uH	Inductor	Laird-SI	TYS40304R7M-10		+	
49	1	OSC24M	DSC1121CI1-024.0000	OSC MEMS 24.000MHZ	Micrel	DSC1121CI1-024.0000			

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
50	4	Q_REDG,Q_ILLLS,Q_GRNG,Q_BLUG	CSD17501Q5A	MOSFET N-CH	П	CSD17501Q5A			
51	1	Q_ILLHS	CSD17522Q5A	MOSFET N-CH ,	TI	CSD17522Q5A			
52	5	Q1,Q2,Q3,Q4,Q5	DMN26D0UT-7	MOSFET N-CH	Diodes	DMN26D0UT-7			
		R2,R10,R11,R12,R13,R14,R15,R23,R41, R58,R75,R97,R98,R99,R103,R105,R106, R107,R108,R111,R112,R113,R132,RPCL							
53	25	KS,RPCLKM	22	Resistor, 22, 1/10W, 1%, , 0402	Panasonic	ERJ-2RKF22R0X		402	
54	6	RP1,RP2,RP3,RP4,RP5,RP6	22	Resistor	Panasonic	EXB-N8V220JX		804	
55	1	RT1	100K	Thermistor	Murata	NCP15WF104F03RC		402	
		R1,R4,R7,R8,R16,R19,R21,R22,R34,R35, R38,R39,R40,R45,R46,R54,R55,R56,R57 R59,R60,R61,R62,R63,R64,R66,R67,R6 8,R69,R70,R71,R72,R73,R74,R76,R77,R 78,R79,R80,R86,R88,R95,R109,R110,R1							
56	47	21,R136,R138	10k	Resistor	Panasonic	ERJ-2GEJ103X		402	
57	2	R3,R24	1M	Resistor	Panasonic	ERJ-2GEJ105X		402	
58	0	R5,R32	10k	Resistor	Panasonic	ERJ-2GEJ103X		402	
59	2	R6,R33	47k	Resistor	Panasonic	ERJ-2GEJ473X		402	
60	0	R9,R17,R30,R37,R82,R83,R85	0	Resistor	Panasonic	ERJ-2GE0R00X		402	
61	21	R18,R27,R29,R42,R43,R44,R96,R102,R1 26,R128,R133,R134,R135,R139,R141,R 142,R145,R149,R150,R151	0	Resistor	Panasonic	ERJ-2GE0R00X			
62	1	R20	300k	Resistor	Panasonic	ERJ-2RKF3003X		402	
63	1	R25	1.5k	Resistor	Panasonic	ERJ-3GEYJ152V		603	
64	3	R26,R100,R104	3.16k	Resistor	Panasonic	ERJ-3EKF3161V		603	
	3	R28,R31,R36,R47,R48,R49,R50,R51,R52,R53,R65,R81,R84,R87,R91,R92,R101,R	3.201		a diagonic	EIO JENI JIOZV		003	
65	21	114,R117,R125,R153	1k	Resistor	Yageo	RC0402FR-071KL		402	
66	2	R89,R90	43	Resistor	Panasonic	ERJ-2RKF43R0X		402	
67	3	R93,R94,R152	100k	Resistor	Panasonic	ERJ-3EKF1003V		603	
68	1	R115	63.4K	Resistor	Panasonic	ERJ-2RKF6342X		402	
69	0	R116	3.16k	Resistor	Panasonic	ERJ-3EKF3161V		402	
70	1	R118	20.0k	Resistor	Yageo	RC0402FR-0720KL		402	
71	0	R119	1.5k	Resistor	Panasonic	ERJ-3GEYJ152V		603	
72	1	R120	0	Resistor	Stackpole	RMCF2512ZT0R00		2512	
73	5	R122,R123,R124,R130,R131	10	Resistor	Rohm	ESR03EZPF10R0		603	
74	1	R127	0	Resistor	Panasonic	ERJ-6GEY0R00V		805	
75	1	R129	3.9	Resistor	Rohm	ESR25JZPJ3R9		1210	
76	3	R140,R143,R144	30k	Resistor	Panasonic	ERA-2AEB303X		402	
77	2	R25m1,R25m2	0.025	Resistor	TT Electronics	LRC-LRF2010LF-01-R025F		2010	
78	1	SW_MSPONOFF	GT11MSCBE	SWITCH TOGGLE	CK Components	GT11MSCBE			
79	0	SW1	TL1105F100Q	SWITCH TACTILE	Eswitch	TL1105F100Q			
80	2	TGND1,TGND2	EM,TERM,5051 GND TESTPOINT	TEST POINT PC MINI	Keystone	5001			
81	2	UDLPC_S,UDLPC_M	DLPC3439	DLP Controller	Texas Instruments	DLPC3439ZEZ		DPP3439_13mmx13m m_VFBGA_201balls	

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
82	1	U_CYP	CY7C65215	CY7C65215	Cypress	CY7C65215-32LTXI		32-VFQFN	
83	1	U_DLPA	DLPA3005	DLPA3005 PMIC	Texas Instruments	DLPA3005CPFDR			
84	1	U_EDIDROM	M24C02-WMN	IC EEPROM 2KBIT	STMicro	M24C02-WMN6TP		8SOIC	•
85	2	U_FLBS,U_FLBM	SN74AVC4T774PWR	IC BUS TRANSCVR 4BIT	Texas Instruments	SN74AVC4T774PWR		16-TSSOP	
86	2	U_FLSHS,U_FLSHM	W25Q64FVSSIG	IC FLASH 64MBIT	Winbond	W25Q64FVSSIG		8SOIC	
87	1	U_ITE	IT6801FN	HDMI 1.4 Receiver	ITE Tech Inc	IT6801FN		ITE6801_76pin_QFN	
88	1	U_LDO12	TLV70012DDC	IC REG LDO	Texas Instruments	TLV70012DDCT		5-SOT	
89	1	U_MSP	MSP430F22x4	MCU MSP430 16BIT 32KB FLASH	Texas Instruments	MSP430F2274IDAR		38-TSSOP	
90	1	U_OSCBUF	CDCLVC1102PWR	IC CLK BUFFER 1:2 250MHZ	Texas Instruments	CDCLVC1102PWR		8-TSSOP	
91	1	U_SBSW	TPS560200	IC REG BUCK SYNC	Texas Instruments	TPS560200DBVR		5SOT23	
92	1	U_UESD	TPD2E2U06	TVS DIODE	Texas Instruments	TPD2E2U06DRLR		SOT-553	
93	1	U_ZDB	PL123E-05SC-R	IC CLK ZDB 1:5 220MHZ	Micrel	PL123E-05SC-R		8SOIC	
94	1	U1	TPS2061CDBVT	IC SWITCH PWR DIST SNGL	Texas Instruments	TPS2061CDBVT		SOT23-5	
95	2	U2,U3	TPD4E05U06DQAR	HDMI 1.4 ESD TVS DIODE	Texas Instruments	TPD4E05U06DQAR		10-SON	
96	5	U4,U7,U8,U9,U12	74AUP1G07DCK	IC BUFF/DVR LOW PWR N-INV	Texas Instruments	SN74AUP1G07DCKR		5-TSSOP	
97	1	U5	TC7WB66CFK	IC DUAL BUS SWITCH	Toshiba	TC7WB66CFK,LF		8-VFSOP	
98	3	U6,U10,U11	74AUP1G06DCK	IC INVERTER SINGLE	Texas Instruments	SN74AUP1G06DCKT			
99	1	X1	27MHz	CRYSTAL 27MHZ	стѕ	403C35D27M00000			
100	1	R137	300	Resistor	Panasonic	ERJ-2RKF3000X		402	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.