

## PMP7921 REV 1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
IPC B?	1		PMP7850 RevB	Any	PMP7850 RevB	N/A
C1, C2, C19, C21	4	470pF	GRM2165C2A471JA01D	MuRata	CAP, CERM, 470pF, 100V, +/-5%, C0G/NP0, 0805	0805
C3	1	330uF	10SVPS330M	Panasonic	CAP, AL, 330uF, 10V, +/-20%, SMD	SVPS
C4, C5, C22, C23	4	180uF	16SVP180MX	Sanyo	CAP, AL, 180uF, 16V, +/-20%, SMD	SVP
C6, C7, C8, C9, C10, C24, C25, C26, C27, C28	10	10uF	C3216X5R1C106M	TDK	CAP, CERM, 10uF, 16V, +/-20%, X5R, 1206	1206
C11, C13, C29, C31	4	0.47uF	GRM188R71E474KA12D	MuRata	CAP, CERM, 0.47uF, 25V, +/-10%, X7R, 0603	0603
C12, C16, C30, C33	4	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	0603
C14, C32	2	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1uF, 25V, +/-10%, X7R, 0603	0603
C15	1	0.1uF	GRM188R71E104KA01D	MuRata	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0603	0603
C17	1	0.047uF	GRM188R71E473KA01D	MuRata	CAP, CERM, 0.047uF, 25V, +/-10%, X7R, 0603	0603
C18	1	470pF	06035A471JAT2A	AVX	CAP, CERM, 470pF, 50V, +/-5%, C0G/NP0, 0603	0603
C20	1	0.047uF	06033C473JAT2A	AVX	CAP, CERM, 0.047uF, 25V, +/-5%, X7R, 0603	0603
C34	1	0.01uF	GRM188R71C103KA01D	MuRata	CAP, CERM, 0.01uF, 16V, +/-10%, X7R, 0603	0603
Cinx	1	1.8mF	16ME1800AX	SUNCON	CAP, Aluminum, 1800uF, 16V, [TH]	12.5mm X 25mm
D1, D3, D4, D5	4	0.57V	PMEG6010CEH,115	NXP Semiconductor	Diode, Schottky, 60V, 1A, SOD-123F	SOD-123F
IN1, OUT1, Sync In 1, Sync In 2, TP5, TP6, TPx	7	White	5002	Keystone	Test Point, TH, Miniature, White	Keystone5002
J1, J2, J3, J4	4		575-4	Keystone	Standard Banana Jack, Uninsulated, 5.5mm	Keystone_575-4
L1, L2	2	2.2uH	SER2915H-222KL	Coilcraft	Inductor, Shielded E Core, Ferrite, 2.2uH, 30A, 0.00186 ohm, SMD	SER29xx
Q1, Q2, Q3, Q4, Q5, Q6, Q7, Q8	8	25V	CSD16415Q5	Texas Instruments	MOSFET N-CH 25V 8SON	SON 5x6mm
R1, R2, R19, R23	4	7.5	ERJ-12ZYJ7R5U	Panasonic	RESISTOR 7.5 OHM 3/4W 5% 2010	2010
R3, R3x, R24, R24x	4	0.001	ERJ-M1WTF1M0U	Panasonic	RES, 0.001 ohm, 1%, 1W, 2512	2512
R4, R7, R8, R13, R14, R15, R27, R28, R30, R31, R32	11	0	ERJ-3GEY0R00V	Panasonic	RES, 0 ohm, 5%, 0.1W, 0603	0603
R5, R6, R25, R26	4	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100 ohm, 1%, 0.1W, 0603	0603
R9	1	158k	CRCW0603158KFKEA	Vishay-Dale	RES, 158k ohm, 1%, 0.1W, 0603	0603
R10	1	49.9k	CRCW060349KFKEA	Vishay-Dale	RES, 49.9k ohm, 1%, 0.1W, 0603	0603
R11, R29	2	3.3	CRCW06033R30JNEA	Vishay-Dale	RES, 3.3 ohm, 5%, 0.1W, 0603	0603
R12	1	15.0k	RC0603FR-0715KL	Yageo America	RES, 15.0k ohm, 1%, 0.1W, 0603	0603
R16, R33	2	36.5k	CRCW060336K5FKEA	Vishay-Dale	RES, 36.5k ohm, 1%, 0.1W, 0603	0603
R17, R34	2	78.7k	CRCW060378K7FKEA	Vishay-Dale	RES, 78.7k ohm, 1%, 0.1W, 0603	0603
R18	1	2.21k	CRCW06032K21FKEA	Vishay-Dale	RES, 2.21k ohm, 1%, 0.1W, 0603	0603
R20	1	2.67k	CRCW06032K67FKEA	Vishay-Dale	RES, 2.67k ohm, 1%, 0.1W, 0603	0603
R21	1	23.2k	CRCW060323K2FKEA	Vishay-Dale	RES, 23.2k ohm, 1%, 0.1W, 0603	0603
R22	1	604	CRCW0805604RFKEA	Vishay-Dale	RES, 604 ohm, 1%, 0.125W, 0805	0805
U1, U2	2		LM5122MHX/NOPB	Texas Instruments	Wide Input Synchronous Boost Controller with Multiple Phase Capability, PWP0020A	PWP0020A
Vin1, Vout1	2	Red	5000	Keystone	Test Point, TH, Miniature, Red	Keystone5000
Vin Gnd1, Vout Gnd1	2	Black	5001	Keystone	Test Point, TH, Miniature, Black	Keystone5001

<b>Designator</b>	<b>Quantity</b>	<b>Value</b>	<b>PartNumber</b>	<b>Manufacturer</b>	<b>Description</b>	<b>PackageReference</b>
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.