

Variant: 001
 Generated: 8/1/2016 11:45:45 AM
 TID #: PMP10726



PMP10726 REV E3 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	PCB1	1		PMP10726	Any	Printed Circuit Board	
2	C1, C19	2	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 uF, 25 V, +/- 10%, X7R, 0603	0603
3	C2, C17	2	0.22uF	C1005X7R1C224K050BC	TDK	CAP, CERM, 0.22 uF, 16 V, +/- 10%, X7R, 0402	0402
4	C3, C5, C18	3	100pF	GRM1535C1H101JDD5D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
5	C4	1	0.22uF	C1608X7R1H224K080AB	TDK	CAP, CERM, 0.22uF, 50V, +/-10%, X7R, 0603	0603
6	C6	1	0.047uF	C1005X7R1H473K050BB	TDK	CAP, CERM, 0.047 uF, 50 V, +/- 10%, X7R, 0402	0402
7	C7, C10	2	0.1uF	GCM188R71H104KA57D	MuRata	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
8	C8	1	0.022uF	GCM155R71H223KA55D	MuRata	CAP, CERM, 0.022 uF, 50 V, +/- 10%, C0G/NP0, 0402	0402
9	C9	1	1000pF	885012205061	Würth Elektronik	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0402	0402
10	C11	1	68pF	GRM1555C1H680JA01D	MuRata	CAP, CERM, 68 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
11	C13	1	220pF	GRM1555C1H221JA01D	MuRata	CAP, CERM, 220 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
12	C14	1	47uF	UUD1E470MCL1GS	Nichicon	CAP, AL, 47 uF, 25 V, +/- 20%, 0.44 ohm, SMD	6.3x5.8
13	C15	1	4.7uF	GRM21BR71C475KA73L	MuRata	CAP, CERM, 4.7 uF, 16 V, +/- 10%, X7R, 0805	0805
14	Cin1	1	4.7uF	GRM31CR71H475KA12L	MuRata	CAP, CERM, 4.7 uF, 50 V, +/- 10%, X7R, 1206	1206
15	Cin2, Cin3, Cin4	3	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 uF, 50 V, +/- 10%, X7R, 1210	1210
16	Co1, Co2, Co3	3	22uF	GRM32ER71E226KE15L	MuRata	CAP, CERM, 22 uF, 25 V, +/- 10%, X7R, 1210	1210
17	Co4	1	10uF	C3216X7R1E106M160AE	TDK	CAP, CERM, 10 uF, 25 V, +/- 20%, X7R, 1206_190	1206_190
18	Co5	1	10uF	EMK212BB7106MG-T	Taiyo Yuden	CAP, CERM, 10 uF, 16 V, +/- 20%, X7R, 0805	0805
19	D1	1	45V	BAS 52-02V H6327	Infineon Technologies	Diode, Schottky, 45 V, 0.75 A, SOD-523	SOD-523
20	D2, D3	2	100V	BAS516,115	NXP Semiconductor	Diode, Switching, 100V, 0.25A, SOD-523	SOD-523
21	D4	1	30V	SMAJ30CA	Littelfuse	Diode, TVS, Bi, 30 V, 400 W, SMA	SMA
22	H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
23	H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
24	J1	1		FTSH-102-01-F-DV	Samtec	Header, 1.27mm, 2x2, Gold, SMT	Header, 1.27mm, 2x2, SMT
25	L1	1	5.6uH	XAL5050-562MEB	Coilcraft	Inductor, Shielded, Composite, 5.6 uH, 6.3 A, 0.03 ohm, SMD	XAL5050
26	QH1, QH2, QL1, QL2	4	40V	BSZ097N04LS G	Infineon Technologies	MOSFET, N-CH, 40 V, 40 A, PG-TSDSON-8	PG-TSDSON-8
27	R1, R2, R3, R4	4	10	CRCW040210R0JNED	Vishay-Dale	RES, 10, 5%, 0.063 W, 0402	0402
28	R5	1	2.49k	CRCW04022K49FKED	Vishay-Dale	RES, 2.49 k, 1%, 0.063 W, 0402	0402
29	R6, R20	2	49.9k	CRCW040249K9FKED	Vishay-Dale	RES, 49.9 k, 1%, 0.063 W, 0402	0402
30	R7	1	24.9	CRCW060324R9FKEA	Vishay-Dale	RES, 24.9, 1%, 0.1 W, 0603	0603
31	R8	1	115k	CRCW0402115KFKED	Vishay-Dale	RES, 115 k, 1%, 0.063 W, 0402	0402
32	R8a	1	9.53k	CRCW04029K53FKED	Vishay-Dale	RES, 9.53 k, 1%, 0.063 W, 0402	0402
33	R8b	1	4.87k	CRCW04024K87FKED	Vishay-Dale	RES, 4.87 k, 1%, 0.063 W, 0402	0402
34	R8c	1	2.80k	CRCW04022K80FKED	Vishay-Dale	RES, 2.80 k, 1%, 0.063 W, 0402	0402
35	R8d	1	2.10k	CRCW04022K10FKED	Vishay-Dale	RES, 2.10 k, 1%, 0.063 W, 0402	0402
36	R9	1	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
37	R10	1	3.57k	CRCW04023K57FKED	Vishay-Dale	RES, 3.57 k, 1%, 0.063 W, 0402	0402
38	R11	1	64.9k	CRCW040264K9FKED	Vishay-Dale	RES, 64.9 k, 1%, 0.063 W, 0402	0402
39	R12, R13, R15, RH1, RH2, RL1, RL2	7	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
40	R14, R16	2	100	CRCW0402100R0FKED	Vishay-Dale	RES, 100, 1%, 0.063 W, 0402	0402
41	R17, R18	2	3.32k	CRCW04023K32FKED	Vishay-Dale	RES, 3.32 k, 1%, 0.063 W, 0402	0402
42	R19	1	200k	CRCW0402200KFKED	Vishay-Dale	RES, 200 k, 1%, 0.063 W, 0402	0402
43	RS1, RS2	2	0.01	WSP1206R0100FEA	Vishay-Dale	RES, 0.01, 1%, 1 W, 1206	1206
44	TP1, TP2, TP3, TP4	4		5019	Keystone	Test Point, Miniature, SMT	Test Point, Miniature, SMT
45	U1	1		LM5175PWPR	Texas Instruments	42V Wide VIN 4-Switch Synchronous Buck-Boost Controller, PWP0028F	PWP0028F
46	U2	1		TPS70933DBVR	Texas Instruments	150-mA, 30-V, 1-uA IQ Voltage Regulator with Enable, DBV0005A	DBV0005A
47	U3	1		TPL0401A-10DCKR	Texas Instruments	128 TAPS Single Channel Digital Potentiometer with I2C Interface, DCK0006A	DCK0006A
48	C12	0	100pF	GRM1535C1H101JDD5D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
49	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2016, Texas Instruments Incorporated