

Count	RefDes	Value	Description	Size	Manufacturer Part #
1	C1	1000PF	CAP_SM-CE,1000PF,50V,10%,PB-FR_X7R_0402	C0402	STD
1	C2	47UF	PCAP_SM-AL,47UF,100V,20%,5454_PB-FR	C5454	EEEFK2A470AQ
2	C3,C5	2.2UF	CAP_SM-CE,2.2UF,100V,10%,1210_X7R	C1210	GRM32ER72A225KA35
1	C4	2.2UF	CAP_SM-CE,2.2UF,100V,10%,X7R_1206_PB-FR	C1206	C3216X7S2A225K
1	C6	10UF	CAP_SM-CE,10UF,16V,10%,0805_X5R_1.25MMH_PB-FR	C0805	STD
1	C7	100PF	CAP_SM-CE,100PF,50V,5%,0402_PB-FR	C0402	STD
1	C8	1000PF	CAP_SM-CE,1000PF,3000V,10%,1808_X7R_2.2MMH_PB-FR	C1808	1808HC102KAZ
1	C9	0.1UF	CAP_SM-CE,0.1UF,50V,10%,0603_X7R	C0603	STD
1	C10	0.047UF	CAP_SM-CE,0.047UF,25V,10%,0603_X7R_PB-FR	C0603	STD
0	C11	100PF	CAP_SM-CE,100PF,50V,5%,0402_PB-FR	C0402	STD
1	C12	1000PF	CAP_SM-CE,1000PF,100V,5%,C0G_1206	C1206	STD
2	C13,C22	0.47UF	CAP_SM-CE,0.47UF,16V,10%,0402_X5R	C0402	STD
2	C14,C16	100UF	CAP_SM-CE,100UF,6.3V,20%,1210_X5R_PB-FR	C1210	GRM32ER60J107ME20K
3	C15,C19,C20	2.2UF	CAP_SM-CE,2.2UF,25V,20%,0402_X5R	C0402	STD
1	C18	100PF	CAP_SM-CE,100PF,3KV,10%,1812	C1812	C4532C0G3F101K160KA
1	C21	10UF	CAP_SM-CE,10UF,10V,20%,0603_X5R_PB-FR	C0603	STD
1	C59	0.1UF	CAP_SM-CE,0.1UF,50V,10%,0402_X5R	C0402	STD
2	C17,C60	330UF	PCAP_SM-TA,330UF,6.3V,20%,2816_MAX_ESR_PB-FR	C7343	T530D337M006ATE010
1	CR2		ZENER_SM_CA-FAIRCHILD_MMSZ5244B,14V	DSOD123	MMSZ5244B
1	CR3		DIODE_SM1-BAV21W-F,250V	DSOD123	BAV21W
1	CR4		DIODE_SMA-ES1D-13-F,200V	SMA	ES1D-13
1	CR6		SCHOTTKY_DUAL_S_SOT-BAT54S,0.4V	SOT23	BAT54S
1	CR8		DIODE_DUALCK_SOT-MMBD4148CC,100V	SOT23	MMBD4148CC
1	CR9		ZENER_SOT-BZX84C5V1_PB-FR,5.1V	SOT23	BZX84C5V1
1	CR10		DIODE_SMA-B340A-13-F,40V	SMA	B340A
1	CR12		ZENER_SM-MMSZ4685T1G,3.6V	DSOD123	MMSZ4685T1G
1	J1		CON1X3_F-ST,NONE,AMP_A-1JA,COAX_AMC_PB-FR	CON-3	A1JB
2	J2,J3		TERM_BLK1X2_TH-ST,NONE,MOLEX_282841-2	TBLK-2	EDZ350/2
1	P1		HDR1X2_M-ST,PB-FR,TSW-102-07-L-S	CON-2	TSW-102-07-L-S
1	Q2		NMOSFET_PP8_PP8-NONE,BSC190N15NS3_G	SO-8	BSC190N15NS3
1	Q3		NMOSFET_PP8_PP8-60V_12A,CSD18543Q3A	PWRPAK-8	CSD18543Q3A
1	Q4		NPN_SOT-NONE,MMBT3904	SOT23	MMBT3904
1	R1	100K	RES_SM-TF,100K,0.125W,1%,1206	R1206	STD
1	R2	3.24K	RES_SM-TF,3.24K,0.063W,1%,0603_PB-FR	R0603	STD

1	R3	3.3	RES_SM-TF,3.3,0.125W,5%,1206	R1206	STD
1	R4	31.6K	RES_SM-TF,31.6K,0.063W,1%,0402_PB-FR	R0402	STD
1	R5	20	RES_SM-TF,20,0.125W,1%,1206	R1206	STD
1	R6	1K	RES_SM-TF,1K,0.1W,5%,0603_PB-FR	R0603	STD
2	R7,R28	10K	RES_SM-TF,10K,0.250W,5%,1206_PB-FR	R1206	STD
2	R8,R9	0	RES_SM-TF,0,0.063W,5%,0402_PBFREE	R0402	STD
1	R11	43	RES_SM-TF,43,0.5W,5%,2010	R2010	STD
1	R12	499	RES_SM-TF,499,0.063W,1%,0603_PB-FREE	R0603	STD
1	R13	1K	RES_SM-TF,1K,0.063W,1%,0402_PB-FR	R0402	STD
2	R14,R27	10K	RES_SM-TF,10K,0.063W,1%,0402_FB-FR	R0402	STD
1	R15	33	RES_SM-TF,33,0.063W,5%,0402	R0402	STD
1	R16	10K	RES_SM-TF,10K,0.063W,0.1%,PB-FR_0402	R0402	STD
1	R17	6.04K	RES_SM-TF,6.04K,0.063W,0.1%,0402_PB-FR	R0402	STD
1	R18	0.33	RES_SM-TF,0.330,0.5W,2%,1206	R1206	STD
1	R19	10	RES_SM-TF,10,0.125W,5%,0805_PB-FR	R0805	STD
1	R20	300	RES_SM-TF,300,0.125W,1%,0805	R0805	STD
0	R21	1.2K	RES_SM-TF,1.2K,0.063W,5%,0603	R0603	STD
1	R22	270K	RES_SM-TF,270K,0.063W,5%,0603	R0603	STD
1	R23	56K	RES_SM-TF,56K,0.063W,5%,0603	R0603	STD
1	R24	6.2K	RES_SM-TF,6.2K,0.063W,5%,0603	R0603	STD
1	R25	100K	RES_SM-TF,100K,0.063W,1%,0402_TKF_PB-FR	R0402	STD
1	R29	2K	RES_SM-TF,2K,0.063W,1%,0402_PB-FR	R0402	STD
1	R37	49.9	RES_SM-TF,49.9,0.063W,1%,0402_PB-FR	R0402	STD
1	T2	100UH	KA4759_AL_SM12-100UH,PWR_XFMR_250KHZ	TXFMR-12	KA4759-AL
2	TP1,TP3		TESTPOINT_NO_PN-TH,60RD,RED_2.54X4.57MM	TESTPOINT	5000
2	TP2,TP4		TESTPOINT_NO_PN-TH,60RD,PC-MINI	TESTPOINT	5001
1	U1		LM5020_SON10-100V_CUR_MOD_PWM_CNTRL	DFN-10	LM5020SD-1/NOPB
1	U2		OPTO_SO4-HMHA2801A,3750V	SO-4	HMHA2801A
1	U3		LMV431_SOT23_3-VREG_SHUNT_PB-FR	SOT23	LMV431AIMF/NOPB
1	U4		UCC24610_DFN8-HI-PERFRMNCE_CNTRLR_DRVR	DFN-8	UCC24610DRB

TOTAL=

74

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2019, Texas Instruments Incorporated