Variant: 001

Generated: 7/18/2016 1:07:13 PM

TID #: 00887

TIDA-00887 REV E1 Bill of Materials



lt a.u. #	Declarator	O	Value	Douthlymshau	Manufacturer	Description	Deelson-Defenence
Item#	Designator !PCB1	Quantity 1	Value	PartNumber TIDA-xxxx	Manufacturer	Description Printed Circuit Board	PackageReference
2	C1		0.1uF	GRM188R71C104KA01D	Any MuRata		0603
3	C2, C3		4.7uF	GRM32ER71H475KA88L	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0603 CAP, CERM, 4.7 µF, 50 V, +/- 10%, X7R, 1210	1210
4	C4		0.22uF	GRM21BR71H224KA01L	MuRata	CAP, CERM, 0.22 µF, 50 V, +/- 10%, X7R, 1210	0805
5	C5	1	1uF	GRM21BR71E105KA99L	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0805	0805
6	C6, C7	2	47uF	GRM32ER61C476ME15L	MuRata	CAP, CERM, 47 µF, 16 V, +/- 20%, X7R, 0003	1210
7	C8, C35, C39	3	10uF	C2012X7R0J106M125AB	TDK	CAP, CERM, 10 µF, 6.3 V, +/- 20%, X7R, 0805	0805
8	C9		0.022uF	GRM155R71C223KA01D	MuRata	CAP, CERM, 0.022 µF, 16 V, +/- 10%, X7R, 0402	0402
9	C10, C11, C14,	4	10uF	0805YD106MAT2A	AVX	CAP, CERM, 10 µF, 16 V, +/- 20%, X5R, 0805	0805
	C18			00001210011211		ο, α, σε, απ, το μι, το τ, τ, εσου, ποι η σσου	
10	C12	1	0.56uF	12063C564KAT2A	AVX	CAP, CERM, 0.56 µF, 25 V, +/- 10%, X7R, 1206	1206
11	C13, C19	2	1000pF	202R18W102KV4E	Johanson Technology	CAP, CERM, 1000 pF, 2000 V, +/- 10%, X7R, 1206_190	1206_190
12	C15	1	1uF	GRM155R70J105MA12D	MuRata	CAP, CERM, 1 µF, 6.3 V, +/- 20%, X7R, 0402	0402
13	C16, C17	2	20pF	GRM1555C1H200JA01D	MuRata	CAP, CERM, 20 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
14	C20, C21, C24,	8	0.01uF	GRM155R71H103KA88D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0402	0402
	C26, C29, C30, C31, C32						
15	C22, C23, C25, C27, C33, C34	6	0.1uF	TMK105B7104MV-FR	Taiyo Yuden	CAP, CERM, 0.1 μF, 25 V, +/- 20%, X7R, 0402	0402
16	C28, C37	2	100uF	C1210C107M8PACTU	Wurth Elektronik	CAP, CERM, 100 µF, 10 V, +/- 20%, X5R, 1210	1210
17	C36, C38	2	1uF	GCM31CR72A105KA03	MuRata	CAP, CERM, 1 µF, 100 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206_190	1206_190
18	D1	1	60V	PDS560-13	Diodes Inc.	Diode, Schottky, 60 V, 5 A, PowerDI5	PowerDI5
19	D2	1	Green	LTST-C171GKT	Lite-On	LED, Green, SMD	LED_0805
20	J1, J3	2		575-4	Keystone	Standard Banana Jack, Uninsulated, 5.5mm	Keystone_575-4
21	J2	1		67068-8000	Molex	Connector, Receptacle, USB TYPE B, R/A, Top Mount TH	USB Type B Receptacle
22	J4, J7	2		292303-4	TE Connectivity	Connector, Receptacle, USB Type A, R/A, Top Mount TH	USB Type A right angle
23	J5, J6, J8, J9	4		PEC03SAAN	Sullins Connector Solutions	Header, 100mil, 3x1, Tin, TH	Header, 3 PIN, 100mil, Tin
24	L1	1	5.5uH	744325550	Wurth Elektronik eiSos	Inductor, Shielded Drum Core, Superflux, 5.5 µH, 10 A, 0.0112 ohm, SMD	WE-HC6
25	L2, L3, L4, L5	4	10nH	LQG15HS10NJ02D	MuRata	Inductor, Multilayer, Air Core, 10nH, 0.3A, 0.26 ohm, SMD	0402 polarized
26	R1	1	100k	CRCW0402100KDHEDP	Vishay-Dale	RES, 100 k, 0.5%, 0.063 W, 0402	0402
27	R2	1	255	CRCW0402255RFKED	Vishay-Dale	RES, 255, 1%, 0.063 W, 0402	0402
28	R3	1	17.8k	CRCW040217K8FKED	Vishay-Dale	RES, 17.8 k, 1%, 0.063 W, 0402	0402
29	R4		49.9k	CRCW040249K9FKED	Vishay-Dale	RES, 49.9 k, 1%, 0.063 W, 0402	0402
30	R5	1	1.87k	CRCW04021K87FKED	Vishay-Dale	RES, 1.87 k, 1%, 0.063 W, 0402	0402
31	R6, R7	2	30.1	CRCW040230R1FKED	Vishay-Dale	RES, 30.1, 1%, 0.063 W, 0402	0402
32	R8	1	1.00Meg	CRCW04021M00FKED	Vishay-Dale	RES, 1.00 M, 1%, 0.063 W, 0402	0402
33	R9		4.99k	CRCW04024K99FKED	Vishay-Dale	RES, 4.99 k, 1%, 0.063 W, 0402	0402
34	R10		9.53k	CRCW04029K53FKED	Vishay-Dale	RES, 9.53 k, 1%, 0.063 W, 0402	0402
35	R11		1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
36	R12, R14, R16		4.7k	CRCW04024K70JNED	Vishay-Dale	RES, 4.7 k, 5%, 0.063 W, 0402	0402
37	R13, R19		86.6k	CRCW060386K6FKEA	Vishay-Dale	RES, 86.6 k, 1%, 0.1 W, 0603	0603
38	R15, R20	2	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
39	R17		90.9k	CRCW040290K9FKED	Vishay-Dale	RES, 90.9 k, 1%, 0.063 W, 0402	0402 0402
40	R18 T1, T2	2	10.0k	CRCW040210K0DHEDP	Vishay-Dale	RES, 10.0 k, 0.5%, 0.063 W, 0402	0402
41 42	TP1, TP3	2	Orange	mcf12102g900 5008	Taiyo Yuden Keystone	SMT Common Mode Choke Test Point, Compact, Orange, TH	Orange Compact Testpoint
43	TP2	1		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
44	U1	1		LMR14050SQDDARQ1	Texas Instruments	SIMPLE SWITCHER 40 V 5 A, 2.2 MHz Step-Down Converter with 40 uA IQ, DDA0008E	DDA0008E
45	U2	1		TPD2E2U06QDBZRQ1	Texas Instruments	Dual-Channel High-Speed ESD Protectiong Device, DBZ0003A	DBZ0003A
46	U3	1		TPS74801RGWR	Texas Instruments	Single Output LDO, 1.5 A, Adjustable 0.8 to 3.6 V Output, 0.8 to 5.5 V Input, with Programmable Soft Start, 20-pin VQFN (RGW), -40 to 125 degC, Green (RoHS & no Sb/Br)	RGW0020A
47	U4	1		TPS7A4533DCQR	Texas Instruments	Single Output Fast Transient Response LDO, 1.5 A, Fixed 3.3 V Output, 2.1 to 20 V Input, 6-pin SOT-223 (DCQ), -40 to 125 degC, Green (RoHS & no Sb/Br)	DCQ0006A
48	U5	1		TUSB4020BIPHP	Texas Instruments	400 Mbps IEEE 1394a One-Port Cable Transceiver / Arbiter, 3.3V, 0 to 70 degC, 48-Pin HTQFP (PHP), Green (RoHS & no Sb/Br)	PHP0048C
49	U6, U8	2		TPD3S716QDBQRQ1	Texas Instruments	AUTOMOTIVE USB 2.0 Interface Protection with Short-to-Battery, Short-to-Ground Protection, and Adjustable Current Limit, DBQ0016A	DBQ0016A
50	Y1	1		445C25D24M00000	CTS Freq Controls	Crystal, 24.000MHz, 20pF, SMD	Crystal, XTAL_2_SM_197X12 6
51	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
<u> </u>			!	1	1		1

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/sampterms.htm).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated