TIDA-01407 REV B Bill of Materials



Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	150uF	EEV-FK2A151M	Panasonic	CAP, AL, 150 µF, 100 V, +/- 20%, 0.17 ohm, AEC-Q200 Grade 2, SMD	SMT Radial J16
2	C2, C3, C4, C5	4	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 µF, 100 V, +/- 10%, X7R, 1210	1210
3	C2, C3, C4, C5 C6, C7	2	2.2uF 0.1uF	GRM32ER72A225KA35L GRM31CR72E104KW03L	MuRata	CAP, CERM, 2.2 µF, 100 V, +/- 10%, X/R, 1210 CAP, CERM, 0.1 µF, 250 V, +/- 10%, X/R, 1206	1210
4	C8	1	DNP	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 µF, 100 V, +/- 10%, X7R, 1210	1210
5	C9	1	170nH Custom	170nH Custom Shim		Inductor, Flat Wire, 680 nH, 3.5 A, 0.035 ohm, SMD	3.2x1.2x2.5mm
6	C10, C11, C12, C13, C14, C15,	16	Shim 22uF	GRM32ER71E226KE15L	MuRata	CAP, CERM, 22 µF, 25 V, +/- 10%, X7R, 1210	1210
	C16, C17, C18, C19, C20, C22, C23, C24, C25, C26						
7	C21	1	33uF	EKZE350ELL330ME11D	Chemi-Con	CAP, AL, 33 µF, 35 V, +/- 20%, TH	D5xL11mm
8	C27, C28	2	DNP	16TQC150MYF	Panasonic	CAP, Tantalum Polymer, 150 µF, 16 V, +/- 20%, 0.05 ohm, 7343-31 SMD	7343-31
9	C29	1	DNP	GRM1885C1H470JA01D	MuRata	CAP, CERM, 47 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
10	C30	1	330pF	GRM1885C1H331JA01D	MuRata	CAP, CERM, 330 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
11 12	C31 C32, C33, C36, C38, C42, C44	1 6	0.01uF 1uF	GRM188R71H103KA01D GRM188R71E105KA12D	MuRata MuRata	CAP, CERM, 0.01 μF, 50 V, +/- 10%, X7R, 0603 CAP, CERM, 1 μF, 25 V, +/- 10%, X7R, 0603	0603 0603
13	C34	1	820pF	GRM1885C1H821JA01D	MuRata	CAP, CERM, 820 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
14	C35	1	0.047uF	GRM188R71H473KA61D	MuRata	CAP, CERM, 0.047 μF, 50 V, +/- 10%, X7R, 0603	0603
15	C37, C39, C40, C41, C43, C45	6	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
16	D1, D2	2	200V	ES1D-13-F	Diodes Inc.	Diode, Ultrafast, 200 V, 1 A, SMA	SMA
17	D3	1	100V	1N4148W-7-F	Diodes Inc.	Diode, Ultrafast, 100 V, 0.15 A, SOD-123	SOD-123
18 19	D4, D5 J1, J2, J5, J6, J8,	2 7	200V	DNP PPTC021LFBN-RC	Diodes Inc. Sullins Connector Solutions	Diode, Ultrafast, 200 V, 1 A, SMA Receptacle, 100mil, 2x1, Tin, TH	SMA Receptacle, 2x1,
20	J10, J11 J3, J4, J7, J9	4		L35	Thomas & Betts	Connector, L Type Copper Single Conductor, TH	100mil, Tin Connector, L Type Copper Single
21	L1	1	1uH	59024	Payton	Inductor, 1 µH, 47 A, TH	Conductor, TH 20x19.5mm
22	Q1, Q4, Q5, Q6, Q7, Q8	6	80V	BSC057N08NS3 G	Infineon Technologies	MOSFET, N-CH, 80 V, 100 A, PG-TDSON-8	PG-TDSON-8
23	Q2, Q3, Q9, Q10	4	80V	BSC072N08NS5ATMA1	Infineon Technologies	MOSFET, N-CH, 80 V, 74 A, PG-TDSON-8	PG-TDSON-8
24	R1, R11, R13, R18, R24, R26	6	2.2	CRCW06032R20JNEA	Vishay-Dale	RES, 2.2, 5%, 0.1 W, 0603	0603
25	R16, R24, R26 R2, R3, R4, R5	4	5.1k	CRCW25125K10JNEH	Vishay-Dale	RES, 5.1 k, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
26	R6, R8, R19, R21, R41, R42, R55, R56, R57, R58	10	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
27	R7, R9, R10, R12, R14, R20, R22, R23, R25, R27, R34, R44, R45, R53, R54	15	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
28	R15	1	10.0	CRCW120610R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.25 W, 1206	1206
29	R16	1	49.9	CRCW120649R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.25 W, 1206	1206
30	R17, R36, R37, R38, R40, R43	6	DNP	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
31 32	R28 R29	1	DNP 13.3k	CRCW06030000Z0EA CRCW060313K3FKEA	Vishay-Dale Vishay-Dale	RES, 0, 5%, 0.1 W, 0603 RES, 13.3 k, 1%, 0.1 W, 0603	0603 0603
33	R30	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
34	R31	1	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, 0603	0603
35	R32	1	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
36	R33	1	18.2k	CRCW060318K2FKEA	Vishay-Dale	RES, 18.2 k, 1%, 0.1 W, 0603	0603
37	R35	1	1.96k	CRCW06031K96FKEA	Vishay-Dale	RES, 1.96 k, 1%, 0.1 W, 0603	0603
38 39	R39 R46	1	19.1k 60.4k	CRCW060319K1FKEA CRCW060360K4FKEA	Vishay-Dale Vishay-Dale	RES, 19.1 k, 1%, 0.1 W, 0603 RES, 60.4 k, 1%, 0.1 W, 0603	0603 0603
40	R47	1	20.0k	CRCW060300K4FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
41	R48	1	1.54k	CRCW06031K54FKEA	Vishay-Dale	RES, 1.54 k, 1%, 0.1 W, 0603	0603
42	R49, R50, R51	3	13.0k	RC0603FR-0713KL	Yageo America	RES, 13.0 k, 1%, 0.1 W, 0603	0603
43	R52	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
44	T1	1		PA1005.100NL	Pulse Engineering	SMT Current Sense Tranformer	P82xx
45 46	T2 TP1, TP3, TP4	1 3		59023 5000	Payton Keystone	Transformer, TH Test Point, Miniature, Red, TH	31x26mm Red Miniature
47	TP2, TP5, TP6	3		5001	Keystone	Test Point, Miniature, Black, TH	Testpoint Black Miniature
48	U1	1		UCC28951QPWRQ1	Texas Instruments	Green Phase-Shifted Full-Bridge Controller with Synchronous Rectification with Current Mode Control, 97 % Duty Cycle, -40 to +125 degC, 24-pin TSSOP (PW), Green (RoHS & no Sb/Br)	Testpoint PW0024A
49	U2, U3	2		UCC27511AQDBVRQ1	Texas Instruments	Single-Channel High-Speed Low-Side Gate Driver (with 4-A Peak Source and 8-A Peak Sink), DBV0006A (SOT-6)	DBV0006A
50	U4, U5	2		UCC27212AQDDARQ1	Texas Instruments	120-V Boot, 4-A Peak, High Frequency High-Side and Low-Side Driver, DDA0008E (SOIC-8)	DDA0008E

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products http://www.ti.com/sc/docs/stdterms.htm), evaluation modules, and samples (http://www.ti.com/sc/docs/stdterms.htm), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated