
Test Report: PMP22806 Class 4 PoE PD Isolated Flyback Converter (12 V, 2.1 A) With Primary Side Regulation Reference Design

TEXAS INSTRUMENTS

Description

This reference design implements a Power over Ethernet (PoE) Power Device (PD) flyback converter with a 12-V, 2.1-A output. A TPS23731 PD, PWM controller provides all the necessary functions to implement the PoE PD control and the PWM control for the flyback converter. The TPS23731 device uses primary side regulation (PSR), eliminating the need for optocoupler feedback.




Top Photo

Features

- Combined PD and PWM controller
- Primary-side regulation (no optocoupler)
- Optional 48-V adapter input
- Frequency dithering for improved EMI

Applications

- IP network camera
- WLAN, Wi-Fi® access point
- Barcode reader



Bottom Photo

1 Test Prerequisites

1.1 Voltage and Current Requirements

Table 1-1. Voltage and Current Requirements

Table 1 Il Voltage and Carton Requirements			
Parameter	Specifications		
Input voltage	42.5 V–57 V		
Output voltage	12 V ±3%		
Output current	2.1 A		
Nominal Switching Frequency	250 kHz		

1.2 Required Equipment

- Type 2 PoE Power Source Equipment (PSE)
- Isolated DC power source, 0 V-57 V, 1-A minimum
- 12-V, 5-A electronic load

1.3 Considerations

- All measurements were taken at approximately 25°C ambient
- All measurements taken with 48-V input and 2.1-A load unless noted



2 Testing and Results

2.1 Efficiency Graphs

Figure 2-1 shows the PMP22806 efficiency curve.




Figure 2-1. PMP22806 Rev. B Efficiency Graph, PoE Diode Bridge

2.2 Efficiency Data

Efficiency data is shown in the following tables.

I _{OUT} (J4)	V.	оцт (J4)	I _{IN} (J1)	V _{IN} (J	J1)	Eff (J1)
0.00		13.594	0.013	48.0	3	0.0%
0.10		12.442	0.042	48.0	3	61.7%
0.20		12.325	0.070	48.0	3	73.3%
0.30		12.264	0.094	48.0	2	81.5%
0.40		12.225	0.125	48.0	2	81.5%
0.50		12.197	0.155	48.0	2	81.9%
0.60		12.174	0.180	48.0	1	84.5%
0.80		12.135	0.233	48.0	0	86.8%
1.00		12.108	0.294	48.0	0	85.8%
1.20		12.081	0.349	48.0	1	86.5%
1.40		12.052	0.403	48.0	1	87.2%
1.60		12.022	0.458	48.0	0	87.5%
1.80		11.992	0.513	48.0	1	87.6%
2.00		11.960	0.568	48.0	0	87.7%
2.10		11.944	0.596	48.0	0	87.7%
I _{OUT} (J4)	V _{OUT} (J4)	I _{IN} (J3)	V _{IN} (J3)	Eff (J3)	V _{IN} (VDD,PGND)	Eff (CONV)
0.00	13.765	0.015	48.03	0.0%	47.69	0.0%
0.10	12.509	0.043	48.03	60.6%	47.64	61.1%
0.20						
	12.378	0.071	48.02	72.6%	47.61	73.2%
0.30	12.378 12.311	0.071	48.02 48.01			
0.30				72.6%	47.61	73.2%
	12.311	0.095	48.01	72.6% 81.0%	47.61 47.59	73.2% 81.7%
0.40	12.311 12.270	0.095	48.01 48.01	72.6% 81.0% 81.8%	47.61 47.59 47.56	73.2% 81.7% 82.6%
0.40 0.50	12.311 12.270 12.239	0.095 0.125 0.155	48.01 48.01 48.00	72.6% 81.0% 81.8% 82.3%	47.61 47.59 47.56 47.54	73.2% 81.7% 82.6% 83.0%
0.40 0.50 0.60	12.311 12.270 12.239 12.215	0.095 0.125 0.155 0.180	48.01 48.01 48.00 48.00	72.6% 81.0% 81.8% 82.3% 84.8%	47.61 47.59 47.56 47.54 47.52	73.2% 81.7% 82.6% 83.0% 85.7%
0.40 0.50 0.60 0.80	12.311 12.270 12.239 12.215 12.179	0.095 0.125 0.155 0.180 0.231	48.01 48.01 48.00 48.00 48.03	72.6% 81.0% 81.8% 82.3% 84.8% 87.8%	47.61 47.59 47.56 47.54 47.52 47.52	73.2% 81.7% 82.6% 83.0% 85.7% 88.8%
0.40 0.50 0.60 0.80 1.00	12.311 12.270 12.239 12.215 12.179 12.152	0.095 0.125 0.155 0.180 0.231 0.292	48.01 48.01 48.00 48.00 48.03 48.03 48.01	72.6% 81.0% 81.8% 82.3% 84.8% 87.8% 86.7%	47.61 47.59 47.56 47.54 47.52 47.52 47.48	73.2% 81.7% 82.6% 83.0% 85.7% 88.8% 87.7%
0.40 0.50 0.60 0.80 1.00 1.20	12.311 12.270 12.239 12.215 12.179 12.152 12.126	0.095 0.125 0.155 0.180 0.231 0.292 0.345	48.01 48.01 48.00 48.00 48.03 48.01 48.01	72.6% 81.0% 81.8% 82.3% 84.8% 87.8% 86.7% 87.9%	47.61 47.59 47.56 47.54 47.52 47.52 47.48 47.45	73.2% 81.7% 82.6% 83.0% 85.7% 88.8% 87.7% 88.9%
0.40 0.50 0.60 0.80 1.00 1.20 1.40	12.311 12.270 12.239 12.215 12.179 12.152 12.126 12.098	0.095 0.125 0.155 0.180 0.231 0.292 0.345 0.399	48.01 48.01 48.00 48.00 48.03 48.03 48.01 48.01 48.01	72.6% 81.0% 81.8% 82.3% 84.8% 87.8% 86.7% 87.9% 88.4%	47.61 47.59 47.56 47.54 47.52 47.52 47.52 47.48 47.45 47.42	73.2% 81.7% 82.6% 83.0% 85.7% 88.8% 87.7% 88.9% 89.5%
0.40 0.50 0.60 0.80 1.00 1.20 1.40 1.60	12.311 12.270 12.239 12.215 12.179 12.152 12.126 12.098 12.069	0.095 0.125 0.155 0.180 0.231 0.292 0.345 0.399 0.453	48.01 48.01 48.00 48.00 48.03 48.01 48.01 48.01 48.01 48.02	72.6% 81.0% 81.8% 82.3% 84.8% 87.8% 86.7% 87.9% 88.4% 88.8%	47.61 47.59 47.56 47.54 47.52 47.52 47.48 47.48 47.45 47.42 47.42	73.2% 81.7% 82.6% 83.0% 85.7% 88.8% 87.7% 88.9% 89.5% 89.9%

2.3 Load Regulation

Figure 2-2 shows the PMP22806 rev B load regulation curve.





Figure 2-2. Load Regulation

2.4 Thermal Images

Figure 2-3 and Figure 2-4 show the thermal images.

Measuremen	its	٦	11/13/2021 2:13:44
Sp1	58.7 °C		Contraction of the
Sp2	53.1 °C		10 M
Sp3	41.0 °C		
Sp4	39.5 °C		50
Sp5	37.8 °C		
Sp6	36.7 °C		
Parameters			
	0.05		






Figure 2-3. Top Thermal Image

Measuremer	nts	11/13/2021 2:20	:35 PM	°(
Sp1	65.8 °C			50
Sp2	57.1 °C		A 💽	1
Parameters				
Emissivity	0.95		A CONTRACTOR OF	~ ~
Refl. temp.	20 °C		A second	
				N.
				23
		PMP22806B	FLIR E75	785033

Figure 2-4. Bottom Thermal Image



2.5 Bode Plot

Figure 2-5 shows the bode plot waveform.




Figure 2-5. Bandwidth = 9.3 kHz, Phase Margin = 59 degrees, Gain Margin = 18.1 dB



3 Waveforms

3.1 Switching

Switching behavior is shown in the following figures.




Figure 3-1. Voltage Drain to PGND, Q2, 57-V Input, 2.1-A Load, 20 V/div, 1 µs/div, Measured 115.3 Vpeak




Figure 3-2. Voltage Anode to GND, D100, 57-V Input, 2.1-A Load, 10 V/div, 1 µs/div, Measured 42.3 Vpeak



3.2 Voltage Ripple

The following images show the input and output ripple waveforms.




Figure 3-3. Output Ripple (J4), 50 mV/div, 2 µs/div, Measured 83.0 mVpp





3.3 Load Transients

Load transient response is shown in the following figures.






Figure 3-5. Output Load Step Response, 1.05-A to 2.10-A Load Step, 200 mV/div, 1 A/div, 1 ms/div, Slew Rate = 250 mA/µs, Measured +220 mV | –247 mV







3.4 Short-Circuit Protection

Short at output connector J4. Input power during short circuit is 48.02 V, 59 mA, and 2.83 W.




Figure 3-7. Output Current, 2 A/div, 20 ms/div, Measured 12.13 Apeak




Figure 3-8. Output Voltage Recovery From Short Circuit, 2 V/div, 2 A/div, 5 ms/div

Figure 3-9 and Figure 3-10 show thermal plots during short circuit.

Measuremen	ts
Sp1	30.6 °C
Sp2	30.0 °C
Sp3	40.7 °C
Sp4	33.8 °C
Sp5	32.8 °C
Sp6	34.3 °C
Parameters	
Emissivity	0.95
Refl. temp.	20 °C




Figure 3-9. Thermal Plot During Short Circuit, Top






Figure 3-10. Thermal Plot During Short Circuit, Bottom (Diode D100)




3.5 Start-Up Sequence

The following images show the start-up behavior waveforms.









IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated