Application Brief **Optimizing ADAS Domain Controllers Using Logic and Translation**



Albert Xu

Interface Logic

Functional Block Diagram

For the purpose of this application brief, a simplified ADAS domain controller block diagram shows the logic and translation use cases. See Simplified Block Diagram for ADAS Domain Controller as an example. Each red block has an associated use-case document. Table 1 and Table 2 list links for more information. To see a complete block diagram, see the interactive online end equipment reference diagram for ADAS Domain Controller.




Figure 1. Simplified Block Diagram for ADAS Domain Controller

1



Logic and Translation Use Cases

Each use case is linked to a separate short document that provides additional details including a block diagram, design tips, and part recommendations. The nearest block and use-case identifiers are listed to match up exactly to the use cases shown in Figure 1.

Nearest Block	Use-Case Identifier	Use Case			
Battery Input Protection	Power Good Combination	Combine Power Good Signals			
Sensors Data Processing	Increase I/O	Increase Inputs on a uC			
Fusion and Object Data Processing	Timed Reset	Reset a System for a Short Time			
Diagnostics and Monitoring	Combine Error Signals	Combine Error Signals			


Table 1 Logic Use Cases

Table 2. Translation Use Cases

Nearest Block	Use-Case Identifier	Use Case
Raw Data Sensor Interface	I2C Translation	Translate Voltages for I2C
Fusion and Object Data Memory	GPIO Translation	Translate Voltages for GPIO Pins

Reset a System for a Short Time

System controllers can use GPIO pins to reset other components if a fault is detected; however, system controllers generally cannot reset themselves or their entire system. By using a monostable multivibrator, the system controller can reset the entire system.



- Either falling-edge or rising-edge trigger configurations can be used for this application. See the data sheet of ٠ the selected multivibrator for details.
- A pullup or pulldown resistor is required to return the input signal to a valid state once the system controller turns off. The recommended value for this resistor is 10 k Ω .
- Retriggerable or non-retriggerable monostable multivibrators can be used for this operation.
- [FAQ] [H] Monostable Multivibrators Top Questions Answered ٠
- [FAQ] How does a slow or floating input affect a CMOS device?
- [FAQ] Where do I find maximum power dissipation for a device? •
- Ask a question on our *E2E[™] forum*.

2



Table 3. Recommended Parts					
Part Number	Automotive Qualified	V _{CC} Range	Туре	Features	
SN74LVC1G125- Q1	V	1.65 V – 5.5 V	Single buffer with 3-state outputs	Standard CMOS inputs Inverting OE signal; see '1G126 for non-inverting OE signal.	
SN74LVC1G07-Q1	V	1.65 V – 5.5 V	Single buffer with open- drain outputs	Schmitt-trigger inputs Inputs are over-voltage tolerant; signals can exceed V _{CC} .	
SN74LVC1G08-Q1	1	1.65 V – 5.5 V	Single 2-input AND gate	Schmitt-trigger inputs Supports partial-power-down with loff circuitry, disabling outputs.	

For more devices with Schmitt trigger input architecture, see the *online parametric tool* which can be sorted by the desired voltage, output current, and other features.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated