

## Bill of Materials

TUSB542EVM INT030

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Digikey Part Number	PCB Footprint	Note
1	14	C1,C2,C3,C4,C5,C6,C8,C9,C10,C19,C 20,C23,C24,C25	0.1uF	Capacitor	TDK	C0603X7S1A104M030BC	445-9018-2-ND	201	
2	1	C7	0.01uF	Capacitor	TDK	C0603X5R1A103K030BA	445-1793-1-ND	201	
3	6	C11,C14,C17,C18,C26,C27	1uF	Capacitor	TDK	C1005X5R1A105K050BB	445-4114-1-ND	402	
4	4	C12,C13,C15,C16	10uF	Capacitor	TDK	C1608X5R0J106M080AB	445-4112-1-ND	603	
5	1	C21	47uF	Capacitor	TDK	C3216X6S0J476M160AB	445-6011-1-ND	1206	
6	1	C22	47nF	Capacitor	TDK	C1005X7R1C473K050BC	445-1264-1-ND	402	
7	1	D1		LED	LITE-ON	LTST-C170KGKT	160-1414-1-ND	805	
8	1	D2		Schottky	Rohm Semiconductor	RB161M-20TR	RB161M-20TR-ND	SOD_123FL	
9	7	J1,J2,J3,J4,J5,J6,J7	HDR2x1 M .1	2-Pin Header	Sullins Connector Solutions	S1012E-02	S1012E-02-ND		
10	1	P1		USB3 Type B Receptacle	Wurth Electronics	692221030100	732-3158-ND		
11	1	P2		Type C USB Connector	JAE	DX07S024JJ3R1300	670-2846-2-ND		Alternate: 670-2794-1-ND p/n: DX07S024JJ2R1300
12	1	Q1		PMOS FET	Texas Instruments	CSD25484F4T	296-42131-1-ND	YJJ-DFN_3	
13	12	R1,R2,R3,R4,R5,R6,R7,R8, R9,R10,R11,R12	10K	Resistor	Panasonic Electronic Components	ERJ-2GEJ103X	P10KJCT-ND	402	
14	1		909K	Resistor	Panasonic Electronic Components	ERJ-2RKF9093X	P909KLDKR-ND	402	
15	1	R14	499	Resistor	Panasonic Electronic Components	ERJ-2RKF4990X	P499LCT-ND	402	
16	1	R15	4.7K	Resistor	Panasonic Electronic Components	ERJ-2GEJ472X	P4.7KJCT-ND	402	
17	4	R16,R17,R18,R19	200k	Resistor	Panasonic Electronic Components	ERJ-2RKF2003X	P200KLCT-ND	402	
18	0	R20	10K (No Pop)	Resistor	Panasonic Electronic Components	ERJ-2GEJ103X	P10KJCT-ND	402	NoPop
19	1	R21	29.4K	Resistor	Panasonic Electronic Components	ERJ-2RKF2942X	P29.4KLCT-ND	402	
20	4	R22,R23,R24,R25	0	Resistor	Panasonic Electronic Components	ERJ-6GEY0R00V	PO.OACT-ND	805	
21	1	R26	1.6k	Resistor	Panasonic Electronic Components	ERJ-1GEF1601C	P1.60KABCT-ND	201	
22	5	SW1,SW2,SW3,SW4,SW5		Switch	Copal Electronics	CJS-1201TA	<u>563-1023-1-ND</u>	CJS-1200B	
23	1	U1		USB3 Switch / Redriver	Texas Instruments	TUSB542RWQ	N/A	RWQ	
24	1	U2		CC Controller	Texas Instruments	TUSB321RWBR	296-42400-1-ND	RWB	
25	1	U3		1.8V LDO	Texas Instruments	LP5907MFX-1.8NOPB	296-41463-1-ND	SOT-23-5	
26	1	U4		Power Switch	Texas Instruments	TPS25910RSA	296-39385-1-ND	16-VQFN	
27	1	U5		USB 2.0 Redriver	Texas Instruments	TUSB211RWB	296-42399-6-ND	RWB	
28	1	U6		3.3V LDO	Texas Instruments	LP5907SNX-3.3/NOPB	296-39066-1-ND	X2SON	
29	1	PCB			ANY	INT030			PCB Board

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated