Item	Qty	Reference	Description	Size	Value	Part Number	MFR
1	1	D2	Switching Diode, 0.2A,/200V	SOT23	0.2A, 200V	BAS20LT1G	ON Semiconductor
2	1	C7	CAP CER 3.3UF 10V 10% X5R 0603	0603	3.3uF/10V	GRM188R61A335KE15D	muRata
3	1	C5	Capacitor, Ceramic	0603	NA		muRata
4	1	C16	Capacitor, Ceramic	0603	NA		muRata
5	3	C8 C13 C15	Capacitor, Ceramic	1210	NA		muRata
			Metallized Polypropylene File, CBB21,				
6	1	C2	0.1uF/450V,		0.1uF		Epcos
			Capacitor, Ceramic, Low Inductance, vvV,				
7	1	C3	[temp], [tol]	1206	2.2nF/630V	GRM31BR72J222KW012	muRata
8	1	D1	Bridge Rectifier, 600V, 1A	DFS	1A/600V	DF06S	DIODES/Vishay
9	1	D5	DIODE ULTRA FAST 3A 300V SMC	SMC	3A,300V	ES3F-E3/57T	Vishay
10	1	D3	Standard Rectifier, 1A, 1000V	SMA	1A, 1000V	M7	ON/Diodes
11	1	F1	FUSE 300V TL TE5 LL AMMO 1A		1A/300Vac (T)	3691100000	Littlefuse
12	1	L4	Common choke,T6-3-2,0.15mH	T6-3-2	150uH	T6-3-2	BOCHANG
13	1	L3	Common choke,EI-11.6,30mH	EI-11.6	30mH	EI-11.6	BOCHANG
14	1	L2	0.6mm Jumper			STD	STD
15	1	L1	I-inductor, 2mH/0.5A, size: 8mm*10mm		2mH	DR8-10	BOCHANG
			Capacitor, film, 0.047 uF, +/-20% Tol, -				
16	1	C9	40/+125C, Safety: X2, 275VAC		47nF/X2	R46KF2470DQH1M	KEMET
17	0	C9	FILM CAP 47NF 10% 305V MKP X2		47nF/X2	B32921C3473K	Epcos
			Capacitor, film, 0.068 uF, +/-20% Tol, -				
18	1	C1	40/+125C, Safety: X2, 275VAC		68nF/X2	R46KF2680DQH1M	KEMET
19	0	C1	CAP FILM 68NF 10% 305V MKP X2		68nF/X2	B32921C3683K	Epcos
20	1	C14	CAP CER 2200PF 250V 20% RADIAL		222/Y1	DE1E3KX222MA4BL01	Murata
21	1	T1	ECR28 Transformer, 460uH	ECR28	460uH		BOCHANG
22	2	R5 R24	Resistor, Chip, 1/8W, 1%	0805	10R	STD	Yageo
23	1	R9	Resistor, Chip, 1/10W, 1%	0603	18K	STD	Yageo
24	1	R2	Resistor, Chip, 1/8W, 1%	0805	240K	STD	Yageo
25	1	R13	Resistor, Chip, 1/10W, 1%	0603	51K	STD	Yageo
26	1	R10	Resistor, Chip, 1/10W, 1%	0603	6.8K	STD	Yageo

		T	T	I	1	T.	
27	1	R8	Resistor, Chip, 1/8W, 1%	0805	91K	STD	Yageo
28	2	R17 R20	Resistor, Chip, 1/10W, 1%	0603	NA		Yageo
29	1	R25	Resistor, Chip, 1/8W, 1%	0805	NA		Yageo
30	1	R14	Resistor, 1206, 1/4W, 1%	1206	0.68R	STD	Yageo
31	1	R15	Resistor, 1206, 1/4W, 1%	1206	8.2R	STD	Yageo
32	1	R1	Resistor, Chip, 1/8W, 1%	0805	10K	STD	Yageo
33	2	R6 R7	Resistor, Chip, 1/4W, 1%	1206	100K	STD	Yageo
34	1	R3	Resistor, Chip, 1/4W, 5%	1206	68R	STD	Yageo
35	2	R4 R21	Resistor, Chip, 1/4W, 1%	1206	82K	STD	Yageo
36	2	R18-19	Resistor, Chip, 1/4W, 1%	1206	NA		Yageo
37	2	R22-23	Resistor, Chip, 1/4W, 5%	1206	NA		Yageo
				10mm(die.)x20			
38	2	C11-12	CAP ALUM 330UF 63V 20% RADIAL	mm(hight)	330uF/63V	ECA1JHG331	Panasonic
				6.3mm(die.)x7			
39	1	C4	CAP ALUM 33UF 35V 20% RADIAL	mm(hight)	33uF/35V	ECE-A1VKA330	Panasonic
40	1	D4	Switching diode, 0.2A, 100V	SOD323	0.2A,200V	MMDL914T1G	ON Semiconductor
41	1	D6	DIODE SWITCH 75V 200MW SOD323	SOD323	0.2A,200V	1N4148WS	DIODES/Vishay
42	1	D7		SOD323	NA		DIODES/Vishay
43	4	L LED+ LED- N	2.54mm Pin Header			61300111121	Wurth
			Off-Line Primary Side Sensing Controller with				
44	1	U1	PFC in 8-SOIC	S0-8	TPS92314D	TPS92314D	ΤΙ
45	1	Q4		SOT23	NA		
46	1	Q1	MOSFET N-CH 600V 2A DPAK	TO-252	2A 600V	STD2HNK60Z	ST
			•				-

Note: Devices with fields marked as NA can be chosen at the option of the designer.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

## Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive Communications and Telecom **Amplifiers** amplifier.ti.com www.ti.com/communications **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps

DSP **Energy and Lighting** dsp.ti.com www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical logic.ti.com Logic Security www.ti.com/security

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers <u>microcontroller.ti.com</u> Video and Imaging <u>www.ti.com/video</u>

RFID <u>www.ti-rfid.com</u>

OMAP Applications Processors <a href="www.ti.com/omap">www.ti.com/omap</a> TI E2E Community <a href="e2e.ti.com">e2e.ti.com</a>

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>