

TPS65266EVM-686 Evaluation Module

This document presents the information required to operate the TPS65266 PMIC as well as the support documentation including schematic, layout, hardware setup, and bill of materials (BOM).

Contents

	Contents	
1	Introduction	2
2	TPS65266 EVM Schematic	3
3	Board Layout	4
4	Bench Test Setup Conditions	7
5	Power-Up Procedure	
6	Bill of Materials	9
	List of Figures	
1	TPS65266EVM-686 Schematic	3
2	Component Placement (Top Layer)	4
3	Board Layout (Top Layer)	4
4	Board Layout (Second Layer)	
5	Board Layout (Third Layer)	5
6	Board Layout (Bottom Layer)	6
7	Headers Description and Jumper Placement	7
	List of Tables	
1	Summary of Performance	2
2	Input/Output Connection	8
3	Jumpers	8
4	Bill of Materials	9



Introduction www.ti.com

1 Introduction

The TPS65266 PMIC is a triple 3A/2A/2A output current, synchronous step-down (buck) converter with an operational range of 2.7 to 6.5 V. The feedback voltage reference for each buck is 0.6 V. Each buck is independent with dedicated enable, soft-start, and loop compensation. The TPS65266 operates in force continuous current mode (FCC) at light load.

As there are many possible options to set the converters, Table 1 presents the performance specification summary for the EVM.

Table 1. Summary of Performance

Test Conditions	Performance
$V_{IN} = 2.7 \text{ to } 6.5 \text{ V}$	Buck1, 1.0 V, up to 3 A
$f_{sw} = 1 \text{ MHz}$	Buck2, 1.5 V, up to 2 A
(25°C ambient)	Buck3, 1.8 V, up to 2 A

The evaluation module is designed to provide access to the features of the TPS65266 device. Some modifications can be made to this module to test performance at different input and output voltages, current, and switching frequency. Please contact TI Field Applications Group for advice on these matters.



www.ti.com TPS65266 EVM Schematic

2 TPS65266 EVM Schematic

Figure 1 illustrates the TPS65266 EVM schematic.




Figure 1. TPS65266EVM-686 Schematic



Board Layout www.ti.com

3 Board Layout

Figure 2 through Figure 6 illustrate the printed-circuit board (PCB) layouts.




Figure 2. Component Placement (Top Layer)




Figure 3. Board Layout (Top Layer)



www.ti.com Board Layout




Figure 4. Board Layout (Second Layer)




Figure 5. Board Layout (Third Layer)



Board Layout www.ti.com




Figure 6. Board Layout (Bottom Layer)



4 Bench Test Setup Conditions

4.1 Headers Description and Jumper Placement

Figure 7 illustrates the header descriptions and jumper placement on the EVM.




Figure 7. Headers Description and Jumper Placement

Test points:

- (A) LX of VOUT1
- (B) LX of VOUT2
- (C) LX of VOUT3

VOUT1, VOUT2, VOUT3, VIN, PGOOD, CLK_SYN



Power-Up Procedure www.ti.com

Table 2 lists the I/O connections and Table 3 lists the jumpers for the TPS65266EVM-686.

Table 2. Input/Output Connection

No.	Function	Description
J1	Buck1 Connector	Output of Buck1
J2	Buck2 Connector	Output of Buck2
J3	Buck3 Connector	Output of Buck3
J4	VIN Connector	Apply power supply to this connector

Table 3. Jumpers

No.	Function	Placement
J5	Buck1 enable (EN1)	Connect EN1 to GND to disable V_{OUT1} , connect EN1 to V_{IN} through a 100-k Ω resistor to enable V_{OUT1} ; Leave open to enable V_{OUT1}
J6	Buck2 enable (EN2)	Connect EN2 to GND to disable V_{OUT2} , connect EN2 to V_{IN} through a 100-k Ω resistor to enable V_{OUT2} ; Leave open to enable V_{OUT2}
J7	Buck3 enable (EN3)	Connect EN3 to GND to disable V_{OUT3} , connect EN3 to V_{IN} through a 100-k Ω resistor to enable V_{OUT3} ; Leave open to enable V_{OUT3}

5 Power-Up Procedure

This section provides the steps for powering up the EVM.

POWER-UP with the dedicated enable pin:

- 1. Apply 2.7 V 6.5 V to J4
- 2. Toggle J5 , J6, or J7 to enable $V_{\text{OUT1}},\,V_{\text{OUT2}},\,\text{AND }V_{\text{OUT3}},\,\text{respectively}$
- 3. Apply loads to the output connectors



www.ti.com Bill of Materials

6 Bill of Materials

Table 4 lists the BOM for this EVM.

Table 4. Bill of Materials

Designator	Quantity	Value	Description	Package Reference	Part Number	Manufacturer
PCB1	1		Printed Circuit Board		PWR686	Any
C1, C10, C17	3	0.047uF	CAP, CERM, 0.047uF, 50V, +/-10%, X7R, 0603	0603	C1608X7R1H473K	TDK
C2, C3, C7, C8, C9, C12, C13, C18, C19	9	22uF	CAP, CERM, 22uF, 16V, +/-20%, X5R, 1206	1206	1206YD226MAT2A	AVX
C6, C16, C20	3	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0603	0603	C0603C102K5RACTU	Kemet
C11	1	2.2uF	CAP, CERM, 2.2 uF, 10 V, +/- 10%, X5R, 0603	0603	C0603C225K8PACTU	Kemet
C22, C23, C24	3	0.01uF	CAP, CERM, 0.01uF, 50V, +/-5%, X7R, 0603	0603	C0603C103J5RACTU	Kemet
C26	1	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 5%, X7R, 0603	0603	C0603C102J5RACTU	Kemet
C27	1	4700pF	CAP, CERM, 4700 pF, 50 V, +/- 5%, X7R, 0603	0603	C0603C472J5RACTU	Kemet
C28	1	0.01uF	CAP, CERM, 0.01 uF, 50 V, +/- 5%, X7R, 0603	0603	C0603C103J5RACTU	Kemet
H1, H2, H3, H4	4		Bumpon, Hemisphere, 0.44 X 0.20, Clear	Transparent Bumpon	SJ-5303 (CLEAR)	3M
J1, J2, J3, J4	4		Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH	7.0x8.2x6.5mm	ED555/2DS	On-Shore Technology
J5, J6, J7	3		Header, 100mil, 3x1, Tin plated, TH	Header, 3 PIN, 100mil, Tin	PEC03SAAN	Sullins Connector Solutions
L1, L2, L3	3	2.2uH	Inductor, Shielded Drum Core, Superflux, 2.2 uH, 9 A, 0.0115 ohm, SMD	WE-HC4	744311220	Wurth Elektronik eiSos
LBL1	1		Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W	THT-14-423-10	Brady
R1, R2, R4, R7, R8, R13, R14	7	0	RES, 0 ohm, 5%, 0.1W, 0603	0603	CRCW06030000Z0EA	Vishay-Dale
R3	1	9.1k	RES, 9.1 k, 5%, 0.1 W, 0603	0603	CRCW06039K10JNEA	Vishay-Dale
R5, R12	2	15.0k	RES, 15.0 k, 1%, 0.1 W, 0603	0603	CRCW060315K0FKEA	Vishay-Dale
R6, R11, R16	3	10.0k	RES, 10.0k ohm, 1%, 0.1W, 0603	0603	CRCW060310K0FKEA	Vishay-Dale
R9, R19, R20, R21	4	100k	RES, 100k ohm, 1%, 0.1W, 0603	0603	CRCW0603100KFKEA	Vishay-Dale
R10, R15	2	20k	RES, 20 k, 5%, 0.1 W, 0603	0603	CRCW060320K0JNEA	Vishay-Dale
R17	1	20.0k	RES, 20.0k ohm, 1%, 0.1W, 0603	0603	CRCW060320K0FKEA	Vishay-Dale
R18	1	51.1k	RES, 51.1 k, 1%, 0.1 W, 0603	0603	CRCW060351K1FKEA	Vishay-Dale
TP1, TP2, TP6, TP7, TP10, TP13	6	White	Test Point, Miniature, White, TH	White Miniature Testpoint	5002	Keystone
TP3, TP5, TP8, TP11, TP14	5	Black	Test Point, Miniature, Black, TH	Black Miniature Testpoint	5001	Keystone
U1	1		2.7V to 6.5V Input Voltage, 3A/2A/2A Output Current Triple Synchronous Step-down Converters, RHB0032E	RHB0032E	TPS65266RHB	Texas Instruments
C4, C14, C15, C21, C25	0	22pF	CAP, CERM, 22pF, 50V, +/-5%, C0G/NP0, 0603	0603	06035A220JAT2A	AVX
C5	0	82pF	CAP, CERM, 82pF, 50V, +/-5%, C0G/NP0, 0603	0603	06035A820JAT2A	AVX
R22, R23, R24	0	DNI	RES, 100k ohm, 1%, 0.1W, 0603	0603	CRCW0603100KFKEA	Vishay-Dale
TP4, TP9, TP12	0	DNI	Test Point, Miniature, White, TH	White Miniature Testpoint	5002	Keystone



Revision History www.ti.com

Revision History

Changes from Original (November 2014) to A Revision		
•	Changed pulse skipping mode (PSM) to force continuous current mode (FCC)	2
N	OTE: Page numbers for previous revisions may differ from page numbers in the current version.	

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products Applications

Audio www.ti.com/audio Automotive and Transportation www.ti.com/automotive amplifier.ti.com Communications and Telecom www.ti.com/communications Amplifiers **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** www.dlp.com Consumer Electronics www.ti.com/consumer-apps DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic Security www.ti.com/security logic.ti.com

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID www.ti-rfid.com

OMAP Applications Processors <u>www.ti.com/omap</u> TI E2E Community <u>e2e.ti.com</u>

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>