

**ABSTRACT**

This user's guide describes the characteristics, operation, and use of TI's evaluation module (EVM) for the TPS628691, TPS628692, TPS628681, TPS628682 devices. The TPS62869EVM-118 (BSR118) facilitates the evaluation of the TPS62869 family of 6-A, step-down converter with DCS-Control™ in a small 1.5-mm by 2.5-mm QFN package solution. The EVM creates output voltages between 0.4V and 1.675V with 1% accuracy output voltages from higher input voltages between 2.4 V and 5.5 V, to a regulated 0.9V output voltage. The TPS62869 family is a highly efficient and tiny solution for point-of-load (POL) converters for space-constrained applications, such as artificial intelligence chips, camera modules, solid state drives (SSDs), and optical modules.

Table of Contents

1 Introduction	2
1.1 Performance Specification	2
1.2 Modifications	2
2 Setup	2
2.1 Input/Output Connector Descriptions	2
2.2 Hardware Setup	2
3 TPS62869EVM-118 Test Results	3
4 Board Layout	3
5 Schematic and List of Materials	6
5.1 Schematic	6
5.2 List of Materials	6
6 Software User Interface	7
6.1 Software Setup	7
6.2 Interface Hardware Setup	7
6.3 User Interface Operation	7
7 Revision History	9

List of Figures

Figure 4-1. Top Assembly	3
Figure 4-2. Top Layer	3
Figure 4-3. Signal Layer 1	4
Figure 4-4. Signal Layer 2	4
Figure 4-5. Signal Layer 3	4
Figure 4-6. Signal Layer 4	5
Figure 4-7. Bottom Layer	5
Figure 5-1. TPS62869EVM-118 Schematic	6
Figure 6-1. Quick Connection Overview	7
Figure 6-2. GUI Home Screen	8
Figure 6-3. GUI Settings Screen	9

List of Tables

Table 1-1. Performance Specification Summary	2
Table 5-1. TPS628691ARQY List of Materials	6

1 Introduction

The TPS62869 is a family of synchronous, step-down converter, coming in a 1.5-x2.5-x1.0-mm QFN package.

1.1 Performance Specification

[Table 1-1](#) provides a summary of the TPS62869EVM-118 performance specifications.

Table 1-1. Performance Specification Summary

SPECIFICATION	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Input voltage		2.4	5	5.5	V
Output voltage setpoint			0.9		V
Output current		0		6000	mA

1.2 Modifications

The printed-circuit board (PCB) for this EVM is designed to accommodate the different adjustable output voltage versions of this integrated circuit (IC). On the EVM, additional input and output capacitors can be added.

2 Setup

This section describes how to properly use the TPS62869EVM-118.

2.1 Input/Output Connector Descriptions

J1, Pin 1 and 2 – VIN	Positive input connection from the input supply for the EVM
J1, Pin 3 and 4 – S+/S-	Input voltage sense connections. Measure the input voltage at this point.
J1, Pin 5 and 6 – GND	Input return connection from the input supply for the EVM
J2, Pin 1 and 2 – VOUT	Output voltage connection
J2, Pin 3 and 4 – S+/S-	Output voltage sense connections. Measure the output voltage at this point.
J2, Pin 5 and 6 – GND	Output return connection
J3, Pin 5 – VBUS	The VBUS pin of this header is used to bias the SCL and SDA nodes of I ² C interface via a resistor.
J3, Pin 6 – GND	The GND pin of this header is used to connect the grounds of the IC and the I ² C interface.
J3, Pin 9 – SCL	The pin of this header should be connected to the SCL of the I ² C interface.
J3, Pin 10 – SDA	The pin of this header should be connected to the SDA of the I ² C interface.
JP1 – VID/PG	VID/ PG pin jumper. Place the jumper across VID/ PG and LOW pins before start-up. This sets the output voltage and device address. After startup, VOUT reflects the value set on V _{OUT} Register 1 if the jumper is placed across VID/ PG and LOW pins. VOUT follows the value set on V _{OUT} Register 2 if the jumper is placed across VID/ PG and HIGH pins.
JP2 – EN	EN pin input jumper. Place the jumper across ON and EN to turn on the IC. Place the jumper across OFF and EN to turn off the IC.

2.2 Hardware Setup

To operate the EVM, set jumpers JP1 and JP2 to the desired position per [Section 2.1](#). Connect the input supply to J1 and connect the load to J2.

4 Board Layout

For evaluation only; not FCC approved for resale.

JP2 JP1 J4

ON EN OFF HIGH LOW GND

R2 [] R1

VID/PG

BSR118
Rev. A

TPS62869EVM-118

GND

J1 S- S+ VIN 2.4V-5.5V

J2 S- S+ VOUT

J3 R4 [] R3

CE

3




Figure 4-3. Signal Layer 1




Figure 4-4. Signal Layer 2




Figure 4-5. Signal Layer 3




Figure 4-6. Signal Layer 4




Figure 4-7. Bottom Layer

5 Schematic and List of Materials

This section provides the TPS62869EVM-118 schematic and list of materials.

5.1 Schematic

Figure 5-1 illustrates the EVM schematic.




Figure 5-1. TPS62869EVM-118 Schematic

5.2 List of Materials

Table 5-1 lists a list of materials for this EVM.

Table 5-1. TPS628691ARQY List of Materials

DESIGNATOR	QTY	DESCRIPTION	PART NUMBER	MANUFACTURER
C1	1	Capacitor, Ceramic, 470 pF, 50 V, ±5%, C0G/NP0, 0603	GRM1885C1H471JA01D	Murata
C5	1	Capacitor, Ceramic, 10 µF, 10 V, ±10%, X7R, 0603	GRM188Z71A106KA73D	Murata
C2, C3	2	Capacitor, ceramic, 22 µF, 6.3 V, ±20%, X7R, 0805	GRM21BZ70J226ME44L	Murata
C9	1	Capacitor, Ceramic, 47 µF, 6.3 V, ±20%, X5R, 0603	GRM188R60J476ME15D	Murata
C8	1	Capacitor, tantalum, 68 µF, 20 V, ±10%, 7343	T495D686K020ATE150	Kemet
L1	1	Inductor, 220 nH, 16.8 A, 5.8 mΩ, SMD, 4040	XAL4020-221MEB	Coilcraft
R1	1	Resistor, 86.6 kΩ, 1%, 0.1 W, 0603	Std	Std
R2	1	Resistor, 100 kΩ, 1%, 0.1 W, 0603	Std	Std
R3, R4	2	Resistor, 2.0 kΩ, 1%, 0.1 W, 0603	Std	Std
U1	1	6-A Step-Down Converter with I ² C Interface and Wide Output Voltage Range, QFN - 9 Pins	TPS628691ARQY	Texas Instruments

6 Software User Interface

6.1 Software Setup

A graphical user interface (GUI) is available from the [TPS62869 tools and software page](#), which allows simple and convenient programming of the device through the [TI USB2ANY](#) interface board. Alternatively, you can use any I²C-standardized programming tool or I²C host to configure the device. Mind the I²C pins specification, such as timing parameters and proper pullup resistors, specified in the [TPS62869 2.4-V to 5.5-V Input, 6-A Synchronous Step-Down Converter Data Sheet](#)

6.2 Interface Hardware Setup

Connect the USB2ANY adapter to your PC using the supplied USB cable. Connect the EVM connector J3 to the USB2ANY adapter using the supplied 10-pin ribbon cable. The connectors on the ribbon cable are keyed to prevent incorrect installation. [Figure 6-1](#) shows a quick adapter connection overview.

USB Interface Adaptor Quick Connection Diagram




Figure 6-1. Quick Connection Overview

6.3 User Interface Operation

Upon start-up, the GUI automatically connects to the EVM. If not, click on the Connect button in the upper right corner of the GUI window. Ensure the I²C Slave Address is correct. The following sections give a short overview of the two main GUI screens.

6.3.1 Home Screen

The Home screen gives a short overview of the TPS62869 devices. To start evaluating the device, click on the Start button or on the Settings icons on the left side of the GUI window.




Figure 6-2. GUI Home Screen

6.3.2 Settings Screen

The Settings screen provides control over the output voltage and operating modes of the TPS62869. The Register Map at the bottom shows a register-wise view of all parameters. Here, single registers can be read or written to the device (if applicable). Refer to the register map in the [TPS62869 2.4-V to 5.5-V Input, 6-A Synchronous Step-Down Converter Data Sheet](#) for a detailed description of the TPS62869 registers.




Figure 6-3. GUI Settings Screen

7 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision A (March 2021) to Revision B (November 2021)	Page
• Updated TPS628692 to TPS628682	1
• Updated title from Setup to Hardware Setup	2
Changes from Revision * (May 2021) to Revision A (March 2021)	Page
• Updated TPS62869EVM-118 Schematic.....	6

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025