

LM27761EVM User's Guide

1 Introduction

The Texas Instruments LM27761EVM evaluation module (EVM) helps designers evaluate the operation and performance of the LM27761 switched capacitor inverter.

The EVM contains one LM27761 regulated switched capacitor inverter (See [Table 1](#)). For more details and electrical characteristics of this device, see the LM27761 device data sheet ([SNVSA85](#)).

Table 1. Device and Package Configurations

FLASH LED DRIVER	IC	PACKAGE
U1	LM27761	WSON (8 pins)

2 Setup

This section describes the jumpers and connectors on the EVM as well as how to properly connect, set up, and use the LM27761EVM.

2.1 Input/Output Connector Description

VIN / GND: These are the power input pins for the driver. The pins provides a power (VIN) and ground (GND) connection to allow the user to attach the EVM to a cable harness.

EN: This is the jumper used to enable the boost converter (EN pin). The driver will be enabled when the EN pin is high (+) and disabled when it is low (–).

VOUT: This is the output pin for the LM27761EVM. Currents up to 250 mA can be drawn from this pin when the input voltage is higher than 2.7 V and lower than 5.5 V.




Figure 1. Enable Jumper Settings

2.2 Input Voltage

The input voltage range for the LM27661 device is 2.7 V to 5.5 V.

2.3 Jumper Configuration

For proper operation of the LM27761EVM, the jumpers must be properly configured. The recommended setting, using shorting blocks is:

EN to +

In this configuration, the device powers up when an input voltage is applied. Once running, current can be pulled from the VOUT connector. Test points are provided for voltage measuring when current is drawn from the LM27761EVM.

2.4 Output Voltage Setting

The output voltage of the LM27761EVM is externally configurable. The value of R1 and R2 determines the output voltage setting. The output voltage can be calculated using [Equation 1](#):

$$V_{OUT} = -1.2 \text{ V} \times (R1 + R2)/R2 \quad (1)$$

3 Board Layout

[Figure 2](#) and [Figure 3](#) show the board layout for the LM27761EVM. The EVM offers capacitors and jumpers to enable the device and to configure it as desired.

The LM27761 dissipates power, especially during high current and high input voltage operation. The EVM layout is designed to minimize temperature rise during operation.




Figure 2. Top Assembly Layer




Figure 3. Bottom Assembly Layer

4 Schematic




Figure 4. LM27761EVM Schematic

5 Bill of Materials

DESIGNATOR	DESCRIPTION	MANUFACTURER	PART NUMBER
PCB	Printed Circuit Board	Any	SV601203
C1	CAP, CERM, 10 μ F, 10 V, +/- 20%, X5R, 0603	TDK	C1608X5R1A106M
C2	CAP, CERM, 1 μ F, 25 V, +/- 10%, X5R, 0402	TDK	C1005X5R1E105K050BC
C3	CAP, CERM, 2.2 μ F, 6.3 V, +/- 10%, X5R, 0603	Taiyo Yuden	JMK107BJ225KAHT
C4	CAP, CERM, 1 μ F, 10 V, +/- 10%, X5R, 0402	MuRata	GRM155R61A105KE15D
C5	CAP, CERM, 10 μ F, 10 V, +/- 20%, X5R, 0603	TDK	C1608X5R1A106M
CPOUT	Test Point, Miniature, Black, TH	Keystone	5001
GND	Test Point, Multipurpose, Black, TH	Keystone	5011
J1	Header, 100mil, 3x1, Gold, TH	Samtec	TSW-103-07-G-S
J2	Standard Banana Jack, Insulated, Red	Keystone	6091
J3	BANANA JACK, 15A, Insulated, Nylon, Yellow	Emerson Network Power	108-0907-001
J4	Standard Banana Jack, Insulated, Black	Keystone	6092
R1	RES, 249 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603249KFKEA
R2	RES, 499 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603499KFKEA
SH-J1	Shunt, 100mil, Gold plated, Black	3M	969102-0000-DA
TP6	Test Point, Multipurpose, Black, TH	Keystone	5011
U1	Low-Noise Regulated Switched-Capacitor Voltage Inverter, DSG0008A	Texas Instruments	LM27761DSGR
VIN	Test Point, Multipurpose, Red, TH	Keystone	5010
VOUT	Test Point, Multipurpose, Yellow, TH	Keystone	5014

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com