



1. Enable Start Up


Test condition: 12Vin, 1.5V/0A




Test condition: 12Vin, 1.5V/5A




Test condition: 14Vin, 1.5V/0A




Test condition: 14Vin, 1.5V/5A



**Test condition: 8Vin, 1.5V/0A**




**Test condition: 8Vin, 1.5V/5A**




**2. Enable Shutdown**


**Test condition: 12Vin, 1.5V/0A**




**Test condition: 12Vin, 1.5V/5A**




### Test condition: 14Vin, 1.5V/0A




### Test condition: 14Vin, 1.5V/5A



### Test condition: 8Vin, 1.5V/0A




### Test condition: 8Vin, 1.5V/5A




### 3. Pre-bias start up


Test condition: 12Vin, 1.5V/0A with pre-bias 0.5V



Test condition: 12Vin, 1.5V/0A with pre-bias 1.0V




Test condition: 12Vin, 1.5V/0A with pre-bias 1.1V




Note: The unit could not start up if the pre-bias voltage is higher than 1.1V

#### 4. Switching node waveform


Test condition: 12Vin, 1.5V/0A




Test condition: 12Vin, 1.5V/5A




Test condition: 14Vin, 1.5V/0A




Test condition: 14Vin, 1.5V/5A



### Test condition: 8Vin, 1.5V/0A




### Test condition: 8Vin, 1.5V/5A




### 5. Output Ripple


#### Test condition: 12Vin, 1.5V/0A



#### Test condition: 12Vin, 1.5V/5A



### Test condition: 14Vin, 1.5V/0A




Buttons

Ch1 Position  
-980.0mdiv

Ch1 Scale  
50.0mV

### Test condition: 14Vin, 1.5V/5A




Buttons

Curs1 Pos  
-15.0mV

Curs2 Pos  
19.0mV


V1 : -15.0mV  
V2 : 19.0mV  
ΔV : 34.0mV

### Test condition: 8Vin, 1.5V/0A



Buttons

### Test condition: 8Vin, 1.5V/5A



Buttons


Curs1 Pos  
-15.0mV

Curs2 Pos  
18.0mV


V1 : -15.0mV  
V2 : 18.0mV  
ΔV : 33.0mV

## 6. Switching Node Jitter

Test condition: 12Vin, 1.5V/0A




Test condition: 12Vin, 1.5V/5A




## 7. Transient Response

Test condition: 12Vin, 1.5V/0A-5A




Test condition: 14Vin, 1.5V/0A-5A






**Test condition: 8Vin, 1.5V/0A-5A**



**8. Over Shoot Reduction(OSR)**


**Test condition: 12Vin, 1.5V/0A-5A on board dynamic**

**OSR=OFF**




**Test condition: 12Vin, 1.5V/0A-5A on board dynamic**

**OSR=MIN**



**Test condition: 12Vin, 1.5V/0A-5A on board dynamic  
OSR=MED**




Buttons

Curs1 Pos  
48.0mV

Curs2 Pos  
7.0mV

V1 : 48.0mV  
V2 : 7.0mV  
ΔV : -41.0mV

**Test condition: 12Vin, 1.5V/0A-5A on board dynamic  
OSR=MAX**



Buttons


Curs1 Pos  
39.0mV

Curs2 Pos  
7.0mV

V1 : 39.0mV  
V2 : 7.0mV  
ΔV : -32.0mV


**9. Deep Sleep Mode and Deep Stop Mode**

**Test condition: 12Vin, 1.5V/0A VID5 change  
DPRSTP#=1V, DPRSLP=GND**




Buttons

**Test condition: 12Vin, 1.5V/0A VID5 change  
SLP=1V Enable SLP  
DPRSTP#=1V, DPRSLP=3.3V**




Buttons

Test condition: 12Vin, 1.5V/0A VID5 change  
DPRSTP#=GND, DPRSLP=3.3V



Test condition: 12Vin, 1.5V/0A VID5 change  
DPRSTP#=GND, DPRSLP=GND



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2021, Texas Instruments Incorporated