



High-Performance Analog Solutions for Handsets

Texas Instruments provides a broad and deep portfolio of high-performance products, applications knowledge and local technical support to help get you to market faster with a winning design. If you want the most reliable, scalable and power-efficient solutions for portable electronics, then look no further than TI.

Audio Power Amplifier - Speaker

Device	Description
TPA2006D1	1.45-W Mono, Fully Differential, Filter-Free Class-D Audio Amplifier
TPA2010D1	2.5-W Mono, Fully Differential, Filter-Free Class-D Audio Amplifier in WCSP
TPA2012D2	2.1-W Stereo Class-D Audio Amplifier in WCSP
TPA2013D1	2.7-W Mono Audio Class-D Amplifier with Integrated Boost Converter
TPA6204A1	1.7-W Mono Fully Differential, Class-AB Audio Amplifier
TPA6205A1	1.25-W Mono, Fully Differential, Class-AB Audio Amplifier

Audio Codec and DAC

Device	Description
TLV320AIC31/2/3	Low-Power Stereo Codec with HP/Speaker Amps and 3D Effects
TLV320AIC3104/5/6	Low-Power Stereo Codec with HP Amp and Enhanced Digital Effects
TLV320AIC34	Low-Power 4-Channel Audio Codec with Dual Audio Buses
PCM3793A/4A	Very Low-Power Stereo Codec with HP/Class-D Speaker Amplifier, Notch Filters, ALC and 3D Effects
TLV320DAC32	Low-Power Stereo DAC with 4 Outputs, HP/Speaker Amps and 3D Effects

Audio Power Amplifier - Headphone

Device	Description
TPA4411	80-mW DirectPath™ Stereo Headphone Driver
TPA6130A2	138-mW DirectPath™ Stereo Headphone Amplifier with I2C Volume Control
TPA6100A2	50-mW Ultra-Low Voltage Stereo Headphone Audio Amplifier
TPA6110A2	Stereo Headphone Audio Amplifier

Video and Interface

Device	Description
OPA360/1	3-V Video Amplifier with 6dB Gain and Filter
SN65LVDS301/302	subLVDS 24-Bit RGB Serdes for LCD Modules

Linear and Logic

Device	Description
TXB0102/4	2/4 - Bit Bidirectional Voltage-Level Translator with Auto Direction Sensing and ±15-kV ESD Protection
TS3A24157	0.65Ω Dual SPDT Analog Switch Dual-Channel 2:1 Multiplexer/Demultiplexer
TS3USB30	High-Speed USB 2.0 (480-Mbps) 1:2 Multiplexer/Demultiplexer Switch
TCA6408	Low-Voltage 8-Bit I2C and SMBus I/O Expander
SN74AUPIGxx	Advanced Ultra-Low Power CMOS Single-Gate Logic

Multi-Channel Power Management

Device	Description
TPS65020	6-Channel Power Mgmt IC with I2C for Li-Ion Powered Systems
TPS65053	5-Channel Power Mgmt IC with GPIO Control for Li-Ion Powered Systems
TPS65820	9-Channel Fully Integrated Power Mgmt IC with Li-Ion Charger for Li-Ion Powered Systems
Partner Products	
TPS65030	Power Management IC for USG-OTG in CSP
TUSB6010	USB 2.0 High-Speed On-the-Go Local Bus Interface Bridge Controller

DC/DC Converter and LDO

Device	Description
TPS62270	400-mA, 2.25-MHz Step-Down Converter with Selectable V _{OUT} (2-Level) for DVS
TPS62400	400-mA and 600-mA Dual Output Step-Down Converter with GPIO Interface for DVS
TPS62290	1000-mA Step-Down Converter in 2mm x 2mm SON Package
TPS62356	1000-mA, 3-MHz Step-Down Converter with I2C for Dynamic Voltage Scaling (DVS)
TPS63000	96% Efficient, 1.2-A Buck-Boost Converter in 3 x 3 QFN
TPS71701	150-mA, High-Bandwidth PSRR LDO in 1.5mm x 1.5mm SON
TPS71918-12	2 x 200-mA Dual Output, High PSRR LDO in 2mm x 2mm SON
TPS728185315	200-mA LDO with Dual Switchable Voltage Level for DVS
TPS3808	Low Quiescent Current, Programmable-Delay Supervisory Circuit (SVS)

Battery Management and Authentication

Device	Description
bq24020	1-Cell Li-Ion Fully Integrated Charger for AC/DC Adapter and USB
bq24070	Single-Chip Charge and System Power-Path Management IC
bq26150	CRC-Based Battery Authentication IC
bq27500	System-Side, Impedance Track™ Fuel Gauge for Li-Ion Powered Systems
bq24300	Charger Front End Protection IC with 30-V Max V _{IN} and 5.5-V LDO Output in 2 x 2 QFN
TLV3012	Low Battery Detector with 6µs Comparator and 1.242-V 1% Reference

Touch Screen Controller

Device	Description
TSC2003	4-Wire Touch Screen Controller with I2C Interface
TSC2004	4-Wire Touch Screen Controller with Programmable Pre-Processing, I2C Interface, 1.2V to 3.6V in CSP
TSC2005	4-Wire Touch Screen Controller with Programmable Pre-Processing, SPI Interface, 1.6V to 3.6V in CSP
TSC2007	4-Wire Touch Screen Controller with Pre-Processing, I2C Interface, 1.2V to 3.6V in CSP with Integrated Audio Converters
TSC2100	Programmable 4-Wire Touch Screen Controller with Stereo Audio Codec and Headphone/Speaker Amplifier
TSC2101	Programmable 4-Wire Touch Screen Controller with 6 Audio Inputs, Stereo Audio Codec and Headphone/Speaker Amplifier

OLED and TFT Display Supply

Device	Description
TPS61045	28-V, 0.4-A Switch Boost Converter for OLED
TPS61140	Dual-Output, Single Inductor Boost Converter for OLED Sub- and WLED Main Display
TPS61081	27-V, 1.2-A Switch Boost Converter with Integrated Power Diode
TPS65120	4-Channel Small Form Factor TFT Display Power Supply
TPS65130	Dual ±Output Driver for Active-Matrix OLED Displays

White LED and Xenon Camera Flash

Device	Description
TPS61050	1.2-A High Power White LED Flashlight Driver with I2C
TPS65560	Integrated Photo Flash Charger and IGBT Driver for Xenon Lamps
TCA6507	7-Bit, I2C and SMBus LED Driver with Intensity Control and Shutdown

White LED Backlight Driver

Device	Description
TPS60250	Charge Pump for 7 WLEDs with 2 or 3 Banks and I2C Interface
TPS61161	Inductive Boost Converter for 6-10 White LEDs with Digital or PWM Dimming
TPS61150	Dual-Output, Single Inductor Boost Converter for up to 12 WLEDs
TPS75103	LDO-Based 2 x 2 Bank LED Driver with PWM Brightness Control

For more information, visit www.ti.com/analogportable

The platform bar, DirectPath and Impedance Track are trademarks of Texas Instruments. All other trademarks are the property of their respective owners. © 2008 Texas Instruments Incorporated. Printed in U.S.A. ♻️ Printed on recycled paper.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Medical	www.ti.com/medical
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2008, Texas Instruments Incorporated