

Filename: PMP7967_REVA_BOM.xls

Variant: None

Generated: 6/5/2013 12:47:47 PM

PMP7967 REVA

Designator	Description	Manufacturer	PartNumber	Quantity
AA1	Printed Circuit Board	Any	PRJ_Number	1
C1, C19, C33, C50	CAP, AL, 330uF, 160V, +/-20%, TH	Nichicon	UCY2C331MHD	4
C3, C4, C5, C6, C21, C22, C23, C24, C35, C36, C37, C38, C52, C53, C54, C55	CAP, CERM, 4.7uF, 50V, +/-10%, X7R, 1206	MuRata	GRM31CR71H475KA12L	16
C7, C25, C39, C56	CAP, CERM, 1uF, 200V, +/-10%, X7R, 1825	Kemet	C1825X105K2RACTU	4
C9, C27, C41, C58	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	MuRata	GRM1885C1H101JA01D	4
C10, C28, C43, C59	CAP, CERM, 0.47uF, 25V, +/-10%, X7R, 0603	MuRata	GRM188R71E474KA12D	4
C11, C29, C44, C60	CAP, CERM, 1uF, 25V, +/-10%, X7R, 0603	MuRata	GRM188R71E105KA12D	4
C12, C30, C45, C46	CAP, CERM, 470pF, 100V, +/-5%, C0G/NP0, 0805	MuRata	GRM2165C2A471JA01D	4
C13	CAP, CERM, 1uF, 16V, +/-10%, X7R, 0603	MuRata	GRM188R71C105KA12D	1
C14	CAP, CERM, 0.047uF, 25V, +/-10%, X7R, 0603	MuRata	GRM188R71E473KA01D	1
C15, C17, C48, C61, D1, D2, D3, D5	RES, 0 ohm, 5%, 0.125W, 0805	Vishay-Dale	CRCW08050000Z0EA	8
C16, C42	CAP, CERM, 1000pF, 50V, +/-5%, C0G/NP0, 0603	TDK	C1608C0G1H102J	2
C18	CAP, CERM, 0.22uF, 16V, +/-10%, X7R, 0603	TDK	C1608X7R1C224K	1
C31, C47, C49	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0603	MuRata	GRM188R71E104KA01D	3
C32	CAP, CERM, 2.2uF, 16V, +/-10%, X5R, 0603	MuRata	GRM188R61C225KE15D	1
C62	CAP, AL, 100uF, 63V, +/-20%, 0.35 ohm, SMD	Panasonic	EEE-FK1J101P	1
FID1, FID2, FID3, FID4, FID5, FID6	Fiducial mark. There is nothing to buy or mount.	N/A	N/A	6
H1, H2, H3, H4	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	B&F Fastener Supply	NY PMS 440 0025 PH	4
IN1, OUT1, Sync In 1, Sync In 2, Sync In 3, Sync In 4	Test Point, TH, Compact, White	Keystone	5007	6
J1, J2	Terminal 50A Lug	Panduit	CB35-36-CY	2
J3, J4, J5, J6	Standard Banana Jack, Uninsulated, 8.9mm	Keystone	575-8	4
L1, L2, L3, L4	Inductor, Shielded Drum Core, WE-HCI 82uH, 7A, 0.0304 ohm, SMD	Würth Elektronik eiSos	7443551130	4
Q1, Q3, Q5, Q7	Diode, Ultrafast, 200V, 3A, SMC	Diodes, Inc.	MURS320-13-F	4
Q2, Q4, Q6, Q8	MOSFET, N-CH, 150V, 50A, PG-TDSON-8	Infineon Technologies	BSC190N15NS3 G	4
R1, R20, R31, R44	RES, 0.01 ohm, 1%, 1W, 2512	Vishay-Dale	WSL2512R0100FEA	4

Designator	Description	Manufacturer	PartNumber	Quantity
R2, R4, R21, R22, R32, R33, R45, R46	RES, 221 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603221RFKEA	8
R6	RES, 10.7k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310K7FKEA	1
R7, R25, R36, R49	RES, 3.3 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06033R30JNEA	4
R8	RES, 2.67k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06032K67FKEA	1
R9, R10, R27, R28, R39, R41, R51, R52	RES, 0 ohm, 5%, 0.1W, 0603	Panasonic	ERJ-3GEY0R00V	8
R12, R30, R43, R54	RES, 60.4k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060360K4FKEA	4
R15	RES, 51k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060351K0JNEA	1
R16	RES, 1.21k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K21FKEA	1
R17	RES, 88.7k ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080588K7FKEA	1
R18	RES, 20 ohm, 5%, 0.125W, 0805	Vishay-Dale	CRCW080520R0JNEA	1
R24, R38	RES, 10.0k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310K0FKEA	2
R26	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA	1
R35	RES, 18.0k ohm, 0.1%, 0.1W, 0603	Yageo America	RT0603BRD0718KL	1
R37	RES, 499 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603499RFKEA	1
R40	RES, 1.50k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K50FKEA	1
R48, R50, R55, R56	RESISTOR 7.5 OHM 3/4W 5% 2010	Panasonic	ERJ-12ZYJ7R5U	4
R57	RES, 100k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603100KFKEA	1
R58	RES, 158k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603158KFKEA	1
SW1, SW2, SW3, SW4	Test Point, TH, Miniature, White	Keystone	5002	4
U1, U3, U4, U7		TI	LM5122MH	4
U5	IC OSC MONO TIMING 3MHZ 8-SOIC	National Semiconductor	LMC555CMX	1
U6	IC 10-OUT DECADE COUNTER 16-SOIC		CD4017BM96	1
U8	Series of Adjustable Micropower Voltage Regulators, 8-pin LLP	National Semiconductor	LP2951CSD	1
Vin Gnd, Vout Gnd	Test Point, TH, Miniature, Black	Keystone	5001	2
Vin, Vout	Test Point, TH, Miniature, Red	Keystone	5000	2

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.