

TEXAS INSTRUMENTS INCORPORATED

PMP20025 Rev A

Power Design Services Test Report

Ryan Manack

1/4/2016

Table of Contents

1	PMP20025 REVA 1.2V/6A – TPS62184	2
1.1	Board Photos.....	2
1.2	Efficiency and Power Loss	3
1.3	Load Regulation	3
1.4	Thermal	4
1.5	Startup	5
1.6	Shutdown	5
1.7	Output Ripple.....	6
1.8	Transient response.....	8
1.9	Synchronous Rectifier Stress.....	8
1.10	Frequency Characteristics.....	9
1.11	Loop Response	10

1/04/2016



PMP20025 Rev A Test Results



1 PMP20025 REVA 1.2V/6A - TPS62184


1.1 Board Photos

The top and bottom images of PMP20025 TPS62184 are shown below.




1.2 Efficiency and Power Loss

The efficiency and power loss of the power supply is shown below at 12Vin with natural convection.




1.3 Load Regulation

The load regulation of the power supply is shown below at 12Vin.



1.4 Thermal

The thermal image of the power supply is shown at room temperature with 12Vin, 6Aout, and natural convection. The power supply soaked for 10min at 6A before the measurement was taken. The IC, which has integrated MOSFETs, is one of the hottest components at 66.7°C.




Area analysis	Value
IC Max	66.7°C
Ind L3 Max	67.2°C
Ind L4 Max	60.3°C

NO.1


1.5 Startup

The power supply startup at 0A is shown below. The startup time is 750 μ s.





1.6 Shutdown

The shutdown of the power supply with 1.2 Ω constant-resistance load is shown below.




1.7 Output Ripple

The 1.2V output ripple is shown in red below, DC coupled with offset, for 0A, 3A and 6A, respectively.




1/04/2016

PMP20025 Rev A Test Results




1.8 Transient response

The transient response is shown in the plot below where the red trace is the DC offset output voltage. The current step is 1A-6A-1A at 5A/us slew rate.



1.9 Synchronous Rectifier Stress



The voltage stresses on the synchronous MOSFETs are shown below. The image is taken at 12Vin and 6A with 200MHz of bandwidth limit.



PMP20025 Rev A Test Results

1.10 Frequency Characteristics

The switch nodes are shown below in blue and red and measured on the inductor. The first image illustrates the power supply switching frequency of ~850kHz per phase. The second image shows negligible frequency jitter. Both images are taken with 12Vin and 6Aout.




PMP20025 Rev A Test Results



1.11 Loop Response

The loop response of the power supply at 12Vin and 6A load current is shown below. The bandwidth is 12.5kHz with ~45° of phase margin.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com