
WMA Version8 Encoder (v1.10) on C64x+

FEATURES

- eXpressDSP™ Algorithm Interface Standard (XDAIS) compliant
- eXpressDSP Digital Media (XDM) interface compliant
- Validated on the DM644x evaluation module (EVM)
- 16-bit PCM samples as input supported
- Full implementation, that is, Class 4 type of WMA Encoder supported
- Bit rates from 5 kbps to 192 kbps supported
- Only CBR (Constant Bit Rate) mode is supported
- 8 to 48 kHz output sampling frequencies

supported

- Mono and stereo channels supported
- Advanced system format (ASF) supported
- Microsoft Acceptance Test criteria compliant

DESCRIPTION

WMA version8 encoder is an XDM compliant encoder, which encodes and converts the wave files into Windows Media Audio (WMA) files in the advanced systems format.

PRODUCT PREVIEW



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

eXpressDSP is a trademark of Texas Instruments.

Performance Summary

This section describes performance of the WMA version8 encoder.

Table 1. Configuration Table

CONFIGURATION	ID
ASF Support Library	WMA_ENC_001

Table 2. Cycles Information – Profiled on DM644x EVM With Code Generation Tools Version 6.0.8

CONFIGURATION ID	PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) ⁽¹⁾		
	TEST DESCRIPTION	AVERAGE	PEAK ⁽²⁾
WMA_ENC_001	Test2_44kHz_long.wav (32 kbps)	28.04	47.85
	Test2_44kHz_long.wav (48 kbps)	22.88	43.79
	Test2_44kHz_long.wav (80 kbps)	23.54	45.42
	Test3_44kHz_long.wav (32 kbps)	31.27	44.40

(1) Measured with program memory, stack, and I/O buffers in external memory and with default cache configuration: 32K-bytes L1P cache, 16K-bytes L1D cache, and 64K-bytes L2 cache.

(2) All sections are placed in external memory and code profiled with cache invalidate enabled for input and output buffer.

Table 3. Memory Statistics - Generated With Code Generation Tools Version 6.0.8

CONFIGURATION ID	MEMORY STATISTICS ⁽¹⁾				TOTAL
	PROGRAM MEMORY	DATA MEMORY			
		INTERNAL ⁽²⁾	EXTERNAL	STACK	
WMA_ENC_001	115.6	0	94.9	1.5	212

(1) All memory requirements are expressed in kilobytes (1 K-byte = 1024 bytes).

(2) Internal memory is not used.

Table 4. Internal Data Memory Split-Up

CONFIGURATION ID	DATA MEMORY - INTERNAL ⁽¹⁾		
	SHARED		INSTANCE
	CONSTANTS	SCRATCH	
WMA_ENC_001	0	0	0

(1) All memory requirements are expressed in kilobytes.

Table 5. External Data Memory Split-Up

CONFIGURATION ID	DATA MEMORY - EXTERNAL ⁽¹⁾		
	SHARED		INSTANCE
	CONSTANTS	SCRATCH	
WMA_ENC_001	44.6	19.3	31

(1) All memory requirements are expressed in kilobytes.

Table 6. Co Processor(s) Memory Statistics⁽¹⁾

CONFIGURATION ID	SEQ DATA MEMORY	SEQ PROG MEMORY	IMX WORKING MEM	IMX IMG BUF	IMX CMD MEM
WMA_ENC_001	0	0	0	0	0

(1) The encoder does not use co-processors; therefore, all the values are zero.

Notes

- I/O buffers:
- - Input buffer size = 16384 bytes
- - Output buffer size = 10000 bytes
- Total data memory for N non pre-emptive instances = Constants + Runtime Tables + Scratch + N*(Instance + I/O buffers + Stack)
- Total data memory for N pre-emptive instances = Constants + Runtime Tables + N*(Instance + I/O buffers + Stack + Scratch)

References

- *TMS320 DSP Algorithm Standard API Reference Guide* (literature number SPRU360)
- *WMA Version8 Encoder on C64x+ User Guide* (literature number SPRUE12)

Glossary

Term	Description
Constants	Elements that go into .const memory section
Scratch	Memory space that can be reused across different instances of the algorithm
Shared	Sum of constants and scratch
Instance	Persistent-memory that contains persistent information - allocated for each instance of the algorithm

Acronyms

Acronym	Description
ASF	Advanced systems format
EVM	Evaluation module
WMA	Windows Media Audio
XDAIS	eXpressDSP Algorithm Interface Standard
XDM	eXpressDSP Digital Media

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DSP	dsp.ti.com
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
Low Power Wireless	www.ti.com/lpw

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments
Post Office Box 655303 Dallas, Texas 75265