



PowerWise® Adaptive Voltage Scaling (AVS) for Portable Applications

Adaptive Voltage Scaling (AVS)


Adaptive Voltage Scaling (AVS) technology is a real-time, continuous, closed-loop power management technology. The AVS technology enables optimized power delivery to processors, ASICs, and SoCs by optimizing adaptively supply voltages over process and temperature variations in order to maximize system-level energy savings.

Portable Applications

The rapid emergence of data-intensive digital processing in smaller and lighter portable devices has created a significant dilemma for system designers. In pursuit of ever increasing functionality in form factors that appeal to customers, designers are challenged to provide more processing power for the new functions. Functions like music and video capabilities, camera, gaming, web browsing, and mobile email are now required without any increase in battery capacity. Incremental improvements in battery technology have been achieved, but these cannot fill the gap that exists. New semiconductor technologies are adding to the problem as leakage current in deep submicron processes add to the overall power consumption. Power conversion technology has also reached a plateau that offers little hope for significant advances. The situation demands rethinking of power management and a comprehensive approach to developing new systems.

What AVS Can Do


AVS technology is a system-level approach that reduces the power consumption of digital System-on-Chip (SoC) solutions used in modern portable devices. AVS technology is ideally suited for managing multiple independent processing engines inside a SoC either when fully operational or when functions are idling, dormant, or completely turned-off. The energy savings from AVS can be seen in the example below. The system consists of the ARM CPU running with a variable frequency of 60, 120, 180, or 240MHz. With AVS, 64% energy saving is achieved compared to the fixed-voltage scheme. AVS also demonstrates 28%



energy saving over Dynamic Voltage Scaling (DVS) because it compensates for process and temperature variation where DVS frequency-to-voltage look-up-tables do not.

AVS Implementation in Portable Devices

The HPM (Hardware Performance Monitor) and APC (Advance Power Controller) are embedded into the processor in order to monitor the process and temperature variation of the ASIC or SoC. A voltage command is sent by the APC via the PowerWise Interface (PWI) or System Power Management Interface (SPMI), a MIPI alliance standard bus, to the Energy Management Unit (EMU), which adaptively regulates the SoC supply voltage. Together, these components form a closed loop which automatically optimizes the voltage for the given process and temperature profile. The AVS loop is fast enough to accommodate frequency scaling, which provides even more power savings.



AVS Power Savings

In portable devices, AVS enables up to 64% power savings with frequency scaling compared to a fixed-voltage method over process and temperature variation. The power savings depends on multiple factors such as design implementation, frequency scaling, etc.

Applications

- Applications processors or SoC for smart phones
- Graphics processors for handheld devices
- Processors in personal navigation devices

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2012, Texas Instruments Incorporated