# TMS320C5504 & TMS320C5505 Digital Signal Processors – Industry's lowest-power 16-bit DSPs TMS320C550x Evaluation Module

## What products did TI launch on June 10, 2009?

TI announced the TMS320C5505 and TMS320C5504 digital signal processors (DSPs), which are the latest devices in the TMS320C550x generation, and the industry's lowest power 16-bit DSPs operating at lower power levels for energy-efficient portable applications requiring longer battery life. Additionally, the TMS320C5505 EVM, a fully-functional, feature-rich evaluation module (EVM), is announced in conjunction with the parts.

## What applications do the processors target?

The processors are optimized for sophisticated portable devices that require low power and longer battery life, including portable voice/audio devices, noisecancellation headphones, musical instruments, medical monitoring devices, biometrics and industrial instruments. Other applications that benefit from the C5505 and C5504 DSPs are software-defined radio, wireless microphones, telephony and audio cards.

## What is the difference between the C5505 and C5504 DSPs?

Each processor is optimized to address the needs of manufacturers based on their specific requirements. The C5505 DSP is fully loaded with software, integrated peripherals, increased memory, an FFT hardware accelerator and an integrated power management LDO for increased functionality and more user-friendly features. The C5504 DSP is a lower-cost DSP with software compatibility, optimized memory and an integrated power management LDO that maximizes OEMs'/ODMs' investment.

What products did TI launch on June 10, 2009?

What applications do the processors target?

What is the difference between the C5505 and C5504 DSPs?

What are the key features/benefits of the C5505 and C5504 DSPs?

What are the key features/benefits of the C5505 EVM?

What is an FFT and how is it different from what other companies are offering?

*Is the C5505 EVM also compatible with the C5504 processor?* 

What benefits can end users experience from the C5505 and C5504 DSPs?

What is the price of the C5505 and C5504 DSPs and C5505 EVM?

Are other TMS320C5000™ parts available or are these the first?

In this announcement, you tout low power. How do these devices differ from other low-power devices from TI?

What is the market opportunity for TI in this space?

What are the key features/benefits of the C5505 and C5504 DSPs?

#### TMS320C5505 DSP

- Standby power less than 150 µW and active power less than 0.15 mW/MHz
- Highly-integrated peripherals including a programmable FFT hardware accelerator up to 1024 points, high-speed USB 2.0, LCD display, I<sup>2</sup>S, UART, SPI, MMC/SD and GPIOs and 10-bit 4-channel SAR ADC – reduce system cost and enable more user-friendly portable features
- Scalable and pin-to-pin compatible with C5504 DSP low-power devices allows for the ability to design an entire product portfolio using the same hardware and software platform
- Up to 320 KB of on-chip memory saves both power and system cost by reducing the need for external memory

#### TMS320C5504 DSP

- Standby power less than 150 μW and active power less than 0.15 mW/MHz
- Highly-integrated peripherals including a high-speed USB 2.0, I<sup>2</sup>S, UART, SPI, MMC/SD and GPIOs – reduce system cost and enable more user-friendly portable features
- Scalable and pin-to-pin compatible with C5505 DSP low-power devices allows for the ability to design an entire product portfolio using the same hardware and software platform
- Up to 256 KB of on-chip memory saves both power and system cost by reducing the need for external memory

### What are the key features/benefits of the C5505 EVM?

The EVM is fully functional with the ability to evaluate every aspect of the silicon. Embedded on-board emulation only requires an A-to-mini B USB cable to enable customers to perform debugging and development work. The EVM offers the ability to sample code to multiple applications and includes a wide range of software resources and documentation.

What is an FFT and how is it different from what other companies are offering?

An FFT is a Fast Fourier Transform hardware accelerator incorporated for faster, more power-efficient filtering. Though other companies offer an FFT on their processors, TI is offering a 1024-point programmable FFT, which is four to six times more energy efficient and two to four times more cycle efficient.

*Is the C5505 EVM also compatible with the C5504 processor?* 

Yes, the C5505 EVM is fully compatible with the C5504 processor.

What benefits can end users experience from the C5505 and C5504 DSPs? End users will realize an improvement in battery life of over 50 percent and lower system cost with user-friendly features on their portable devices.

What is the price of the C5505 and C5504 DSPs and C5505 EVM?

The C5505 DSP is priced at US \$6.75 in quantities of 1,000 units (1 KU). The C5504 DSP is available for US \$5.60 in quantities of 1,000 units. The C5505 EVM is available for US \$395.00.

Are other TMS320C5000™ parts available or are these the first? We have a portfolio of 34 existing parts. These two are the latest C5000™ DSPs.

In this announcement, you tout low power. How do these devices differ from other lowpower devices from TI? TI offers a suite of low-power devices from digital signal processors, digital media processors and microcontrollers to complementary analog parts. The key differentiating factors are cost – the C5505 and C5504 devices are the lowest power DSPs in our portfolio – and target applications that each is optimized for as. The C5505 and C5504 DSPs are designed for applications where active power and standby power are both key careabouts. Best-inclass combination of standby and active power provided by C5505 and C5504 DSPs of up to 100-MHz performance maximizes the battery life for several portable applications.

MSP430 is ideal for low-power applications that require performance up to 25 MHz. The C5505 and C5504 DSPs complement the MSP430 family by providing excellent power consumption for applications requiring performance up to 100 MHz. More specifically, C5505 and C5504 processors bring extensive DSP performance at ultra-low power levels. Other processors such as OMAP-L1x, OMAP35x and TMS320C6000<sup>™</sup> target applications that require much higher performance than 100 MHz. They are also the industry's lowest power 16-bit DSPs.

So, C5000 DSPs and the new products we're announcing today sit nicely between MSP430 and OMAP<sup>TM</sup>/C6000 embedded processors from TI.

What is the market opportunity for TI in this space? The TMS320C5505 and TMS320C5504 DSPs bring ultra-low power DSP functionality of up to 100 MHz at very low cost for a wide variety of portable applications. The market for smart portable devices is growing significantly across medical, consumer and industrial applications. The TMS320C5000<sup>™</sup> DSP platform complements MSP430 and other low-power processors from TI to enable smart analysis and diagnostics in portable devices. With excellent standby and dynamic power, C5000<sup>™</sup> DSPs cater to a range of markets across "mostly-off" to "mostly-on" end equipments.

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

C5000, OMAP, TMS320C5000 and TMS320C6000 are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Broadband	www.ti.com/broadband
DSP	dsp.ti.com	Digital Control	www.ti.com/digitalcontrol
Clocks and Timers	www.ti.com/clocks	Medical	www.ti.com/medical
Interface	interface.ti.com	Military	www.ti.com/military
Logic	logic.ti.com	Optical Networking	www.ti.com/opticalnetwork
Power Mgmt	power.ti.com	Security	www.ti.com/security
Microcontrollers	microcontroller.ti.com	Telephony	www.ti.com/telephony
RFID	www.ti-rfid.com	Video & Imaging	www.ti.com/video
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2009, Texas Instruments Incorporated