




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRV81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = Top Overlay	TID #: N/A		
PLOT NAME = Top Overlay	GENERATED : 7/19/2024	1:01:28 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRU81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = Top Solder	TID #: N/A		
PLOT NAME = Top Solder Mask	GENERATED : 7/19/2024	1:01:28 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRV81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = Top Layer	TID #: N/A		
PLOT NAME = Top Layer	GENERATED : 7/19/2024 1:01:29 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRV81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = Signal Layer 1	TID #: N/A		
PLOT NAME = Signal 1	GENERATED : 7/19/2024	1:01:29 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRV81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = Signal Layer 2	TID #: N/A		
PLOT NAME = Signal 2	GENERATED : 7/19/2024	1:01:30 PM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRV81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = Bottom Layer	TID #: N/A		
PLOT NAME = Bottom Layer	GENERATED : 7/19/2024 1:01:30 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRV81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = Bottom Solder	TID #: N/A		
PLOT NAME = Bottom Solder Mask	GENERATED : 7/19/2024 1:01:30 PM	TEXAS INSTRUMENTS	





Drill Drawing :

Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance	Routed Path Length	Hole Length
⊙	41	7.87mil (0.200mm)	PTH	Round	Top Layer - Bottom Layer	+3mil/-3mil	-	-
⊖	452	12.00mil (0.305mm)	PTH	Round	Top Layer - Bottom Layer	-	-	-
□	6	29.53mil (0.750mm)	PTH	Round	Top Layer - Bottom Layer	-	-	-
◇	15	40.00mil (1.016mm)	PTH	Round	Top Layer - Bottom Layer	+3mil/-3mil	-	-
▽	10	45.28mil (1.150mm)	PTH	Round	Top Layer - Bottom Layer	+3mil/-3mil	-	-
○	22	51.18mil (1.300mm)	PTH	Round	Top Layer - Bottom Layer	+3mil/-3mil	-	-
⊛	24	63.00mil (1.600mm)	PTH	Round	Top Layer - Bottom Layer	+3mil/-3mil	-	-
⊠	3	31.50mil (0.800mm)	PTH	Slot	Top Layer - Bottom Layer	-	86.61mil (2.200mm)	118.11mil (3.000mm)
⊞	2	51.18mil (1.300mm)	PTH	Slot	Top Layer - Bottom Layer	+3mil/-3mil	-21.65mil (-0.550mm)	29.53mil (0.750mm)
575 Total								

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRU81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Drill Drawing	GENERATED : 7/19/2024 1:01:31 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:DRU81602Q1_EVM	REV: B	SUN REV: Not in version control
LAYER NAME = M2 Board Dimensions	TID #: N/A		
PLOT NAME = Board Dimensions	GENERATED : 7/19/2024 1:01:33 PM	TEXAS INSTRUMENTS	