



U1


ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD114-001	REV: A	SUN REV: Not in version control
LAYER NAME = Top Overlay	TID #: N/A		
PLOT NAME = Top Overlay	GENERATED : 9/10/2025 4:12:56 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD114-001	REV: A	SUN REV: Not in version control
LAYER NAME = Top Solder	TID #: N/A		
PLOT NAME = Top Solder Mask	GENERATED : 9/10/2025 4:12:56 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD114-001	REV: A	SUN REV: Not in version control
LAYER NAME = Top Layer	TID #: N/A		
PLOT NAME = Top Layer	GENERATED : 9/10/2025 4:12:56 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD114-001	REV: A	SUN REV: Not in version control
LAYER NAME =	TID #: N/A		
PLOT NAME = Signal Layer 1	GENERATED : 9/10/2025	4:12:56 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD114-001	REV: A	SUN REV: Not in version control
LAYER NAME =	TID #: N/A		
PLOT NAME = Signal Layer 2	GENERATED : 9/10/2025 4:12:56 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD114-001	REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Layer	TID #: N/A		
PLOT NAME = Bottom Layer	GENERATED : 9/10/2025 4:12:56 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD114-001	REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Solder	TID #: N/A		
PLOT NAME = Bottom Solder Mask	GENERATED : 9/10/2025 4:12:56 PM	TEXAS INSTRUMENTS	



Symbol	Count	Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
⊗	55	0,200mm (7,87mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	52	0,203mm (8,00mil)	PTH	Round	Top Layer - Bottom Layer	
H	4	0,300mm (11,81mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	14	0,305mm (12,00mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	13	0,356mm (14,00mil)	PTH	Round	Top Layer - Bottom Layer	
C	10	0,381mm (15,00mil)	PTH	Round	Top Layer - Bottom Layer	
B	2	0,400mm (15,75mil)	PTH	Round	Top Layer - Bottom Layer	
O	90	0,406mm (16,00mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	2	0,465mm (18,29mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	2	0,650mm (25,59mil)	NPTH	Round	Top Layer - Bottom Layer	
A	4	0,700mm (27,56mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	4	0,900mm (35,43mil)	PTH	Round	Top Layer - Bottom Layer	
□	5	1,016mm (40,00mil)	PTH	Round	Top Layer - Bottom Layer	
F	56	1,100mm (43,31mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	12	1,150mm (45,28mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	4	1,300mm (51,18mil)	PTH	Round	Top Layer - Bottom Layer	
D	2	1,400mm (55,12mil)	PTH	Slot	Top Layer - Bottom Layer	
⊗	10	1,500mm (59,06mil)	PTH	Round	Top Layer - Bottom Layer	
⊗	18	1,600mm (63,00mil)	PTH	Round	Top Layer - Bottom Layer	
E	2	1,700mm (66,93mil)	PTH	Slot	Top Layer - Bottom Layer	
	361 Total					

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size + Slot length as defined in the PCB layout

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD114-001	REV: A	SUN REV: Not in version control
LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Drill Drawing	GENERATED : 9/10/2025 4:12:56 PM	TEXAS INSTRUMENTS	

